






AVERY DENNISON MARKETING SPECIFICATION

THE SUBJECT MATTER DISCLOSED HEREIN EMBODIES PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF THE AVERY DENNISON CO. NONE OF WHICH SHALL BE COPIED, REPRODUCED, DISCLOSED TO OTHERS, PUBLISHED OR USED IN WHOLE OR IN PART, FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS BEING MADE AVAILABLE WITHOUT THE EXPRESS ADVANCE WRITTEN PERMISSION OF A DULY AUTHORIZED AGENT OF THE COMPANY. THIS DOCUMENT IS THE PROPERTY OF THE AVERY DENNISON CO. AND IS TO BE RETURNED TO THE COMPANY ON DEMAND.

HISTORY

REV.	DATE	DESCRIPTION
A	12-08-11	RELEASED



NOTES:

1. MATERIAL SHALL CONFIRM TO WSK-M4D706-A, MS-DB-41 CPN1826, AND GMP.PA66.015

APPROVALS:

ENG. APPR.

Q.A. APPR.

SPECIFIED TOLERANCES ARE:

.XX ± .03 INCHES .X ± .7 MM
 .XXX ± .01 INCHES .XX ± .25 MM
 ANGULAR: ± 2°

MATERIAL

NYLON 6/6,
 IMPACT MODIFIED, HEAT STABILIZED

COLOR

GRAY



AVERY DENNISON

FASTENER DIVISION
 FITCHBURG, MA 01420 U.S.A.
 TEL. 1-800-225-5913
 FAX. 978-353-8157

DESCRIPTION

DIRECTIONAL SLOT TIE

STOCK NO.

20123-0

REV.

A

APPLICATION:	UNDER HOOD
MOUNTING:	7MM X12MM MIN. SLOTTED HOLE
PANEL THICKNESS RANGE:	0.7MM TO 3.6MM THK.
TENSILE STRENGTH:	50 LBF / 222N MIN.
WEIGHT:	1.76 GRAMS
TEMPERATURE RANGE:	-40°F (-40°C) TO 239°F (115°C) CONTINUOUS AND 257°F (125°C) AT MAXIMUM EXPOSURE
BUNDLE DIAMETER:	Ø 1.6MM TO Ø 38.1MM
TOOL:	12001- HAND INSTALLATION TOOL 12500- PNUEM. INSTALLATION TOOL
TOOL TENSION SETTING:	6 - 8
PACKAGING:	500/BAG, 10 BAGS/MASTER

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Avery Dennison:](#)

[20123-0](#)