



AVERY DENNISON MARKETING SPECIFICATION

© 2019 AVERY DENNISON CORPORATION. ALL RIGHTS RESERVED

HISTORY

REV.	DATE	DESCRIPTION
A	07.31.19	RELEASED
B	09.10.19	CORRECTED MAX BUNDLE TO BE 38.1mm



RECOMMENDED
CUT LENGTH

NOTES:

1. Δ = INDICATES SPECIAL CHARACTERISTIC

APPROVALS:

ENG. APPR.	<i>Daniel Gilbertson</i>	09.10.19
Q.A. APPR.	<i>Caitlin Vaillancourt</i>	09.10.19

SPECIFIED TOLERANCES ARE:

.XX $\pm$.03 INCHES	.X $\pm$.7 mm
.XXX $\pm$.010 INCHES	.XX $\pm$.25 mm
ANGULAR: $\pm$ 2°	

MATERIAL **NYLON 6/6,**
IMPACT MODIFIED, HEAT STAB.

COLOR

BLACK



AVERY
DENNISON

FASTENER DIVISION
FITCHBURG, MA 01420 U.S.A.
TEL. 1-800-225-5913
FAX. 978-353-8157

DESCRIPTION

OVAL FIR TREE TIE

STOCK NO.

20185-0

REV.

B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Avery Dennison:](#)

[20185-0](#)