
Type: CDH38D11/SLD, CDH38D11/S

- Product Description
- 4.0×4.0mm Max.(L×W), 1.2mm Max. Height.
- Both Low DCR type CDH38D11/SLD and Standard type CDH38D11/S are available.
- Inductance range: $0.72 \sim 33 \,\mu$ H(CDH38D11/SLD), $0.68 \sim 39 \,\mu$ H(CDH38D11/S)
- Rated current range: 0.36~2.4A(CDH38D11/SLD), 0.40~3.5A (CDH38D11/S)
- In addition to the High power versions of inductors shown here, custom inductors are available to meet your exact requirements.


Feature

- Magnetically unshielded construction.
- · Ideally used in Mobilephone, PDA, MP3, DSC/DVC, etc as DC-DC Converter inductors.
- Strong resistance against drop shock.
- RoHS Compliance


Dimensions (mm)




◆ Land Pattern (mm)



Schematics (Bottom)







Type: CDH38D11/SLD, CDH38D11/S

Specification(CDH38D11/SLD)

Part Name ※	Stamp	Inductance (µH) [Within] 100kHz	D.C.R.(Ω) Max.(Typ.) (at 20℃)	Saturation Current (A) ※1 (at 20℃)	Temperature rise current (A)%2
CDH38D11SLDNP-R72M	R72	0.72±20%	36.3m(29m)	2.40	3.40
CDH38D11SLDNP-1R0M	1R0	1.0±20%	41.3m(33m)	2.00	3.30
CDH38D11SLDNP-1R4M	1R4	1.4±20%	55.0m(44m)	1.80	2.70
CDH38D11SLDNP-1R9M	1R9	1.9±20%	66.3m(53m)	1.45	2.30
CDH38D11SLDNP-2R4M	2R4	2.4±20%	93.8m(75m)	1.30	1.88
CDH38D11SLDNP-2R9M	2R9	2.9±20%	97.5m(78m)	1.20	1.86
CDH38D11SLDNP-3R6M	3R6	3.6±20%	129.6m(108m)	1.10	1.47
CDH38D11SLDNP-4R2M	4R2	4.2±20%	135.6m(113m)	1.00	1.41
CDH38D11SLDNP-5R1M	5R1	5.1±20%	171.6m(143m)	0.90	1.30
CDH38D11SLDNP-5R8M	5R8	5.8±20%	182.4m(152m)	0.84	1.25
CDH38D11SLDNP-7R2M	7R2	7.2±20%	228m(190m)	0.75	0.92
CDH38D11SLDNP-8R2M	8R2	8.2±20%	252m(210m)	0.70	0.86
CDH38D11SLDNP-100M	100	10±20%	336m(280m)	0.64	0.78
CDH38D11SLDNP-120M	120	12±20%	0.38(0.32)	0.60	0.75
CDH38D11SLDNP-150M	150	15±20%	0.49(0.41)	0.52	0.67
CDH38D11SLDNP-180M	180	18±20%	0.55(0.46)	0.48	0.57
CDH38D11SLDNP-220M	220	22±20%	0.73(0.61)	0.44	0.49
CDH38D11SLDNP-270M	270	27±20%	0.84(0.70)	0.42	0.46
CDH38D11SLDNP-330M	330	33±20%	1.0(0.83)	0.36	0.45

Type: CDH38D11/SLD, CDH38D11/S

Specification(CDH38D11/S)

Part Name ※	Stamp	Inductance (µH) [Within] 100kHz	D.C.R.(Ω) Max.(Typ.) (at 20℃)	Saturation Current (A) ※1 (at 20°C)	Temperature rise current (A)%2
CDH38D11SNP-R68M	0R7	0.68±20%	36.3m(29m)	3.50	3.30
CDH38D11SNP-1R0M	1R0	1.0±20%	48.8m(39m)	2.80	2.85
CDH38D11SNP-1R2M	1R2	1.2±20%	60.0m(48m)	2.60	2.60
CDH38D11SNP-1R8M	1R8	1.8±20%	78.8m(63m)	2.20	2.25
CDH38D11SNP-2R2M□	2R2	2.2±20%	102.5m(82m)	1.90	1.84
CDH38D11SNP-2R7M	2R7	2.7±20%	121.2m(101m)	1.70	1.56
CDH38D11SNP-3R3M	3R3	3.3±20%	138.0m(115m)	1.56	1.50
CDH38D11SNP-4R2M	4R2	4.2±20%	168.0m(140m)	1.35	1.40
CDH38D11SNP-4R7M	4R7	4.7±20%	189.6m(158m)	1.30	1.20
CDH38D11SNP-5R8M	5R8	5.8±20%	240m(200m)	1.12	1.12
CDH38D11SNP-6R8M	6R8	6.8±20%	264m(220m)	1.05	1.08
CDH38D11SNP-8R2M	8R2	8.2±20%	348m(290m)	0.96	0.92
CDH38D11SNP-100M	100	10±20%	0.44(0.37)	0.84	0.82
CDH38D11SNP-120M	120	12±20%	0.49(0.41)	0.80	0.80
CDH38D11SNP-150M	150	15±20%	0.67(0.56)	0.68	0.67
CDH38D11SNP-180M	180	18±20%	0.76(0.63)	0.64	0.62
CDH38D11SNP-220M	220	22±20%	0.89(0.74)	0.58	0.59
CDH38D11SNP-270M	270	27±20%	1.02(0.85)	0.51	0.52
CDH38D11SNP-330M	330	33±20%	1.32(1.1)	0.44	0.50
CDH38D11SNP-390M□	390	39 ± 20 %	1.56(1.3)	0.40	0.44

※ Description Of Part Name

CDH38D11/S-R68N□ B Box C Carrier Tape

%1. Saturation current: The DC current at which the inductance decreases to 65% of it's nominal value.

2. Temperature rise current: The DC current at which the temperature rise is $\Delta t=40^{\circ}C$ (Ta=20 $^{\circ}C$).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sumida:

CDH38D11SNP-5R8MC CDH38D11SLDNP-7R2MC CDH38D11SNP-390MC CDH38D11SLDNP-3R6MC CDH38D11SLDNP-120MC CDH38D11SNP-1R2MC CDH38D11SLDNP-220MC CDH38D11SLDNP-1R9MC CDH38D11SLDNP-5R8MC CDH38D11SNP-330MC CDH38D11SNP-2R7MC CDH38D11SLDNP-1R4MC CDH38D11SLDNP-2R9MC CDH38D11SNP-1R0MC CDH38D11SNP-150MC CDH38D11SLDNP-0R72MC CDH38D11SNP-2R2MC CDH38D11SNP-6R8MC CDH38D11SNP-150MC CDH38D11SNP-270MC CDH38D11SNP-4R2MC CDH38D11SNP-0R68MC CDH38D11SLDNP-330MC CDH38D11SNP-270MC CDH38D11SNP-4R2MC CDH38D11SNP-0R68MC CDH38D11SLDNP-1R0MC CDH38D11SNP-120MC CDH38D11SNP-100MC CDH38D11SNP-0R68MC CDH38D11SNP-3R3MC CDH38D11SLDNP-2R4MC CDH38D11SNP-100MC CDH38D11SNP-180MC CDH38D11SNP-3R3MC CDH38D11SLDNP-2R4MC CDH38D11SLDNP-150MC CDH38D11SLDNP-270MC CDH38D11SLDNP-4R2MC CDH38D11SLDNP-100MC CDH38D11SLDNP-180MC CDH38D11SNP-4R7MC CDH38D11SNP-8R2MC CDH38D11SNP-220MC CDH38D11SNP-1R8MC CDH38D11SNP-4R7MC CDH38D11SNP-8R2MC