


SMD Power Inductor CD105





Description

- Ferrite durm core construction.
- Magnetically unshielded.
- L × W × H: 10.4 × 9.4 × 5.8mm Max.
- Product weight:1.3 g(Ref.)
- Moisture Sensitivity Level: 1
- RoHS compliance.

Dimension - [mm]



Land pattern and Schematics - [mm]



Environmental Data

- Operating temperature range: -40°C ~ +100°C (including coil's self temperature rise)
- Storage temperature range: -40°C ~ +100°C
- Solder reflow temperature: 260 °C peak.

Packaging


- Carrier tape and reel packaging.
- 12.9" diameter reel
- 500pcs per reel

Applications

- Ideally used in PDA,MP3,DSC/DVC,HDD, Portable DVD, etc as DC-DC converter inductors.

SMD Power Inductor

CD105




Electrical Characteristics

Part Name	Inductance (μH) [Within] ※1	D.C.R. (Ω) [MAX.] (at 20°C)	Rated Current (A) ※2
CD105NP-100MC	10 $\pm$ 20%	0.06	2.60
CD105NP-120MC	12 $\pm$ 20%	0.07	2.45
CD105NP-150MC	15 $\pm$ 20%	0.08	2.27
CD105NP-180MC	18 $\pm$ 20%	0.09	2.15
CD105NP-220MC	22 $\pm$ 20%	0.10	1.95
CD105NP-270MC	27 $\pm$ 20%	0.11	1.76
CD105NP-330MC	33 $\pm$ 20%	0.12	1.50
CD105NP-390MC	39 $\pm$ 20%	0.14	1.37
CD105NP-470KC	47 $\pm$ 10%	0.17	1.28
CD105NP-560KC	56 $\pm$ 10%	0.19	1.17
CD105NP-680KC	68 $\pm$ 10%	0.22	1.11
CD105NP-820KC	82 $\pm$ 10%	0.25	1.00
CD105NP-101KC	100 $\pm$ 10%	0.35	0.97
CD105NP-121KC	120 $\pm$ 10%	0.40	0.89
CD105NP-151KC	150 $\pm$ 10%	0.47	0.78
CD105NP-181KC	180 $\pm$ 10%	0.63	0.72
CD105NP-221KC	220 $\pm$ 10%	0.73	0.66
CD105NP-271KC	270 $\pm$ 10%	0.97	0.57
CD105NP-331KC	330 $\pm$ 10%	1.15	0.52
CD105NP-391KC	390 $\pm$ 10%	1.30	0.48
CD105NP-471KC	470 $\pm$ 10%	1.48	0.42
CD105NP-561KC	560 $\pm$ 10%	1.90	0.33
CD105NP-681KC	680 $\pm$ 10%	2.25	0.28
CD105NP-821KC	820 $\pm$ 10%	2.55	0.24

※1: Inductance measuring frequency: 10 μH ~ 82 μH ; at 2.52MHz.
100 μH ~ 820 μH ; at 1kHz.













※2: Rated current: The DC current at which the inductance decreases to 90 % of it's initial value or when $\Delta t=40^\circ\text{C}$, whichever is lower ($T_a=20^\circ\text{C}$).

SMD Power Inductor CD105



Saturation Current & Temperature Rise Graph

— L (25°C) — L (105°C) — ΔT




SMD Power Inductor

CD105



Saturation Current & Temperature Rise Graph

— L (25°C) — L (105°C) — ΔT




SMD Power Inductor CD105




Solder Reflow Condition

Heat Endurance



Temperature Chart



Please refer to the sales offices on our website - <http://www.sumida.com>

Hong Kong

Tel. +852-2880-6781
FAX. +852-2565-9600
sales@hk.sumida.com

Saitama(Japan)

Tel. +81-48-691-7300
FAX. +81-48-691-7340
sales@jp.sumida.com

Chicago

Tel. +1-847-545-6700
FAX. +1-847-545-6720
sales@us.sumida.com

Shanghai

Tel. +86-21-5836-3299
FAX. +86-21-5836-3266
shanghai.sales@cn.sumida.com

Seoul

Tel. +82-2-6237-0777
FAX. +82-2-6237-0778
sales@kr.sumida.com

Obernzell

Tel. +49-8591-937-0
FAX. +49-8591-937-103
contact@eu.sumida.com

Shenzhen

Tel. +86-755-8291-0228
FAX. +86-755-8291-0338
shenzhen.sales@cn.sumida.com

Singapore

Tel. +65-6296-3388
FAX. +65-6841-4426
sales@sg.sumida.com

Neumarkt

Tel. +49-9181-4509-110
FAX. +49-9181-4509-310
infocomp@eu.sumida.com

Taipei

Tel. +886-2-8751-2737
FAX. +886-2-8751-2738
sales@tw.sumida.com

San Jose

Tel. +1-408-321-9660
FAX. +1-408-321-9308
sales@us.sumida.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sumida:

<u>CD105NP-560KC</u>	<u>CD105NP-330MC</u>	<u>CD105NP-180MC</u>	<u>CD105NP-181KC</u>	<u>CD105NP-331KC</u>	<u>CD105NP-561KC</u>
<u>CD105NP-220MC</u>	<u>CD105NP-390MC</u>	<u>CD105NP-681KC</u>	<u>CD105NP-151KC</u>	<u>CD105NP-271KC</u>	<u>CD105NP-821KC</u>
<u>CD105NP-270MC</u>	<u>CD105NP-820KC</u>	<u>CD105NP-100MC</u>	<u>CD105NP-680KC</u>	<u>CD105NP-121KC</u>	<u>CD105NP-391KC</u>