


High Power thin film chip resistor with long side termination



FEATURES

- Excellent reliability and stability even under harsh conditions
- Low noise, THIN FILM construction
- EIA Standard case size(1206)
- RoHS Compliance and 100% Lead-Free

APPLICATIONS

- Automotive
- Scale, Test & Measurement
- Optical & Telecommunication
- Medical and Industrial Equipment


Electrical Specification

Type	Size (in inch)	Power Rating	Resistance Tolerance	TCR	Resistance Range (ohm) *E24 & E96 series R value	Packaging
PRG3216	1206	1.0W	±0.1%(B)	±25ppm/°C(P) ±50ppm/°C(Q)	47 – 100k	Tape & Reel T5 = 5000pcs
			±0.5%(D)	±25ppm/°C(P) ±50ppm/°C(Q)	10 – 100k 2.5 – 100k	
PRG5025	2010	1.5W~2.0W	±0.1%(B)	±25ppm/°C(P) ±50ppm/°C(Q)	47 – 200k	Tape & Reel T4 = 4000pcs
			±0.5%(D)	±25ppm/°C(P) ±50ppm/°C(Q)	10 – 200k 2.5 – 100k	
PRG6432	2512	2.0W~3.0W	±0.1%(B)	±25ppm/°C(P) ±50ppm/°C(Q)	47 – 250k	
			±0.5%(D)	±25ppm/°C(P) ±50ppm/°C(Q)	10 – 250k 2.5 – 250k	

Reliability Specification


Test Item	Test Method (JIS C5201-1)	Δ R Limits
Short Time Overload	2.5 times of rated power for 5sec.	Under 47 Ω ±(0.1%+0.01 Ω) 47 Ω and higher ±(0.05%+0.01 Ω)
Load Life	70°C, rated power, 90min. on/ 30min. Off, 1000hrs.	Under 47 Ω ±(0.25%+0.05 Ω) 47 Ω and higher ±(0.1%+0.01 Ω)
Temp. Hum. Bias	85°C 85% RH, 1/10 rated power, 90min. on/ 30min. Off, 1000hrs.	
Thermal Shock	-55°C (30min)/room temp.(2min) /+125°C(30min)/room temp.(2min), no bias, 1000 cycles	
High Temp. Exposure	155°C for 1000h, no bias.	

Dimensions



Unit (mm)			
Type	PRG3216	PRG5025	PRG6432
Dimensions			
W	3.2+0.4/-0.2	5.0±0.2	6.4+0.2/-0.4
L	1.6±0.2	2.5±0.2	3.2±0.2
t	0.45±0.1	0.45±0.1	0.45±0.1
a	0.30±0.2	0.55±0.2	0.40±0.2
b	0.35±0.2	0.60±0.2	0.55±0.2

Recommended Land Pattern



TYPE	a	b	c	Unit (mm)
				d (*1) (Reference value)
PRG3216	0.8±0.1	1.1±0.1	3.7±0.1	27mm or more
PRG5025	1.3±0.1	1.6±0.1	5.7±0.1	27mm or more
PRG6432	2.0±0.1	2.1±0.1	6.9±0.1	27mm or more

(*1) Please give consideration to heat dissipation of the resistor.


The solder fillet when resistor is powered up should not exceed 155°C.

Power Derating Curve

(PRG3216)

For operation above 70°C, power must be derated according to the following chart.


However, in actual use, verify the fillet temperature is not exceeding 155°C.



(PRG5025)

For operation above 1.5W:70°C, 2.0W:50°C, power must be derated according to the following chart


However, in actual use, verify the fillet temperature is not exceeding 155°C.




(PRG6432)

For operation above 2.0W:70°C, 3.0W:25°C, power must be derated according to the following chart



However, in actual use, verify the fillet temperature is not exceeding 155°C.





Load Life @ 70°C at Rated Power 1.0W





Temperature Humidity Bias



Thermal Shock -55°C - +125°C



High Temperature Exposure at 155°C with no power



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Susumu:

[PRG3216Q-330-D-T5](#) [PRG6432P-49R9-D-T4](#) [PRG6432Q-7321-D-T4](#) [PRG6432Q-49R9-B-T4](#) [PRG3216Q-2550-B-T5](#) [PRG5025P-1132-B-T4](#) [PRG5025Q-39R2-D-T4](#) [PRG5025Q-40R2-D-T4](#) [PRG5025Q-100-D-T4](#) [PRG5025Q-202-B-T4](#) [PRG3216Q-4020-D-T5](#) [PRG3216Q-45R3-D-T5](#) [PRG6432P-6340-B-T4](#) [PRG6432P-333-D-T4](#) [PRG5025P-751-D-T4](#) [PRG6432Q-2212-B-T4](#) [PRG6432Q-4320-D-T4](#) [PRG3216Q-14R7-D-T5](#) [PRG5025Q-34R8-D-T4](#) [PRG5025P-2151-B-T4](#) [PRG3216Q-333-B-T5](#) [PRG5025Q-9311-D-T4](#) [PRG3216Q-511-D-T5](#) [PRG5025Q-2101-D-T4](#) [PRG5025Q-61R9-B-T4](#) [PRG5025Q-332-D-T4](#) [PRG6432Q-2101-B-T4](#) [PRG5025P-78R7-D-T4](#) [PRG5025Q-63R4-D-T4](#) [PRG5025Q-71R5-B-T4](#) [PRG6432P-1211-B-T4](#) [PRG6432Q-510-D-T4](#) [PRG5025P-9761-B-T4](#) [PRG5025P-4992-D-T4](#) [PRG6432Q-16R9-D-T4](#) [PRG5025P-6340-D-T4](#) [PRG6432Q-4322-B-T4](#) [PRG5025P-201-D-T4](#) [PRG6432Q-78R7-D-T4](#) [PRG5025Q-9310-B-T4](#) [PRG6432P-2550-B-T4](#) [PRG3216Q-3240-D-T5](#) [PRG6432Q-61R9-B-T4](#) [PRG5025P-390-D-T4](#) [PRG3216Q-2552-B-T5](#) [PRG5025P-913-D-T4](#) [PRG6432Q-4121-B-T4](#) [PRG6432Q-63R4-D-T4](#) [PRG5025P-3240-D-T4](#) [PRG6432P-2430-B-T4](#) [PRG6432P-1580-D-T4](#) [PRG6432P-95R3-D-T4](#) [PRG6432P-113-D-T4](#) [PRG5025Q-1211-B-T4](#) [PRG5025Q-3162-D-T4](#) [PRG6432Q-11R8-D-T4](#) [PRG6432Q-200-D-T4](#) [PRG3216Q-1211-D-T5](#) [PRG6432Q-7R5-D-T4](#) [PRG5025Q-9310-D-T4](#) [PRG6432P-2550-D-T4](#) [PRG6432P-4991-B-T4](#) [PRG6432P-3831-D-T4](#) [PRG5025Q-2550-B-T4](#) [PRG6432Q-2671-D-T4](#) [PRG5025Q-9090-B-T4](#) [PRG6432P-6190-B-T4](#) [PRG6432Q-2100-B-T4](#) [PRG5025P-3242-B-T4](#) [PRG3216Q-3832-D-T5](#) [PRG5025P-1151-D-T4](#) [PRG5025P-1910-B-T4](#) [PRG5025Q-302-B-T4](#) [PRG6432P-1210-B-T4](#) [PRG6432P-6340-D-T4](#) [PRG5025P-752-B-T4](#) [PRG5025P-5900-B-T4](#) [PRG6432Q-3322-B-T4](#) [PRG6432P-53R6-D-T4](#) [PRG6432Q-1330-B-T4](#) [PRG5025P-1271-D-T4](#) [PRG3216Q-333-D-T5](#) [PRG6432Q-5231-D-T4](#) [PRG6432P-34R8-D-T4](#) [PRG5025P-43R2-D-T4](#) [PRG6432Q-2321-B-T4](#) [PRG5025P-5490-B-T4](#) [PRG5025Q-4121-D-T4](#) [PRG3216Q-2672-D-T5](#) [PRG5025Q-6490-B-T4](#) [PRG5025Q-27R4-D-T4](#) [PRG3216Q-221-D-T5](#) [PRG5025P-4421-B-T4](#) [PRG3216Q-1650-B-T5](#) [PRG6432Q-28R0-D-T4](#) [PRG6432Q-1400-D-T4](#) [PRG6432P-221-D-T4](#) [PRG5025P-1741-D-T4](#) [PRG5025P-3570-B-T4](#) [PRG6432Q-2211-B-T4](#)