





1. ALL DIMENSIONS ARE REFERENCE.
2. MATERIALS:
 - HOUSING - THERMOPLASTIC, BLACK
 - TERMINALS - COPPER ALLOY, GOLD FLASH
3. SUPPLIED ON TAPE AND REEL, SEE SHEET 2.
4. THIS PRODUCT IS RoHS COMPLIANT.



SCHEMATIC

PCB LAYOUT 
COMPONENT SIDE
TOLERANCE ± 0.002 [0.05]




CUSTOMER DRAWING

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.													
						SIZE	WIDTH		MULT		LBS/M		TEMPER						
						FINISH SPEC No.						MATERIAL SPEC No.							
						FIRST USED ON				SCALE 6:1				Switchcraft®					
F	28625	09/28/23	PC	TJK		DATE DRAWN		BY	CHKD		APVD								
E	REDRAWN 28478	02/23/22	PC	TJK		1/13/06		JL	GG 1/13/06		GG 1/13/06								
REV	ECO NUMBER	DATE	BY	APVD	NAME 3.5 MM PHONE JACK SURFACE MOUNT, RoHS						PART No. 35RASMT3BHNTRX						REV F		
REVISIONS					DO NOT SCALE DRAWING														

SolidWorks CAD File

1. DETAIL SIZE REFERENCES: EIA-481


2. SPECIFICATIONS: 32 MM X 12 MM



1. QUANTITY: 700 PCS/REEL

2. MATERIAL: THERMOPLASTIC

3. 8 EMPTY AT START OF REEL



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[35RASMT3BHNTRX](#)