

NOTES:

1. ALL DIMENSIONS ARE REFERENCE.





2. MATERIALS:

HOUSING - THERMOPLASTIC, BLACK

TERMINALS - COPPER ALLOY, GOLD FLASH




3. SUPPLIED ON TAPE AND REEL, SEE SHEET 2.

4. THIS PRODUCT IS RoHS COMPLIANT.



SCHEMATIC

PCB LAYOUT
COMPONENT SIDE
TOLERANCE: ± 0.002 [± 0.05]



CUSTOMER DRAWING

REV	ECO NUMBER	DATE	BY	APVD
D	28625	09-28-23	PC	TJK
C	27337	7-30-14	TO	TJK
B	26972	6-20-12	TO	TJK
A	25182	1-13-06	JL	GG

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES [mm]
- TWO PLACE DECIMALS ± 0.02 [0.5]
- THREE PLACE DECIMALS ± 0.005 [0.13]

DO NOT SCALE DRAWING


SolidWorks CAD File

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.

SIZE	WIDTH	MULT	LBS/M	TEMPER
FINISH SPEC No.	MATERIAL SPEC No.			
FIRST USED ON	SCALE 6:1			
DATE DRAWN 13-Jan-06	BY JL	CHKD GG 1-13-06	APVD GG 1-13-06	
NAME 3.5MM PHONE JACK SURFACE MOUNT, RoHS				PART No. 35RASMT4BHNTRX
SHEET 1 OF 2				REV D

1. DETAIL SIZE REFERENCES: EIA-481


2. SPECIFICATIONS: 32 MM X 12 MM



1. QUANTITY: 700 PCS/REEL

2. MATERIAL: THERMOPLASTIC

3. 8 EMPTY AT START OF REEL



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[35RASMT4BHNTRX](#)