



NOTES:  
1. KNOB AND HARDWARE SHIPPED UNASSEMBLED.

2. MAX PANEL THICKNESS: 0.25 [6.4]

3. MATERIALS:  
FRAME - CRS, ZINC PLATED  
BUSHING & ACTUATOR - COPPER ALLOY, NICKEL PLATED  
SPRINGS - SPECIAL COPPER ALLOY  
TERMINALS - TINNED DIPPED SOLDER LUGS  
INSULATORS - PHENOLIC  
LIFTERS & ROLLERS - THERMOPLASTIC  
SCREWS - CRS, NICKEL PLATED  
HEX NUT - COPPER ALLOY, NICKEL PLATED  
WASHER - CRS, NICKEL PLATED  
KNOB - THERMOPLASTIC, BLACK

4. THIS PRODUCT IS RoHS COMPLIANT

REV	ECO NUMBER	DATE	BY	APVD
A	27887	05-12-17	PC	TJK
REVISIONS				

★ STAR SYMBOL DENOTES CRITICAL DIMENSION	
UNLESS OTHERWISE SPECIFIED	
1. ALL DIMENSIONS IN INCHES -TWO PLACE DECIMALS ±0.01 -THREE PLACE DECIMALS ±0.005 -ANGLES ±1° -ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.	
2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002	
3. REMOVE ALL BURRS	
DO NOT SCALE DRAWING	

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
SIZE		WIDTH		MULT		LBS/M		TEMPER	
FINISH					MATERIAL				
SPEC No.					SPEC No.				
FIRST USED ON				SCALE		<b>Switchcraft</b> <sup>®</sup>			
				2:1					
DATE DRAWN	BY	CHKD		APVD					
May-15-19	PC	PC 05-15-19		TJK 05-15-19					
SHEET						1	OF	1	
NAME					PART No.				REV
LT SERIES LEVER SWITCH 3 POSITION NON-LOCK,RoHS					41324X				A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[41324X](#)