








Ø0.138 [3.51]
✓ Ø0.23x82°(2-PLS)



RECOMMENDED
PANEL CUT-OUT



TYPICAL RETURN LOSS

NOTES:

- ELECTRICAL SPECIFICATIONS:**
IMPEDANCE: 75 Ω
FREQUENCY RANGE: 0-3 GHz
W/S VOLTAGE: 250 Vrms
INSULATION RESISTANCE: 1 GΩ min.
CONTACT RESISTANCE: 30 mΩ max. (Initial)
INSERTION LOSS: -1.0 dB max.
RETURN LOSS: per SMPTE 424 M
- MECHANICAL SPECIFICATIONS:**
OPERATING TEMPERATURE: -40°C to +85°C
LIFE: 500 cycles min.
- MATERIAL:**
FLANGE: ZINC ALLOY
SHELLS, MOUNTING NUT: COPPER ALLOY, NICKEL PLATED
CONTACT: COPPER ALLOY, GOLD PLATED
INSULATORS: THERMOPLASTIC
- FOR FLANGE MOUNTING SCREWS TO BE SHIPPED WITH ASSEMBLY, ADD THE SUFFIX "PKG" TO THE PART NUMBER.
- DIMENSIONS SHOWN FOR REFERENCE ONLY
- THIS PRODUCT IS RoHS COMPLIANT

PART NUMBER	FLANGE FINISH
EHDIN1023X2	NICKEL
EHDIN1023X2B	BLACK

CUSTOMER DRAWING

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ±0.02 - THREE PLACE DECIMALS ±0.005	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.					
						SIZE	WIDTH	MULT	LBS/M	TEMPER	
						FINISH			MATERIAL		
						SPEC No.			SPEC No.		
						FIRST USED ON		SCALE 2:1		Switchcraft®	
						DATE DRAWN	BY	CHKD	APVD		
A	26775	06/09/11	BL	TJK		2/17/11	PNK	PNK	SRC		
						2/17/11		2/17/11	2/17/11		
REV	ECO NUMBER	DATE	BY	APVD		NAME				PART No.	REV
REVISIONS					DO NOT SCALE DRAWING	EH SERIES DIN 1.0/2.3 FEED-THRU, RoHS				EHDIN1023X2	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[EHDIN1023X2](#) [EHDIN1023X2B](#) [EHDIN1023X2BPKG](#) [EHDIN1023X2PKG](#)