








NOTES:

- MATERIALS:
HOUSING - THERMOPLASTIC, BLACK
TERMINALS - COPPER ALLOY, GOLD AND TIN PLATED
SHELL - COPPER ALLOY, NICKEL PLATED
SPRING CLIP - STAINLESS STEEL
REAR SHELL - STEEL, NICKEL PLATED
- ELECTRICAL CHARACTERISTICS:
CONTACT RESISTANCE - 30m OHM MAX
INSULATION RESISTANCE - 1000M OHM MIN @ 500V DC
VOLTAGE AND CURRENT RATING - 1.5A @ 250V AC MIN
DIELECTRIC WITHSTAND VOLTAGE - 750V AC RMS FOR 1MINUTE
- CYCLE LIFE - 1500 MATE/UNMATE CYCLES
- THIS PART IS RoHS COMPLIANT

CUSTOMER DRAWING

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.																							
						SIZE	WIDTH		MULT		LBS/M		TEMPER																
						FINISH						MATERIAL																	
						SPEC No.						SPEC No.																	
						FIRST USED ON				SCALE		Switchcraft®																	
						-				3:1																			
A	28548	10/26/22	PC	TJK																									
REV	ECO NUMBER	DATE	BY	APVD	DATE DRAWN				BY	CHKD		APVD		SHEET 1 OF 1															
					8/24/22				TS	TS		TS																	
REVISIONS					DO NOT SCALE DRAWING					NAME				RIGHT ANGLE DUAL TYPE-A USB 2.0, RoHS				PART No.				RAHPC2UA20				REV		A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[RAHPC2UA20](#)