









CUSTOMER DRAWING

NOTES:

- MATERIALS:
HOUSING - THERMOPLASTIC, BLACK
SHIELD - COPPER ALLOY, NICKEL PLATED
CONTACTS - COPPER ALLOY, GOLD PLATED OVER NICKEL UNDERPLATING
- ELECTRICAL CHARACTERISTICS:
CONTACT RESISTANCE - 20m Ω MAX
INSULATION RESISTANCE - 500M Ω MIN
CURRENT RATING - 1.5AMP MAX @ 120V AC
DIELECTRIC WITHSTAND VOLTAGE - 1000V RMS FOR 1 MINUTE
- OPERATING TEMPERATURE: -40°C TO +85°C
LIFECYCLE - 500 MATE/UNMATE CYCLES
- THIS PART IS RoHS COMPLIANT.

						THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
						SIZE	WIDTH	MULT	LBS/M	TEMPER
						FINISH SPEC No.			MATERIAL SPEC No.	
						FIRST USED ON			SCALE 3:1	
						DATE DRAWN	BY	CHKD TS	APVD TS	
						8/25/22	TS	10/21/22	10/21/22	
						NAME RIGHT ANGLE SHIELDED RJ45, RoHS			PART No. RAHPCRJ45AUE	
						DO NOT SCALE DRAWING			REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[RAHPCRJ45AUE](#)