










NOTES:

- MATERIALS:
HOUSING - THERMOPLASTIC, BLUE
SHELL - STEEL, NICKEL PLATED
TERMINALS - COPPER ALLOY, GOLD PLATED ON CONTACT AREA
TIN PLATED ON SOLDER TAIL
- ELECTRICAL CHARACTERISTICS:
CONTACT RESISTANCE - 30mΩ MAX
INSULATION RESISTANCE - 100MΩ MIN AT 500V DC
CURRENT RATING - 1.5AMP MAX
DIELECTRIC WITHSTANDING VOLTAGE - 500V AC FOR 1 MINUTE
- OPERATING TEMPERATURE: -30°C TO +85°C
- THIS PART IS RoHS COMPLIANT.

CUSTOMER DRAWING

						THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.																			
						UNLESS OTHERWISE SPECIFIED					SIZE		WIDTH		MULT		LBS/M		TEMPER						
						1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.008 [0.20]					FINISH				MATERIAL										
					SPEC No.						SPEC No.														
					FIRST USED ON						SCALE				Switchcraft®										
											5:1														
					DATE DRAWN						BY		CHKD		APVD										
					08/25/22		TS		TS		TS		10/24/22												
A	28548	10/26/22	PC	TJK						NAME		RIGHT ANGLE USB						PART No.		REV					
REV	ECO NUMBER	DATE	BY	APVD								TYPE-A 3.0, RoHS						RAHPCUA30E		A					
REVISIONS					DO NOT SCALE DRAWING																				

SolidWorks CAD File

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[RAHPCUA30E](#)