










NOTES:

1. MATERIALS:

HOUSING - THERMOPLASTIC, BLACK
SHELL - COPPER ALLOY, NICKEL PLATED
TERMINALS - COPPER ALLOY, GOLD PLATED ON CONTACT AREA
TIN PLATED ON SOLDER TAIL

2. ELECTRICAL CHARACTERISTICS:

CONTACT RESISTANCE - 30m OHMS MAX
INSULATION RESISTANCE - 1000M OHMS MIN @ 500V DC
CURRENT RATING - 1.5A MAX
DIELECTRIC WITHSTANDING - 500V AC FOR 1 MINUTE

3. OPERATING TEMPERATURE - 25°C TO +85°C

4. THIS PART IS RoHS COMPLIANT.

CUSTOMER DRAWING

						THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.												
						UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.008 [0.20]	SIZE		WIDTH		MULT		LBS/M		TEMPER			
							FINISH						MATERIAL					
							SPEC No.						SPEC No.					
							FIRST USED ON				SCALE 4:1		Switchcraft®					
							DATE DRAWN	BY	CHKD		APVD							
							8/26/22	MK	MK 10/27/22		MK 10/27/22							
A	28548	10/26/22	PC	TJK			SHEET 1 OF 1											
REV	ECO NUMBER	DATE	BY	APVD			NAME RIGHT ANGLE TYPE-A USB 2.0, RoHS						PART No. RAVPCUA20				REV A	
REVISIONS					DO NOT SCALE DRAWING													

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[RAVPCUA20](#)