













**SN70B11****SN70B12A**

SN70B12B



SN70B14B



**RECOMMENDED
PC BOARD LAYOUT
COMPONENT SIDE**

CUSTOMER DRAWING

NOTES:

1. MAY BE USED WITH PC BOARD THICKNESSES RANGING FROM 0.054 - 0.070.
2. THESE DIMENSIONS VARY DEPENDING ON PCB THICKNESS. DIMENSIONS SHOWN ARE FREE STATE AS SHIPPED.
3. MATERIAL SPECIFICATIONS:
HOUSING - THERMOPLASTIC, BLACK.
SPRINGS - SPECIAL COPPER ALLOY, TINNED.
HARDWARE - COPPER ALLOY, NICKEL PLATED.
4. HARDWARE SHIPPED UNASSEMBLED.
5. THESE PRODUCTS ARE RoHS COMPLIANT.

PART NUMBER	DIM "A"		DIM "B"	
	FREE STATE	WITH 0.062 THICK PCB	FREE STATE	WITH 0.062 THICK PCB
SN70B11	0.720	0.708	0.970	0.958
SN70B12A	0.720	0.708	0.970	0.958
SN70B12B	0.720	0.708	0.970	0.958
SN70B14B	0.720	0.708	0.970	0.958

D	CAD REDRAW ECO #27409	11/17/14	PC	TJK
REV	ECO NUMBER	DATE	BY	APVD
REVISIONS				


UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES

- TWO PLACE DECIMALS ± 0.02

- THREE PLACE DECIMALS ± 0.005

DO NOT SCALE DRAWING

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED AND AUTHORIZED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
SIZE		WIDTH		MULT		LBS/M		TEMPER	
FINISH SPEC No.					MATERIAL SPEC No.				
FIRST USED ON				SCALE 3:1					
DATE DRAWN 11/21/83	BY EB	CHKD AM 01/02/85	APVD RV 01/04/85						
NAME						SHEET 1 OF 1			
PHONE JACK INSULATED BUSHING						PART No. SN70B SERIES		REV D	

Switchcraft®

SHEET 1 OF 1

PART No.	SN70B SERIES
----------	--------------

A

E

C

7

1

E

A

E

C

7

1

E

SolidWorks CAD File

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[SN70B12A](#) [SN70B11](#) [SN70B12B](#) [SN70B14B](#)