






SPECIFICATIONS

MECHANICAL:
SHOCK: MIL-STD 202 METHOD 213B, COND. K.
VIBRATION: MIL-STD 202 METHOD 201
LIFE: 300 INSERTION/WITHDRAWAL CYCLES (MINIMUM)



ELECTRICAL
DIELECTRIC WITHSTANDING VOLTAGE: 1,000 VAC
INSULATION RESISTANCE: 100 MEGOHMS (MIN) AT 77°F
CONTACT RESISTANCE: 5.0 MILLOHMS MAX.
CURRENT RATING: 7.5 AMPS (#20 CONTACT)
6.5 AMPS (7 & 8 PIN #20 CONTACT)
13.0 AMPS (#16 CONTACT)

ENVIRONMENTAL
TEMPERATURE LIMITS: -40°C TO +65°C (NON-OPERATING)
MOISTURE RESISTANCE: MIL-STD 202 METHOD 106F
INSULATION RESISTANCE: MIL-STD 202 METHOD 302, COND. B
THERMAL SHOCK: MIL-STD 202 METHOD 107G
SALT SPRAY: MIL-STD 202 METHOD 101D, COND. B
WATER TIGHTNESS TEST: U.S. COAST GUARD CFR 46 PART 110.20



CONTACT ARRANGEMENTS

SHOWN ARE REAR VIEWS OF MALE INLINE CONNECTORS




CUSTOMER DRAWING

MATERIALS:
IN-LINE CONNECTOR SHELL, CONTACT LOCKING DISK, AND CABLE CLAMP ASSEMBLY: THERMOPLASTIC POLYMER GLASS FIBER, FLAME RETARDANT

REAR BOOT AND CONNECTOR SHELL INTERIOR: THERMOPLASTIC RUBBER

CONTACTS: COPPER BASE ALLOY GOLD-PLATED OVER NICKEL UNDERPLATE



REV	ECO NUMBER	DATE	BY	APVD
B	22232	5-8-98	SG	RB
A	RELEASE TO MFG ECO #21494	11-25-96	MM	FL
REV	ECO NUMBER	DATE	BY	APVD

★ STAR SYMBOL DENOTES CRITICAL DIMENSION				
UNLESS OTHERWISE SPECIFIED				
1. ALL DIMENSIONS IN INCHES				
- TWO PLACE DECIMALS ±0.01				
- THREE PLACE DECIMALS ±0.005				
- ANGLES ±1°				
- ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.				
2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002				
3. REMOVE ALL BURRS				
DO NOT SCALE DRAWING				

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
SIZE	WIDTH	MULT	LBS/M	TEMPER
FINISH		MATERIAL		
SPEC No.		SPEC No.		
FIRST USED ON		SCALE 2:1		
DATE DRAWN	BY	CHKD	APVD	
22-May-95	SG	5-22-95	5-25-95	
NAME				PART No.
MALE CONNECTOR				EN3L_M
				REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[EN3L3FKX](#) [EN3L3M16CKX](#) [EN3L3M16CX](#) [EN3L3M16KX](#) [EN3L3M16X](#) [EN3L3MCKX](#) [EN3L3MCX](#) [EN3L3MKX](#)
[EN3L4FCKX](#) [EN3L4FCX](#) [EN3L4FKX](#) [EN3L4MCKX](#) [EN3L4MCX](#) [EN3L4MKX](#) [EN3L5FCKX](#) [EN3L5FCX](#) [EN3L5FKX](#)
[EN3L5MCKX](#) [EN3L5MCX](#) [EN3L5MKX](#) [EN3L6FCKX](#) [EN3L6FCX](#) [EN3L6FKX](#) [EN3L6MCX](#) [EN3L6MKX](#)
[EN3L7MCKX](#) [EN3L7MCX](#) [EN3L7MKX](#) [EN3L7MX](#) [EN3L8MCKX](#) [EN3L8MCX](#) [EN3L8MKX](#) [EN3L2MX](#)
[EN3L3F16CKX](#) [EN3L3F16CX](#) [EN3L3F16KX](#) [EN3L3F16X](#) [EN3L3FCKX](#) [EN3L3FCX](#) [EN3L15F26CX](#)
[EN3L16M26SLX](#) [EN3L3F16LX](#)