









RECOMMENDED PC BOARD LAYOUT
COMPONENT SIDE



- NOTES:
1. MATERIALS:
BUSHING - ZINC ALLOY, NICKEL PLATED
HOUSING - THERMOPLASTIC, BLACK
CONTACTS & TERMINALS - COPPER ALLOY, TIN PLATED
GROUND TERMINAL - SPECIAL COPPER ALLOY, TIN PLATED
HARDWARE - COPPER ALLOY, NICKEL PLATED
 2. ELECTRICAL SPECIFICATIONS:
CURRENT RATING - 1.5 A
CONTACT RESISTANCE - 0.010 OHM MAX
INSULATION RESISTANCE - 100 MEGA OHMS MIN
DIELECTRIC WITHSTANDING VOLTAGE - 250 VAC
MECHANICAL LIFE - 2000 CYCLES
 3. HARDWARE SHIPPED UNASSEMBLED.
 4. THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.											
						SIZE	WIDTH		MULT		LBS/M		TEMPER				
						FINISH						MATERIAL					
						SPEC No.						SPEC No.					
						FIRST USED ON				SCALE		Switchcraft®					
										3:1							
K	28312	08-25-20	PC	TJK		DATE DRAWN	BY	CHKD		APVD							
J	27650 REDRAWN	2-1-16	TO	TJK		4-26-96	RC	RB		DG							
								4-26-96		12-2-98		SHEET 1 OF 1					
REV	ECO NUMBER	DATE	BY	APVD			NAME TINI Q-G MALE RECEPTOR R.A.P.C. 6 PIN, RoHS						PART No. TRA6M				REV K
REVISIONS					DO NOT SCALE DRAWING												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[TRA6M](#)