







TTP96K3FNX
SCHEMATIC



TTP96K3HNX
SCHEMATIC




TTP96K3NNX
SCHEMATIC



NOTES:


1. MATERIALS:
FRONT PANEL - ALUMINUM, BLACK ANODIZE
CHASSIS, FRAME - STEEL, BLACK EPOXY PAINT
COVER PLATE - STEEL, BLACK EPOXY PAINT
JACK INSERTS - THERMOPLASTIC, BLACK
JACK BUSHING - COPPER ALLOY, NICKEL PLATED
JACK FRAME - STEEL, NICKEL PLATED
2. CABLE TIES NOT SHOWN.
3. MOUNTING SCREWS SHIPPED UNASSEMBLED.
4. THESE PRODUCTS ARE RoHS COMPLIANT.

COVERS
MARKING STRIPS
(THESE PARTS REMOVED FOR CLARITY)



SCALE 1:3

PART NUMBER	TYPE	JACK PART NUMBER
TTP96K3FNX	FULL NORMAL	15JI492X (96 TOP & BOTTOM ROW)
TTP96K3HNX	HALF NORMAL	15JI491X (48 TOP ROW) 15JI492X (48 BOTTOM ROW)
TTP96K3NNX	NON-NORMAL	15JI491X (96 TOP & BOTTOM ROW)



CUSTOMER DRAWING

REV	ECO NUMBER	DATE	BY	APVD
A	27692	05-05-16	PC	TJK
REVISIONS				

★ STAR SYMBOL DENOTES CRITICAL DIMENSION				
UNLESS OTHERWISE SPECIFIED				
1. ALL DIMENSIONS IN INCHES				
- TWO PLACE DECIMALS ±0.01				
- THREE PLACE DECIMALS ±0.005				
- ANGLES ±1°				
- ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.				
2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002				
3. REMOVE ALL BURRS				
DO NOT SCALE DRAWING				

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.					
SIZE	WIDTH		MULT	LBS/M	TEMPER
FINISH			MATERIAL		
SPEC No.			SPEC No.		
FIRST USED ON		SCALE		Switchcraft®	
		1:2			
DATE DRAWN	BY	CHKD	APVD		
03-19-24	PC	PC	TJK		
		03-19-24	03-19-24	SHEET OF	
NAME		2RU, UNWIRED		PART No.	REV
P-KIT ASSEMBLY. RoHS				TTP96K3_X_SERIES	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[TTP96K3HNX](#) [TTP96K3NNX](#)