

2A, 100V-600V Super Fast Surface Mount Rectifier

FEATURES

- Glass passivated junction chip
- Ideal for automated placement
- Low power loss, high efficiency
- Low profile package
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

APPLICATIONS

- Freewheeling application
- Switching mode converters and inverters, computer and telecommunication.

MECHANICAL DATA

- Case: Thin SMA
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: Indicated by cathode band
- Weight: 0.029g (approximately)

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
I_F	2	A
V_{RRM}	100-600	V
I_{FSM}	50	A
T_{JMAX}	150	°C
Package	Thin SMA	
Configuration	Single die	



Thin SMA



ABSOLUTE MAXIMUM RATINGS (T _A = 25°C unless otherwise noted)							
PARAMETER		SYMBOL	ES2BAL	ES2DAL	ES2GAL	ES2JAL	UNIT
Marking code on the device			ES2BAL	ES2DAL	ES2GAL	ES2JAL	
Repetitive peak reverse voltage		V _{RRM}	100	200	400	600	V
Reverse voltage, total rms value		V _{R(RMS)}	70	140	280	420	V
Forward current		I _F	2				A
Surge peak forward current single half sine-wave superimposed on rated load	t = 8.3ms	I _{FSM}	50				A
	t = 1.0ms		120				A
Junction temperature		T _J	-55 to +150				°C
Storage temperature		T _{STG}	-55 to +150				°C

THERMAL PERFORMANCE

PARAMETER	SYMBOL	TYP	UNIT
Junction-to-lead thermal resistance	$R_{\theta JL}$	24	°C/W
Junction-to-ambient thermal resistance	$R_{\theta JA}$	72	°C/W
Junction-to-case thermal resistance	$R_{\theta JC}$	14	°C/W

Thermal Performance Note: Units mounted on PCB (5mm x 5mm Cu pad test board)

ELECTRICAL SPECIFICATIONS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER		CONDITIONS	SYMBOL	TYP	MAX	UNIT
Forward voltage ⁽¹⁾	ES2BAL ES2DAL	I _F = 1.0A, T _J = 25°C	V _F	0.82	-	V
		I _F = 2.0A, T _J = 25°C		0.88	0.95	V
		I _F = 1.0A, T _J = 125°C		0.66	-	V
		I _F = 2.0A, T _J = 125°C		0.74	0.84	V
	ES2GAL	I _F = 1.0A, T _J = 25°C		0.89	-	V
		I _F = 2.0A, T _J = 25°C		0.97	1.30	V
		I _F = 1.0A, T _J = 125°C		0.72	-	V
		I _F = 2.0A, T _J = 125°C		0.81	0.91	V
	ES2JAL	I _F = 1.0A, T _J = 25°C		1.11	-	V
		I _F = 2.0A, T _J = 25°C		1.24	1.70	V
		I _F = 1.0A, T _J = 125°C		0.86	-	V
		I _F = 2.0A, T _J = 125°C		1.01	1.14	V
Reverse current @ rated V _R ⁽²⁾		T _J = 25°C	I _R	-	1	μA
		T _J = 125°C		-	25	μA
Reverse recovery time		I _F = 0.5A, I _R = 1.0A, I _{rr} = 0.25A	t _{rr}	-	35	ns
Junction capacitance	ES2BAL ES2DAL	1MHz, V _R = 4.0V	C _J	28	-	pF
	ES2GAL			27	-	pF
	ES2JAL			21	-	pF

Notes:

(1) Pulse test with $PW = 0.3\text{ms}$

(2) Pulse test with $PW = 30\text{ms}$

ORDERING INFORMATION

ORDERING CODE ⁽¹⁾	PACKAGE	PACKING
ES2xAL M3G	Thin SMA	3,500 / 7" reel
ES2xAL M2G	Thin SMA	14,000 / 13" reel

Notes:

(1) "x" defines voltage from 100V(ES2BAL) to 600V(ES2JAL)

CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.1 Forward Current Derating Curve




Fig.2 Typical Junction Capacitance




Fig.3 Typical Reverse Characteristics




Fig.4 Typical Forward Characteristics




Fig.5 Typical Reverse Characteristics




Fig.6 Typical Forward Characteristics




Fig.7 Typical Reverse Characteristics




Fig.8 Typical Forward Characteristics






Fig.9 Typical Transient Thermal Impedance




PACKAGE OUTLINE DIMENSIONS

Thin SMA



DIM.	Unit (mm)		Unit (inch)	
	Min.	Max.	Min.	Max.
A	0.90	1.00	0.035	0.039
A1	0.00	0.10	0.000	0.004
b	1.25	1.45	0.049	0.057
c	0.10	0.22	0.004	0.009
D	2.50	2.70	0.098	0.106
E	5.05	5.35	0.199	0.211
E1	4.15	4.35	0.163	0.171
L	0.75	1.20	0.030	0.047
L1	0.30	0.60	0.012	0.024

SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
A	2.10	0.083
B	1.40	0.055
C	4.40	0.173
D	3.00	0.118
E	5.80	0.228

MARKING DIAGRAM



P/N = Marking Code
 YW = Date Code
 F = Factory Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taiwan Semiconductor:

[ES2DA M2G](#) [ES2BAL M2G](#) [ES2BALH M2G](#) [ES2BFS M2G](#) [ES2BFSH M2G](#) [ES2DAL M2G](#) [ES2DALH M2G](#)
[ES2GAL M2G](#) [ES2GALH M2G](#) [ES2JAL M2G](#) [ES2JALH M2G](#)