

FP24-2000

Electrical Specifications (@25C)

1. Maximum Power: 48 VA
2. Primary Voltage:
Series: 230V@50/60 Hz
Parallel: 115V@50/60Hz
3. Secondary:
Series: 24.0.0VCT @ 2.0Amps
Parallel: 12.0V @ 4.0Amps

Description:

The FP24-2000 is part of a series which has a long history of reliable service in the field, made from a proven design and constructed with UL recognized materials.

Construction:

Wound on two dual channel nylon bobbin. Materials are UL recognized, Class B (130° C) rated.

Safety:

These products are 100% tested for dielectric strength at 2KVAC, 60Hz between primary and secondary windings and between the primary / secondary windings and the core.

Agency File:

UL: File E53148, UL 506, Class B General Purpose Transformer,
cUL: File E53148, UL 506, Class B General Purpose Transformer, Canadian Use



Dimensions:


A	B	C	D	E	F	G
3.12	2.50	1.375	0.267	0.600	0.669	2.18

Units: In inches

Weight: 21.0 oz



Pin Dimension: .020 x .041 in

Schematic:



RoHS Compliance: As of manufacturing date February 2016, all standard products meet the requirements of 2015/863/EU, known as the RoHS 3 initiative.

*Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetix website for the most current version. For soldering and washing information please see <http://www.triadmagnetics.com/faq.html>



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Triad Magnetics:](#)

[FP24-2000](#)