

## 10A, 35V - 200V Schottky Barrier Rectifier

### FEATURES

- AEC-Q101 qualified available
- Low power loss, high efficiency
- Guard ring for overvoltage protection
- High surge current capability
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

### APPLICATIONS


- Switching mode power supply (SMPS)
- Adapters
- DC to DC converters

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
$I_F$	10	A
$V_{RRM}$	35 - 200	V
$I_{F_{SM}}$	120	A
$T_{J\ MAX}$	150	°C
Package	TO-220AB	
Configuration	Dual dies	




### MECHANICAL DATA

- Case: TO-220AB
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Mounting torque: 0.56 N·m maximum
- Meet JESD 201 class 2 whisker test
- Polarity: As marked
- Weight: 1.88g (approximately)



TO-220AB



ABSOLUTE MAXIMUM RATINGS (T <sub>A</sub> = 25°C unless otherwise noted)										
PARAMETER	SYMBOL	MBR 1035 CT	MBR 1045 CT	MBR 1050 CT	MBR 1060 CT	MBR 1090 CT	MBR 10100 CT	MBR 10150 CT	MBR 10200 CT	UNIT
Marking code on the device		MBR 1035 CT	MBR 1045 CT	MBR 1050 CT	MBR 1060 CT	MBR 1090 CT	MBR 10100 CT	MBR 10150 CT	MBR 10200 CT	
Repetitive peak reverse voltage	$V_{RRM}$	35	45	50	60	90	100	150	200	V
Reverse voltage, total rms value	$V_{R(RMS)}$	24	31	35	42	63	70	105	140	V
Forward current	$I_F$	10								A
Surge peak forward current, 8.3ms single half sine wave superimposed on rated load	$I_{F_{SM}}$	120								A
Peak repetitive reverse surge current <sup>(1)</sup>	$I_{RRM}$	1	0.5							A
Peak repetitive forward current (Rated $V_R$ , Square wave, 20KHz)	$I_{FRM}$	10								A

<b>ABSOLUTE MAXIMUM RATINGS</b> ( $T_A = 25^\circ\text{C}$ unless otherwise noted)											
<b>PARAMETER</b>	<b>SYMBOL</b>	<b>MBR 1035 CT</b>	<b>MBR 1045 CT</b>	<b>MBR 1050 CT</b>	<b>MBR 1060 CT</b>	<b>MBR 1090 CT</b>	<b>MBR 10100 CT</b>	<b>MBR 10150 CT</b>	<b>MBR 10200 CT</b>	<b>UNIT</b>	
Critical rate of rise of off-state voltage	dv/dt	10,000									V/ $\mu\text{s}$
Junction temperature	$T_J$	-55 to +150									°C
Storage temperature	$T_{STG}$	-55 to +150									°C

**Notes:**

1. tp = 2.0 $\mu\text{s}$ , 1.0KHz

<b>THERMAL PERFORMANCE</b>			
<b>PARAMETER</b>	<b>SYMBOL</b>	<b>TYP</b>	<b>UNIT</b>
Junction-to-case thermal resistance	$R_{\Theta JC}$	1.5	°C/W

<b>ELECTRICAL SPECIFICATIONS</b> ( $T_A = 25^\circ\text{C}$ unless otherwise noted)						
<b>PARAMETER</b>		<b>CONDITIONS</b>	<b>SYMBOL</b>	<b>TYP</b>	<b>MAX</b>	<b>UNIT</b>
Forward voltage per diode <sup>(1)</sup>	MBR1035CT	$I_F = 5\text{A}, T_J = 25^\circ\text{C}$	$V_F$	-	0.70	V
	MBR1045CT			-	0.80	V
	MBR1050CT			-	0.85	V
	MBR1060CT			-	0.88	V
	MBR1090CT	$I_F = 10\text{A}, T_J = 25^\circ\text{C}$	$V_F$	-	0.80	V
	MBR10100CT			-	0.90	V
	MBR10150CT			-	0.95	V
	MBR10200CT			-	0.98	V
	MBR1035CT	$I_F = 5\text{A}, T_J = 125^\circ\text{C}$	$V_F$	-	0.57	V
	MBR1045CT			-	0.65	V
	MBR1050CT			-	0.75	V
	MBR1060CT			-	0.78	V
	MBR1090CT	$I_F = 10\text{A}, T_J = 125^\circ\text{C}$	$V_F$	-	0.67	V
	MBR10100CT			-	0.75	V
	MBR10150CT			-	0.85	V
	MBR10200CT			-	0.88	V

<b>ELECTRICAL SPECIFICATIONS</b> ( $T_A = 25^\circ\text{C}$ unless otherwise noted)							
<b>PARAMETER</b>		<b>CONDITIONS</b>	<b>SYMBOL</b>	<b>TYP</b>	<b>MAX</b>	<b>UNIT</b>	
Reverse current @ rated $V_R$ per diode <sup>(2)</sup>	MBR1035CT	$T_J = 25^\circ\text{C}$	$I_R$	-	100	$\mu\text{A}$	
	MBR1045CT			-	15	$\text{mA}$	
	MBR1050CT	$T_J = 125^\circ\text{C}$		-	10	$\text{mA}$	
	MBR1060CT			-	2	$\text{mA}$	
	MBR1090CT			-	5	$\text{mA}$	
	MBR10100CT						
MBR10150CT	MBR10200CT						

**Notes:**

1. Pulse test with PW = 0.3ms
2. Pulse test with PW = 30ms

**ORDERING INFORMATION**

<b>ORDERING CODE<sup>(1)(2)</sup></b>	<b>PACKAGE</b>	<b>PACKING</b>
MBR10xCT	TO-220AB	50 / Tube
MBR10xCTH	TO-220AB	50 / Tube


**Notes:**

1. "x" defines voltage from 35V(MBR1035CT) to 200V(MBR10200CT)
2. "H" means AEC-Q101 qualified


## CHARACTERISTICS CURVES

( $T_A = 25^\circ\text{C}$  unless otherwise noted)


**Fig.1 Forward Current Derating Curve**




**Fig.2 Typical Junction Capacitance**




**Fig.3 Typical Reverse Characteristics**





**Fig.4 Typical Forward Characteristics**



**Fig.5 Maximum Non-Repetitive Forward Surge Current**



**CHARACTERISTICS CURVES** $(T_A = 25^\circ\text{C}$  unless otherwise noted)**Fig.6 Typical Transient Thermal Impedance**

**PACKAGE OUTLINE DIMENSIONS**
**TO-220AB**


DIM.	Unit (mm)		Unit (inch)	
	Min.	Max.	Min.	Max.
A	4.42	4.76	0.174	0.187
A2	2.20	2.80	0.087	0.110
b	0.68	0.94	0.027	0.037
b2	1.14	1.77	0.045	0.070
c	0.35	0.64	0.014	0.025
c2	1.14	1.40	0.045	0.055
D	14.60	16.00	0.575	0.630
D1	2.62	3.44	0.103	0.135
D2	5.84	6.86	0.230	0.270
E	-	10.50	-	0.413
e	2.41	2.67	0.095	0.105
L	13.19	14.79	0.519	0.582
L4	2.80	4.20	0.110	0.165
P	3.54	4.00	0.139	0.157

**MARKING DIAGRAM**


P/N = Marking Code  
 G = Green Compound  
 YWW = Date Code  
 F = Factory Code

## **Notice**

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Taiwan Semiconductor:](#)

[MBR15100CT C0](#)