

F-6X

Electrical Specifications (@25C)

1. Maximum Power: 15.0 VA
2. Primary: 115V 60 Hz
3. Secondary: 2.5VCT @ 6.0 Amps
4. Voltage Regulation: 20 % TYP @ full load to no load
5. Temperature Rise: 35C TYP (45C MAX allowed)

Description:

The F-6X is part of a series which has a long history of reliable service in the field, made from a proven design and constructed with UL recognized materials.

Construction:

Wound on a single channel nylon bobbin. Materials are UL recognized, Class B (130° C) rated.

Safety:

These products are 100% hipot tested with an insulation of 2500V between primary and secondary windings as well as between the primary / secondary windings and the core.

Dimensions:

Units: In inches


A	B	C	D
1.937	3.312	1.750	2.776 ± 0.030

Mounting Hole: 0.276 x 0.118 in

Lead length: 7.0 inches ± 1 inch

Weight: 1.00 lbs




Schematic:



Primary: Black to Black
Secondary: Yellow to Yellow

RoHS Compliance: As of manufacturing date February 2016, all standard products meet the requirements of 2015/863/EU, known as the RoHS 3 initiative.

* Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetics' website for the most current version.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Triad Magnetics:](#)

[F6X](#) [F-6X](#)