

## 20A, 50V - 600V Super Fast Rectifier

### FEATURES

- AEC-Q101 qualified available
- Dual rectifier construction, positive center-tap
- Glass passivated chip junctions
- Superfast recovery time, high voltage
- Low forward voltage, high current capability
- Low thermal resistance
- Low power loss, high efficiency
- UL Recognized File # E-326243
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21


### APPLICATIONS

- DC to DC converter
- Switching mode converters and inverters
- Lighting application
- Snubber
- Freewheeling application


### MECHANICAL DATA

- Case: TO-247AD (TO-3P)
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Mounting torque: 1.13 N·m maximum
- Polarity: As marked
- Weight: 5.60g (approximately)

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
$I_F$	20	A
$V_{RRM}$	50 - 600	V
$I_{FSM}$	180	A
$T_{J\ MAX}$	150	°C
Package	TO-247AD (TO-3P)	
Configuration	Dual dies	



TO-247AD (TO-3P)



ABSOLUTE MAXIMUM RATINGS ( $T_A = 25^\circ\text{C}$ unless otherwise noted)										
PARAMETER	SYMBOL	SF 2001 PT	SF 2002 PT	SF 2003 PT	SF 2004 PT	SF 2005 PT	SF 2006 PT	SF 2007 PT	SF 2008 PT	UNIT
Marking code on the device		SF 2001 PT	SF 2002 PT	SF 2003 PT	SF 2004 PT	SF 2005 PT	SF 2006 PT	SF 2007 PT	SF 2008 PT	
Repetitive peak reverse voltage	$V_{RRM}$	50	100	150	200	300	400	500	600	V
Reverse voltage, total rms value	$V_{R(RMS)}$	35	70	105	140	210	280	350	420	V
Forward current	$I_F$	20								A
Surge peak forward current 8.3ms single half sine wave superimposed on rated load	$I_{FSM}$	180								A
Junction temperature	$T_J$	-55 to +150								°C
Storage temperature	$T_{STG}$	-55 to +150								°C

**THERMAL PERFORMANCE**

PARAMETER	SYMBOL	TYP	UNIT
Junction-to-case thermal resistance	$R_{\theta JC}$	2.5	°C/W

**ELECTRICAL SPECIFICATIONS** ( $T_A = 25^\circ\text{C}$  unless otherwise noted)

PARAMETER		CONDITIONS	SYMBOL	TYP	MAX	UNIT
Forward voltage per diode <sup>(1)</sup>	SF2001PT	I <sub>F</sub> = 10A, T <sub>J</sub> = 25°C	V <sub>F</sub>	-	0.975	V
	SF2002PT					
	SF2003PT					
	SF2004PT					
	SF2005PT					
	SF2006PT					
	SF2007PT	I <sub>F</sub> = 20A, T <sub>J</sub> = 25°C		-	1.300	V
	SF2008PT			-	1.700	V
	SF2001PT			-	1.100	V
	SF2002PT					
SF2003PT						
SF2004PT						
SF2005PT						
SF2006PT						
SF2007PT	-	1.500	V			
SF2008PT				-	1.900	V
Reverse current @ rated V <sub>R</sub> per diode <sup>(2)</sup>		T <sub>J</sub> = 25°C	I <sub>R</sub>	-	10	μA
		T <sub>J</sub> = 125°C		-	400	μA
Junction capacitance per diode		1MHz, V <sub>R</sub> = 4.0V	C <sub>J</sub>	175	-	pF
Reverse recovery time		I <sub>F</sub> = 0.5A, I <sub>R</sub> = 1.0A I <sub>rr</sub> = 0.25A	t <sub>rr</sub>	-	35	ns

**Notes:**

- Pulse test with  $PW = 0.3\text{ms}$
- Pulse test with  $PW = 30\text{ms}$

**ORDERING INFORMATION**

ORDERING CODE <sup>(1)(2)</sup>	PACKAGE	PACKING
SF20xPT	TO-247AD (TO-3P)	30 / Tube
SF20xPTH	TO-247AD (TO-3P)	30 / Tube


**Notes:**

- "x" defines voltage from 50V(SF2001PT) to 600V(SF2008PT)
- "H" means AEC-Q101 qualified


## CHARACTERISTICS CURVES

( $T_A = 25^\circ\text{C}$  unless otherwise noted)


**Fig.1 Forward Current Derating Curve**




**Fig.2 Typical Junction Capacitance**




**Fig.3 Typical Reverse Characteristics**



**Fig.4 Typical Forward Characteristics**




**Fig.5 Maximum Non-Repetitive Forward Surge Current**




## CHARACTERISTICS CURVES

( $T_A = 25^\circ\text{C}$  unless otherwise noted)

**Fig.6 Reverse Recovery Time Characteristic and Test Circuit Diagram**



## PACKAGE OUTLINE DIMENSIONS



DIM	Unit (mm)		Unit (inch)	
	Min	Max	Min	Max
A	4.90	5.16	0.193	0.203
A2	2.70	3.00	0.106	0.118
b	1.12	1.22	0.044	0.048
b1	1.93	2.18	0.076	0.086
b2	2.97	3.22	0.117	0.127
c	0.51	0.76	0.020	0.030
D	20.80	21.30	0.819	0.839
D1	5.70	6.20	0.224	0.244
E	15.90	16.40	0.626	0.646
E1	7.90	8.20	0.311	0.323
e	5.20	5.70	0.205	0.224
H	2.90	3.40	0.114	0.134
L	19.70	20.20	0.776	0.795
L4	3.50	4.10	0.138	0.161
P	-	4.30	-	0.169

## MARKING DIAGRAM



P/N = Marking Code  
G = Green Compound  
YWW = Date Code  
F = Factory Code

## **Notice**

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taiwan Semiconductor:

[SF2004PT](#) [SF2005PT](#) [SF2006PT](#) [SF2008PT](#) [SF2004PTH](#) [SF2005PTH](#) [SF2006PTH](#) [SF2008PTH](#)