

5A, 20V - 200V Surface Mount Schottky Barrier Rectifier

FEATURES

- Low power loss, high efficiency
- Ideal for automated placement
- Guard ring for over-voltage protection
- High surge current capability
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21

APPLICATIONS

- Switching mode power supply (SMPS)
- Adapters
- Lighting application
- Converter

MECHANICAL DATA

- Case: DO-214AB (SMC)
- Molding compound meets UL 94V-0 flammability rating
- Part no. with suffix "H" means AEC-Q101 qualified
- Packing code with suffix "G" means green compound (halogen-free)
- Moisture sensitivity level: level 1, per J-STD-020
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: As marked
- Weight: 0.21 g (approximately)

| KEY PARAMETERS | | |
|----------------|----------------|------|
| PARAMETER | VALUE | UNIT |
| $I_{F(AV)}$ | 5 | A |
| V_{RRM} | 20 - 200 | V |
| I_{FSM} | 120 | A |
| $T_{J\ MAX}$ | 150 | °C |
| Package | DO-214AB (SMC) | |
| Configuration | Single die | |



DO-214AB (SMC)

ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

| PARAMETER | SYMBOL | SK 52C | SK 53C | SK 54C | SK 55C | SK 56C | SK 59C | SK 510C | SK 515C | SK 520C | UNIT |
|-----------------------------------------------------------------------------------------------|--------------|--------------|--------|--------|--------|--------|--------|---------|---------|---------|------|
| Marking code on the device | | SK 52C | SK 53C | SK 54C | SK 55C | SK 56C | SK 59C | SK 510C | SK 515C | SK 520C | |
| Repetitive peak reverse voltage | V_{RRM} | 20 | 30 | 40 | 50 | 60 | 90 | 100 | 150 | 200 | V |
| Reverse voltage, total rms value | $V_{R(RMS)}$ | 14 | 21 | 28 | 35 | 42 | 63 | 70 | 105 | 140 | V |
| Maximum DC blocking voltage | V_{DC} | 20 | 30 | 40 | 50 | 60 | 90 | 100 | 150 | 200 | V |
| Forward current | $I_{F(AV)}$ | 5 | | | | | | | | | A |
| Surge peak forward current, 8.3 ms single half sine-wave superimposed on rated load per diode | I_{FSM} | 120 | | | | | | | | | A |
| Critical rate of rise of off-state voltage | dV/dt | 10,000 | | | | | | | | | V/μs |
| Junction temperature | T_J | - 55 to +150 | | | | | | | | | °C |
| Storage temperature | T_{STG} | - 55 to +150 | | | | | | | | | °C |

THERMAL PERFORMANCE

| PARAMETER | SYMBOL | TYP | UNIT |
|--------------------------------------------------|-----------------|-----|------|
| Junction-to-lead thermal resistance per diode | $R_{\theta JL}$ | 17 | °C/W |
| Junction-to-ambient thermal resistance per diode | $R_{\theta JA}$ | 50 | °C/W |

ELECTRICAL SPECIFICATIONS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

| PARAMETER | | CONDITIONS | SYMBOL | TYP. | MAX. | UNIT |
|--------------------------------------------------------|-------------------------------------------|-------------------------------------------|--------|------|------|------|
| Forward voltage per diode ⁽¹⁾ | SK52C SK53C SK54C | $I_F = 5\text{A}, T_J = 25^\circ\text{C}$ | V_F | - | 0.55 | V |
| | SK55C SK56C | | | - | 0.75 | V |
| | SK59C SK510C | | | - | 0.85 | V |
| | SK515C SK520C | | | - | 0.95 | V |
| Reverse current @ rated V_R per diode ⁽²⁾ | SK52C SK53C SK54C SK55C SK56C | $T_J = 25^\circ\text{C}$ | I_R | - | 0.5 | mA |
| | SK59C SK510C SK515C SK520C | | | - | 0.3 | mA |
| Reverse current @ rated V_R per diode ⁽²⁾ | SK52C SK53C SK54C | $T_J = 100^\circ\text{C}$ | I_R | - | 20 | mA |
| | SK55C SK56C | | | - | 10 | mA |
| | SK59C SK510C SK515C SK520C | | | - | - | mA |
| Reverse current @ rated V_R per diode ⁽²⁾ | SK52C SK53C SK54C | $T_J = 125^\circ\text{C}$ | I_R | - | - | mA |
| | SK55C SK56C | | | - | - | mA |
| | SK59C SK510C SK515C SK520C | | | - | 5 | mA |

Notes:

- Pulse test with $PW=0.3\text{ ms}$
- Pulse test with $PW=30\text{ ms}$

ORDERING INFORMATION

| PART NO. | PART NO. SUFFIX | PACKING CODE | PACKING CODE SUFFIX | PACKAGE | PACKING |
|----------------------|-----------------|--------------|---------------------|------------|--------------------------|
| SK5xxC (Note 1,2) | H | R7 | G | SMC | 850 / 7" Plastic reel |
| | | R6 | | SMC | 3,000 / 13" Paper reel |
| | | M6 | | SMC | 3,000 / 13" Plastic reel |
| | | V7 | | Matrix SMC | 850 / 7" Plastic reel |
| | | V6 | | Matrix SMC | 3,000 / 13" Plastic reel |

Note :

1. "xx" defines voltage from 20V (SK52C) to 200V (SK520C)
2. Only V6 and V7 are all green compound (halogen free)

EXAMPLE

| EXAMPLE P/N | PART NO. | PART NO. SUFFIX | PACKING CODE | PACKING CODE SUFFIX | DESCRIPTION |
|-------------|----------|-----------------|--------------|---------------------|--------------------------------------|
| SK52CHR7G | SK52C | H | R7 | G | AEC-Q101 qualified Green compound |

CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.1 Forward Current Derating Curve




Fig.2 Typical Junction Capacitance




Fig.3 Typical Reverse Characteristics





Fig.4 Typical Forward Characteristics



CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.5 Maximum Non-repetitive Forward Surge Current






Fig.6 Typical Transient Thermal Characteristics




PACKAGE OUTLINE DIMENSIONS

DO-214AB (SMC)



| DIM. | Unit (mm) | | Unit (inch) | |
|------|-----------|------|-------------|-------|
| | Min. | Max. | Min. | Max. |
| A | 2.90 | 3.20 | 0.114 | 0.126 |
| B | 6.60 | 7.11 | 0.260 | 0.280 |
| C | 5.59 | 6.22 | 0.220 | 0.245 |
| D | 2.00 | 2.62 | 0.079 | 0.103 |
| E | 1.00 | 1.60 | 0.039 | 0.063 |
| F | 7.75 | 8.13 | 0.305 | 0.320 |
| G | 0.10 | 0.20 | 0.004 | 0.008 |
| H | 0.15 | 0.31 | 0.006 | 0.012 |

SUGGESTED PAD LAYOUT



| Symbol | Unit (mm) | Unit (inch) |
|--------|-----------|-------------|
| A | 3.30 | 0.130 |
| B | 2.50 | 0.098 |
| C | 6.80 | 0.268 |
| D | 4.40 | 0.173 |
| E | 9.40 | 0.370 |

MARKING DIAGRAM

Matrix SMC

SMC



P/N =Marking Code
G =Green Compound
YW =Date Code
F =Factory Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taiwan Semiconductor:

[SK53C](#) [SK520C R7](#) [SK510C R6](#) [SK55C R6G](#) [SK515C R6](#) [SK510C R6G](#) [SK54C R6](#) [SK515C R6G](#) [SK510C R7](#)
[SK59C R6G](#) [SK55C R6](#) [SK515C R7](#) [SK56C R7](#) [SK53C R6](#) [SK56C R6](#) [SK53C V7G](#) [SK52C V7G](#) [SK53C V6G](#)
[SK52C V6G](#) [SK510C V6G](#) [SK510C V7G](#) [SK59C V6G](#) [SK59C V7G](#) [SK56C V6G](#) [SK56C V7G](#) [SK55C V6G](#) [SK55C](#)
[V7G](#) [SK520C V6G](#) [SK520C V7G](#) [SK54C V6G](#) [SK54C V7G](#) [SK515C V6G](#) [SK515C V7G](#) [SK520C](#) [SK510CH](#)
[SK515CH](#) [SK520CH](#) [SK53CH](#) [SK54CH](#) [SK56CH](#)