

8A, 20V - 150V Schottky Barrier Surface Mount Rectifier

FEATURES

- AEC-Q101 qualified
- Low power loss, high efficiency
- Ideal for automated placement
- Guard ring for overvoltage protection
- High surge current capability
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21


APPLICATIONS

- Low voltage, high freq. inverter
- DC/DC converter
- Freewheeling diodes
- Reverse battery protection
- Car lighting


MECHANICAL DATA

- Case: TO-263AB (D²PAK)
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: As marked
- Weight: 1.37g (approximately)

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
I_F	8	A
V_{RRM}	20 - 150	V
I_{FSM}	150	A
$T_{J\ MAX}$	125, 150	°C
Package	TO-263AB (D ² PAK)	
Configuration	Single die	



TO-263AB (D²PAK)



ABSOLUTE MAXIMUM RATINGS (T _A = 25°C unless otherwise noted)										
PARAMETER	SYMBOL	SRAS	SRAS	SRAS	SRAS	SRAS	SRAS	SRAS	SRAS	UNIT
		820 H	830 H	840 H	850 H	860 H	890 H	8100 H	8150 H	
Marking code on the device		SRAS 820	SRAS 830	SRAS 840	SRAS 850	SRAS 860	SRAS 890	SRAS 8100	SRAS 8150	
Repetitive peak reverse voltage	V _{RRM}	20	30	40	50	60	90	100	150	V
Reverse voltage, total rms value	V _{R(RMS)}	14	21	28	35	42	63	70	105	V
Forward current	I _F	8								A
Surge peak forward current, 8.3ms single half sine wave superimposed on rated load	I _{FSM}	150								A
Critical rate of rise of off-state voltage	dv/dt	10,000								V/μs
Junction temperature	T _J	-55 to +125			-55 to +150					°C
Storage temperature	T _{STG}	-55 to +150								°C

THERMAL PERFORMANCE

PARAMETER	SYMBOL	TYP	UNIT
Junction-to-case thermal resistance	$R_{\theta JC}$	3	°C/W

ELECTRICAL SPECIFICATIONS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER	CONDITIONS	SYMBOL	TYP	MAX	UNIT
Forward voltage ⁽¹⁾	SRAS820H SRAS830H SRAS840H	V_F	-	0.55	V
	SRAS850H SRAS860H		-	0.70	V
	SRAS890H SRAS8100H SRAS8150H		-	0.95	V
Reverse current @ rated V_R ⁽²⁾	SRAS820H SRAS830H SRAS840H SRAS850H SRAS860H SRAS890H SRAS8100H SRAS8150H	I_R	-	100	μA
	SRAS820H SRAS830H SRAS840H SRAS850H SRAS860H		-	5	mA
	SRAS890H SRAS8100H SRAS8150H		-	-	mA
	SRAS820H SRAS830H SRAS840H SRAS850H SRAS860H		-	-	mA
	SRAS890H SRAS8100H SRAS8150H		-	5	mA
			-	-	mA

Notes:

- Pulse test with $PW = 0.3\text{ms}$
- Pulse test with $PW = 30\text{ms}$

ORDERING INFORMATION

ORDERING CODE ⁽¹⁾	PACKAGE	PACKING
SRAS8xH	TO-263AB (D ² PAK)	800 / Tape & Reel

Notes:

- "X" defines voltage from 20V(SRAS820H) to 150V(SRAS8150H)

CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.1 Forward Current Derating Curve




Fig.2 Typical Junction Capacitance




Fig.3 Typical Reverse Characteristics




Fig.4 Typical Forward Characteristics






Fig.5 Maximum Non-Repetitive Forward Surge Current




CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.6 Typical Transient Thermal Impedance




PACKAGE OUTLINE DIMENSIONS

TO-263AB (D²PAK)


DIM.	Unit (mm)		Unit (inch)	
	Min.	Max.	Min.	Max.
A	4.44	4.70	0.175	0.185
A2	2.03	2.79	0.080	0.110
b	0.68	0.94	0.027	0.037
c	0.36	0.53	0.014	0.021
c2	1.14	1.40	0.045	0.055
D	8.25	9.25	0.325	0.364
E	-	10.50	-	0.413
e	2.41	2.67	0.095	0.105
H	14.60	15.88	0.575	0.625
L	2.29	2.79	0.090	0.110
L3	1.14	1.40	0.045	0.055

SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
A	10.80	0.425
B	8.30	0.327
C	1.27	0.050
D	4.05	0.159
E	15.95	0.628
F	2.54	0.100
G	9.775	0.385

MARKING DIAGRAM



P/N = Marking Code

G = Green Compound

YWW = Date Code

F = Factory Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Taiwan Semiconductor:](#)

[SRAS8100H](#) [SRAS8150H](#) [SRAS840H](#) [SRAS860H](#)