

Isobar 2-Outlet Surge Protector, Direct Plug-In, 1410 Joules, Diagnostic LEDs, Metal Housing

MODEL NUMBER: ISOBLOK2-0



Highlights

- 2 NEMA 5-15R surge-protected outlets
- 1410-joule surge protection rating
- Durable metal housing mounts out of sight behind furniture
- LEDs indicate power, protection and line fault status
- Plugs directly into outlet with no power cord

Package Includes

- ISOBLOK2-0 Isobar 2-Outlet Surge Protector, Metal Housing
- Mounting hardware
- Owner's manual

Description

Premium protection for your expensive computer and audio/visual equipment, the ISOBLOK2-0 Isobar® 2-Outlet Surge Protector features a surge protection rating of 1410 joules to defend your sensitive electronics against even the strongest surges and spikes. In fact, Tripp Lite will repair or replace any connected equipment damaged by surges, including direct lightning strikes, up to \$10,000 for life (valid in the U.S., Canada and Puerto Rico only).

The ISOBLOK2-0 features two NEMA 5-15R outlets, perfect for your flat-panel HDTV and Blu-ray™ player or a pair of computer peripherals, such as a printer and a router. This unit's unique protection system prevents disruptive line noise from causing A/V distortion, computer lock-ups, data errors and similar problems. Large toroidal chokes, ferrite rod-core inductors, HF/VHF capacitors and multiple layers of metal oxide varistors remove EMI/RFI interference and prevent system crashes, reboots and performance problems.

Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the ISOBLOK2-0 protects all three, covering two protection modes: full normal mode (H-N) and common mode (N-G/H-G).

Diagnostic LEDs show power, protection and line fault status at a glance. The ISOBLOK2-0 plugs directly into any standard NEMA 5-15R outlet. Optional mounting hardware is included for permanent attachment to the outlet cover, which will prevent the ISOBLOK2-0 from coming loose accidentally.

Features

1410-Joule Surge Protection for Your Home Theater Electronics and Computer Peripherals

- Protects your components against surges and spikes
- Full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- 2 NEMA 5-15R surge-protected outlets

Premium Safety Features

- Diagnostic LEDs confirm power, protection and ground status at a glance
- Conforms to current UL 1449 3rd Edition safety standards



Fits Effortlessly Into Your Setup

- Plugs directly into standard NEMA 5-15R outlet with no power cord
- Optional hardware included for permanent mounting to outlet cover
- Metal housing designed for long life

Backed by Tripp Lite's Ultimate Lifetime Insurance

- \$10,000 Ultimate Lifetime Insurance covers any connected components damaged by power surge (U.S., Canada and Puerto Rico only)

Specifications

| OUTPUT | |
|-------------------------------------|--|
| Frequency Compatibility | 50 / 60 Hz |
| Output Receptacles | (2) 5-15R |
| Output (Watts) | 1800 |
| Circuit Breaker (amps) | 15 |
| Right-Angle Outlets | No |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 120V (110-125V) |
| Input Connection Type | NEMA 5-15P input plug |
| Input Cord Length (ft.) | 0 |
| Input Cord Length (m) | 0.00 |
| Input Cord Length Details | Direct Plug-In |
| Voltage Compatibility (VAC) | 120 |
| Right-Angle Plug | No |
| USER INTERFACE, ALERTS & CONTROLS | |
| Diagnostic LED Details | PROTECTION PRESENT (green), LINE FAULT (red) and LINE OK (green) |
| SURGE / NOISE SUPPRESSION | |
| AC Suppression Joule Rating | 1410 |
| AC Suppression Response Time | NM = 0 ns. CM = <1 ns |
| Protection Modes | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression |
| Clamping Voltage (RMS) | 140 |
| AC Suppression Surge Current Rating | 48,000 amps |
| AC Suppression Components Used | Metal oxide varistors, toroidal balanced chokes and VHF capacitors |



| | |
|--|---|
| Safe Thermal Fusing | Prevents unsafe conditions during extreme extended overvoltages and catastrophic occurrences |
| UL1449 Let Through Rating | 330V |
| EMI / RFI Filtering | 40-80 dB |
| Immunity | Conforms to IEE 587 / ANSI C62.41 |
| DATALINE SURGE SUPPRESSION | |
| Telephone/DSL Protection | No |
| Cable (Coax) Protection | No |
| Network (Ethernet) Protection | No |
| PHYSICAL | |
| Unit Dimensions (hwd / in.) | 4 x 2.5 x 2.5 |
| Unit Dimensions (hwd / cm) | 10.2 x 6.4 x 6.4 |
| Material of Construction | Metal |
| Housing Color | Light Gray |
| Receptacle Color | Black |
| Form Factors Supported | Direct plug-in format with retaining bracket supports wall mounting directly to a standard AC wall socket |
| CERTIFICATIONS | |
| UL1449 3rd Edition (AC Suppression) | Tested to UL1449 3rd Edition by ETL |
| cUL / CSA (Canada) | Approved for Canada by ETL |
| Approvals | Exceeds IEEE 587 category A&B specifications |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$10,000 Ultimate Lifetime Insurance |

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[ISOBLOK2-0](#)