



# 10A, 20V - 150V Dual Common Cathode Schottky Rectifiers

## FEATURES

- Low power loss, high efficiency
- Ideal for automated placement
- Guardring for overvoltage protection
- High surge current capability
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21



**TO-263AB (D<sup>2</sup>PAK)**



## MECHANICAL DATA

**Case:** TO-263AB (D<sup>2</sup>PAK)  
**Molding compound,** UL flammability classification rating 94V-0  
**Moisture sensitivity level:** level 1, per J-STD-020  
**Part No. with suffix "H"** means AEC-Q101 qualified  
**Packing code with suffix "G"** means green compound (halogen-free)  
**Terminal:** Matte tin plated leads, solderable per JESD22-B102  
**Meet JESD 201 class 2 whisker test**  
**Polarity:** As marked  
**Weight:** 1.37 g (approximately)

| MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS (T <sub>A</sub> =25°C unless otherwise noted)                             |                    |              |             |             |             |              |             |              |              |      |
|--------------------------------------------------------------------------------------------------------------------------|--------------------|--------------|-------------|-------------|-------------|--------------|-------------|--------------|--------------|------|
| PARAMETER                                                                                                                | SYMBOL             | SRS<br>1020  | SRS<br>1030 | SRS<br>1040 | SRS<br>1050 | SRS<br>1060  | SRS<br>1090 | SRS<br>10100 | SRS<br>10150 | UNIT |
| Maximum repetitive peak reverse voltage                                                                                  | V <sub>RRM</sub>   | 20           | 30          | 40          | 50          | 60           | 90          | 100          | 150          | V    |
| Maximum RMS voltage                                                                                                      | V <sub>RMS</sub>   | 14           | 21          | 28          | 35          | 42           | 63          | 70           | 105          | V    |
| Maximum DC blocking voltage                                                                                              | V <sub>DC</sub>    | 20           | 30          | 40          | 50          | 60           | 90          | 100          | 150          | V    |
| Maximum average forward rectified current                                                                                | I <sub>F(AV)</sub> | 10           |             |             |             |              |             |              |              | A    |
| Peak forward surge current, 8.3 ms single half sine-wave superimposed on rated load                                      | I <sub>FSM</sub>   | 120          |             |             |             |              |             |              |              | A    |
| Maximum instantaneous forward voltage (Note 1)<br>I <sub>F</sub> = 5 A                                                   | V <sub>F</sub>     | 0.55         |             |             | 0.70        |              | 0.90        |              | 1.00         | V    |
| Maximum reverse current @ rated V <sub>R</sub><br>T <sub>J</sub> =25°C<br>T <sub>J</sub> =100°C<br>T <sub>J</sub> =125°C | I <sub>R</sub>     | 0.5          |             |             |             |              | 0.1         |              |              | mA   |
|                                                                                                                          |                    | 15           |             |             | 10          |              | -           |              |              |      |
|                                                                                                                          |                    | -            |             |             |             |              | 5           |              |              |      |
| Typical thermal resistance                                                                                               | R <sub>θJC</sub>   | 2            |             |             |             |              |             |              |              | °C/W |
| Operating junction temperature range                                                                                     | T <sub>J</sub>     | - 55 to +125 |             |             |             | - 55 to +150 |             |              |              | °C   |
| Storage temperature range                                                                                                | T <sub>STG</sub>   | - 55 to +150 |             |             |             |              |             |              |              | °C   |

Note 1: Pulse test with PW=300μs, 1% duty cycle

| ORDERING INFORMATION |                 |              |                         |                    |                        |
|----------------------|-----------------|--------------|-------------------------|--------------------|------------------------|
| PART NO.             | PART NO. SUFFIX | PACKING CODE | PACKING CODE SUFFIX (*) | PACKAGE            | PACKING                |
| SRS10xx<br>(Note 1)  | H               | RN           | G                       | D <sup>2</sup> PAK | 800 / 13" Paper reel   |
|                      |                 | MN           |                         |                    | 800 / 13" Plastic reel |

Note 1: "xx" defines voltage from 20V (SRS1020) to 150V (SRS10150)

\*: Optional available

| EXAMPLE            |          |                 |              |                     |                                      |
|--------------------|----------|-----------------|--------------|---------------------|--------------------------------------|
| PREFERRED PART NO. | PART NO. | PART NO. SUFFIX | PACKING CODE | PACKING CODE SUFFIX | DESCRIPTION                          |
| SRS1060HRNG        | SRS1060  | H               | RN           | G                   | AEC-Q101 qualified<br>Green compound |

## RATINGS AND CHARACTERISTICS CURVES

(T<sub>A</sub>=25°C unless otherwise noted)

FIG.1 FORWARD CURRENT DERATING CURVE




FIG. 2 MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG. 3 TYPICAL FORWARD CHARACTERISTICS




FIG. 4 TYPICAL REVERSE CHARACTERISTICS




FIG. 5 TYPICAL JUNCTION CAPACITANCE






FIG. 6 TYPICAL TRANSIENT THERMAL IMPEDANCE




# PACKAGE OUTLINE DIMENSIONS

## TO-263AB (D<sup>2</sup>PAK)




| DIM. | Unit (mm) |       | Unit (inch) |       |
|------|-----------|-------|-------------|-------|
|      | Min       | Max   | Min         | Max   |
| A    | -         | 10.5  | -           | 0.413 |
| B    | 14.60     | 15.88 | 0.575       | 0.625 |
| C    | 2.41      | 2.67  | 0.095       | 0.105 |
| D    | 0.68      | 0.94  | 0.027       | 0.037 |
| E    | 2.29      | 2.79  | 0.090       | 0.110 |
| F    | 4.44      | 4.70  | 0.175       | 0.185 |
| G    | 1.14      | 1.40  | 0.045       | 0.055 |
| H    | 1.14      | 1.40  | 0.045       | 0.055 |
| I    | 8.25      | 9.25  | 0.325       | 0.364 |
| J    | 0.36      | 0.53  | 0.014       | 0.021 |
| K    | 2.03      | 2.79  | 0.080       | 0.110 |

# SUGGESTED PAD LAYOUT



| Symbol | Unit (mm) | Unit (inch) |
|--------|-----------|-------------|
| A      | 10.8      | 0.425       |
| B      | 8.3       | 0.327       |
| C      | 1.1       | 0.043       |
| D      | 3.5       | 0.138       |
| E      | 16.9      | 0.665       |
| F      | 9.5       | 0.374       |
| G      | 2.5       | 0.098       |

# MARKING DIAGRAM



P/N = Specific Device Code  
G = Green Compound  
YWW = Date Code  
F = Factory Code

### Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Taiwan Semiconductor:

[SRS10100](#) [SRS10150](#) [SRS1030](#) [SRS1040](#) [SRS1050](#) [SRS1060](#) [SRS1090](#) [SRS102](#) [SRS1090 RN](#) [SRS1030 RN](#)  
[SRS10150 RN](#) [SRS10100 RN](#) [SRS1050 RN](#) [SRS1040 RN](#) [SRS10200 RN](#) [SRS1060 RN](#) [SRS1050 RNG](#)  
[SRS1020HRN](#) [SRS1060HRNG](#) [SRS1020 RNG](#) [SRS10100HRNG](#) [SRS1050HRN](#) [SRS1090HRNG](#) [SRS10150HRNG](#)  
[SRS1090 RNG](#) [SRS1060 RNG](#) [SRS10100HRN](#) [SRS10100 RNG](#) [SRS1040HRN](#) [SRS1050HRNG](#) [SRS1020HRNG](#)  
[SRS1030HRNG](#) [SRS1030 RNG](#) [SRS1020 RN](#) [SRS10150HRN](#) [SRS10150 RNG](#) [SRS1040HRNG](#) [SRS1030HRN](#)  
[SRS1040 RNG](#) [SRS1060HRN](#) [SRS1090HRN](#)