

1A, 20V - 150V Surface Mount Schottky Barrier Rectifiers

FEATURES

- Low power loss, high efficiency
- Ideal for automated placement
- Guardring for overvoltage protection
- High surge current capability
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21 definition



DO-214AC (SMA)





MECHANICAL DATA

Case: DO-214AC (SMA)

Molding compound, UL flammability classification rating 94V-0

Moisture sensitivity level: level 1, per J-STD-020 Part No. with suffix "H" means AEC-Q101 qualified

Packing code with suffix "G" means green compound (halogen-free) **Terminal:** Matte tin plated leads, solderable per JESD22-B102

Meet JESD 201 class 2 whisker test **Polarity:** Indicated by cathode band **Weight:** 0.066 g (approximately)

| MAXIMUM RATINGS AND ELECTRICAL CHARA | 1 | | | | | | | | | ı |
|---|--------------------|---------------------------|------------|----|-------|----------|------|----------|--------------|------|
| PARAMETER | SYMBOL | SS | SS | SS | SS | SS | SS | SS | SS | UNIT |
| I AKAWETEK | STWIDOL | 12 | 13 | 14 | 15 | 16 | 19 | 110 | 115 | |
| Maximum repetitive peak reverse voltage | V_{RRM} | 20 | 30 | 40 | 50 | 60 | 90 | 100 | 150 | V |
| Maximum RMS voltage | V_{RMS} | 14 | 21 | 28 | 35 | 42 | 63 | 70 | 105 | V |
| Maximum DC blocking voltage | V_{DC} | 20 | 30 | 40 | 50 | 60 | 90 | 100 | 150 | V |
| Maximum average forward rectified current | I _{F(AV)} | 1 | | | | | Α | | | |
| Peak forward surge current, 8.3 ms single half sine-wave superimposed on rated load | I _{FSM} | 40 | | | | | А | | | |
| Maximum instantaneous forward voltage (Note 1) @ 1 A, T _J =25°C @ 1 A, T _J =100°C | V _F | | 0.5 0.4 | | | 75 65 | _ | .8 .7 | 0.95 0.85 | V |
| T _J =25°C | | 0.2 0.1 | | | | | | | | |
| Maximum reverse current @ rated V _R T _J =100°C | I _R | | 6 | | 5 - 2 | | - | | | mA |
| T _J =125°C | | | - | | | | 2 | | | |
| Voltage rate of change (Rated V _R) | dV/dt | 10000 | | | | | V/µs | | | |
| Typical thormal registance | $R_{	heta JL}$ | 28 | | | | | °C/W | | | |
| Typical thermal resistance | $R_{\theta JA}$ | 88 | | | | | C/VV | | | |
| Operating junction temperature range | TJ | - 55 to +125 - 55 to +150 | | | | °C | | | | |
| Storage temperature range | T _{STG} | - 55 to +150 | | | | | °C | | | |

Note 1: Pulse test with PW=300µs, 1% duty cycle




| ORDERING INFORMATION | | | | | |
|----------------------|--------------------|--------------|------------------------|------------|--------------------------|
| PART NO. | PART NO. SUFFIX | PACKING CODE | PACKING CODE SUFFIX | PACKAGE | PACKING |
| | | R3 | G | SMA | 1,800 / 7" Plastic reel |
| | | R2 | | SMA | 7,500 / 13" Paper reel |
| H SS1xx | ш | M2 | | SMA | 7,500 / 13" Plastic reel |
| | 11 | F3 | | Folded SMA | 1,800 / 7" Plastic reel |
| (Note 1) | (Note 1) | F2 | | Folded SMA | 7,500 / 13" Paper reel |
| | | F4 | | Folded SMA | 7,500 / 13" Plastic reel |
| | N/A | E3 | | Clip SMA | 1,800 / 7" Plastic reel |
| | | E2 | | Clip SMA | 7,500 / 13" Plastic reel |


Note 1: "xx" defines voltage from 20V (SS12) to 150V (SS115)


| EXAMPLE | | | | | |
|-----------------------|----------|--------------------|--------------|------------------------|--------------------------------------|
| PREFERRED PART NO. | PART NO. | PART NO. SUFFIX | PACKING CODE | PACKING CODE SUFFIX | DESCRIPTION |
| SS16HR3G | SS16 | Н | R3 | G | AEC-Q101 qualified Green compound |

RATINGS AND CHARACTERISTICS CURVES

(T_A=25°C unless otherwise noted)















FIG. 5 TYPICAL JUNCTION CAPACITANCE





PACKAGE OUTLINE DIMENSIONS


DO-214AC (SMA)



| | | Н |
|----------|----------|---|
| | | |
| D | | |
| D | | |
| | F G | |
| | E | |
| | I F | |

| DIM. | Unit | (mm) | Unit (inch) | | |
|--------|------|------|-------------|-------|--|
| DIIVI. | Min | Max | Min | Max | |
| Α | 1.27 | 1.58 | 0.050 | 0.062 | |
| В | 4.06 | 4.60 | 0.160 | 0.181 | |
| С | 2.29 | 2.83 | 0.090 | 0.111 | |
| D | 1.99 | 2.50 | 0.078 | 0.098 | |
| Е | 0.90 | 1.41 | 0.035 | 0.056 | |
| F | 4.95 | 5.33 | 0.195 | 0.210 | |
| G | 0.10 | 0.20 | 0.004 | 0.008 | |
| Н | 0.15 | 0.31 | 0.006 | 0.012 | |

SUGGESTED PAD LAYOUT



| Symbol | Unit (mm) | Unit (inch) |
|--------|-----------|-------------|
| Α | 1.68 | 0.066 |
| В | 1.52 | 0.060 |
| С | 3.93 | 0.155 |
| D | 2.41 | 0.095 |
| E | 5.45 | 0.215 |

MARKING DIAGRAM



P/N = Specific Device Code G = Green Compound

YW = Date Code F = Factory Code



Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Document Number: DS_D1411020 Version: P15

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taiwan Semiconductor:

SS13 SS15 SS14 SS16 SS12 SS19 SS13M RS SS14 F3 SS14M RS SS16 F3 SS110 SS115 SS16M RS SS19HF2 SS14 R3G SS16 R3 SS19 F3 SS13HR3G SS12 F2 SS115 F2G SS110HR3 SS16HF2G SS115HR3 SS115HR2 SS16HR2 SS19HF2G SS12 R3G SS15 F2G SS16 F2 SS16 R2G SS14HF2G SS14 E3 SS110HR2G SS115HR3G SS12 R3 SS15HF3G SS110HF3G SS12 R2G SS115HF2G SS16 E3G SS15HF2G SS110 F2 SS13HF3G SS15HF3 SS15 E3G SS19 F3G SS115HF2 SS16 F3G SS15HR3 SS15 R2G SS115 F3 SS19 R2 SS115HF3 SS15 E3G SS19HR3G SS115 F3G SS15 E2G SS13HF2G SS19HF3 SS15HR3G SS13 E3G SS15HR2 SS110HR2 SS15HR2G SS19HR2G SS19HR2 SS14 F2G SS14HF2 SS110 F3G SS110HF3 SS16HR3 SS13 F2 SS16 R2 SS19HR2G SS14 E3G SS16HF3 SS13HF3 SS12 E2G SS12HF2 SS115 E3 SS19 E3 SS14 E2G SS15 R3G SS110 R2 SS110 F3 SS16 E2 SS13 F3 SS115 F2 SS110 E2G SS115 E3G SS115 R2 SS13 E2 SS13HF2 SS14HF3G SS19 E3G SS15 E2G SS14HF3 SS12 R2 SS16HR2G