

Surface Mount Schottky Barrier Rectifier

FEATURES

- Ideal for automated placement
- Compact package size, profile <0.85mm
- High surge current capability
- Low power loss, high efficiency
- AEC-Q101 qualified and Halogen free only
- Moisture sensitivity level: level 1, per J-STD-020
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21 definition


**HALOGEN
FREE**

TYPICAL APPLICATIONS

The devices are designed for high frequency miniature switched mode power supplies such as adapters, lighting and on-board DC/DC converters.

MECHANICAL DATA

Case: SOD-123HE

Molding compound, UL flammability classification rating 94V-0

Base P/N with suffix "G" on packing code - green compound (halogen-free)

Base P/N with prefix "H" on packing code - AEC-Q101 qualified

Terminal: Matte tin plated leads, solderable per JESD22-B102

with prefix "H" on packing code meet JESD 201 class 2 whisker test

Polarity: Indicated by cathode band

Weight: 21mg (approximately)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS ($T_A=25^\circ\text{C}$ unless otherwise noted)								
PARAMETER	SYMBOL	SS12 LS	SS13 LS	SS14 LS	SS16 LS	SS110 LS	SS115 LS	UNIT
Marking code		12LS	13LS	14LS	16LS	10LS	A5LS	
Maximum repetitive peak reverse voltage	V_{RRM}	20	30	40	60	100	150	V
Maximum RMS voltage	V_{RMS}	14	21	28	42	70	105	V
Maximum DC blocking voltage	V_{DC}	20	30	40	60	100	150	V
Maximum average forward rectified current	$I_{F(AV)}$	1						A
Peak forward surge current, 8.3 ms single half sine-wave superimposed on rated load	I_{FSM}	30						A
Maximum instantaneous forward voltage @ 0.5 A (Note 1) @ 1.0 A	V_F	-	-	0.51	0.58	0.70	0.75	V
		0.45	0.50	0.55	0.70	0.80	0.90	
Maximum reverse current @ rated VR $T_J=25^\circ\text{C}$ $T_J=125^\circ\text{C}$	I_R	0.4				0.05		mA
		-				0.5		
Typical junction capacitance (Note 2)	C_J	80						pF
Typical thermal resistance	$R_{\theta JC}$ $R_{\theta JA}$	25 70						°C/W
Operating junction temperature range	T_J	- 55 to +125		- 55 to +150				
Storage temperature range	T_{STG}	- 55 to +150						°C

Note 1: Pulse test with PW=300μs, 1% duty cycle

Note 2: Measured at 1 MHz and Applied Reverse Voltage of 4.0V DC

ORDERING INFORMATION

PART NO.	AEC-Q101 QUALIFIED	PACKING CODE	GREEN COMPOUND CODE	PACKAGE	PACKING
SS1xxLS (Note 1, 2)	Prefix "H"	RV	Suffix "G"	SOD-123HE	3,000 / 7" Reel
		RQ		SOD-123HE	10,000 / 13" Reel

Note 1: "xx" defines voltage from 20V (SS12LS) to 150V (SS115LS)

Note 2: Whole series with AEC-Q101 qualified and green compound (halogen-free)

EXAMPLE

PREFERRED P/N	PART NO.	AEC-Q101 QUALIFIED	PACKING CODE	GREEN COMPOUND CODE	DESCRIPTION
SS115LSHRVG	SS115LS	H	RV	G	AEC-Q101 qualified Green compound

RATINGS AND CHARACTERISTICS CURVES

(TA=25°C unless otherwise noted)








FIG.1- MAXIMUM FORWARD CURRENT DERATING CURVE

FIG. 2- TYPICAL REVERSE CHARACTERISTICS

FIG. 3- MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT

FIG. 4- TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS



FIG. 5- TYPICAL JUNCTION CAPACITANCE


PACKAGE OUTLINE DIMENSIONS
SOD-123HE


DIM.	Unit (mm)		Unit (inch)	
	Min	Max	Min	Max
A	1.65	1.95	0.065	0.077
B	2.60	3.00	0.102	0.118
C	0.85	1.15	0.033	0.045
D	0.75	0.85	0.030	0.033
E	0.10	0.20	0.004	0.008
F	0.55	0.75	0.022	0.030
G	0.35	0.55	0.014	0.022
H	1.90	2.30	0.075	0.091
I	1.35	1.55	0.053	0.061
J	0.95	1.25	0.037	0.049
K	3.50	3.90	0.138	0.154
L	0.35	0.55	0.014	0.022

SUGGESTED PAD LAYOUT


Symbol	Unit (mm)	Unit (inch)
A	1.40	0.055
B	2.40	0.094
C	0.70	0.028
D	0.90	0.035
E	1.40	0.055

MARKING DIAGRAM


P/N = Marking Code
 YW = Date Code
 F = Factory Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taiwan Semiconductor:

[SS12LS RQG](#) [SS16LS RQG](#) [SS14LSHRVG](#) [SS12LSHRQG](#) [SS16LS RVG](#) [SS12LS RVG](#) [SS16LSHRVG](#) [SS14LS RQG](#) [SS110LSHRVG](#) [SS14LS RVG](#) [SS115LSHRVG](#) [SS110LS RVG](#) [SS16LSHRQG](#) [SS13LSHRVG](#) [SS13LS RQG](#) [SS13LSHRQG](#) [SS14LSHRQG](#) [SS110LSHRQG](#) [SS12LSHRVG](#) [SS115LSHRQG](#) [SS115LS RQG](#) [SS13LS RVG](#) [SS110LS RQG](#) [SS115LS RVG](#) [SS110LS](#) [SS115LS](#) [SS12LS](#) [SS13LS](#) [SS14LS](#) [SS16LS](#) [SS110LSH](#) [SS115LSH](#) [SS12LSH](#) [SS13LSH](#) [SS14LSH](#) [SS16LSH](#)