

VGA High-Resolution RGB Coaxial Cable with Audio (HD15 and 3.5mm M/M), 10 ft. (3.05 m)

MODEL NUMBER: **P504-010**



Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- VW-1 and CM Rated Jacketing
- 3.5mm Stereo Plugs

Package Includes

- 10-ft. SVGA/VGA Monitor Cable
 HD15M to HD15M w/Built-in
 Audio connectors

Features

- Extend both Video and Audio signals
- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Constructed from mini-coax (RGB) and paired video wire construction for superior signal quality.
- HD15 male to HD15 male molded connectors
- Computer side Audio Pigtail: 8in Display side Audio Pigtail: 24in
- VW-1 and CM Rated Jacketing

Specifications

OVERVIEW	
UPC Code	037332135797
Product Type	Passive
Technology	Coax; VGA/SVGA; Stereo Audio
PHYSICAL	
Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.1
Shipping Dimensions (hwd / cm)	25.40 x 20.32 x 1.27
Shipping Dimensions (hwd / in.)	10.00 x 8.00 x 0.50



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (kg)	0.36
Shipping Weight (lbs.)	0.80
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side A - Connector 2	3.5MM (MALE)
Side B - Connector 1	HD15 (MALE)
Side B - Connector 2	3.5MM (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P504-010](#)