

High Resolution VGA Monitor Y Splitter Cable (HD15 M to 2x HD15 F), 6 ft. (1.83 m)

MODEL NUMBER: **P516-006-HR**



Highlights

- Splits the SXGA/UXGA signal providing simultaneous display of the same image on two monitors
- HD15 Male splits to 2 HD15 Female, 6-ft

System Requirements

A computer with a VGA port, and two monitors with VGA ports

Package Includes

- 6-ft. SXGA/UXGA Hi-Res Splitter Cable, HD15M to 2 x HD1F

Features

- HD15 Male to 2 x HD15 Female w/Hex Nuts
- RGB cable construction supports resolutions up to 1600 x 1200
- Molded, double-shielded construction for maximum EMI/RFI protection
- Two monitors display the same image from one PC
- Inexpensive solution for presentations

Specifications

OVERVIEW	
UPC Code	037332187789
Product Type	Passive
Technology	VGA/SVGA
PHYSICAL	
Color	Black
Cable Length (ft.)	6
Cable Length (m)	0.3
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.14

Shipping Weight (lbs.)	0.30
CONNECTIONS	
Ports	2
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	(2) HD15 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite](#):

[P516-006-HR](#)