


11.5kW 3-Phase Metered PDU, 208-240V Outlets (36 C13 & 9 C19), L22-20P 360-415V Input, 6 ft. (1.83 m) Cord, 0U Vertical, TAA

MODEL NUMBER: PDU3XMV6L2220



Features

- 11.5 kW Metered Power Distribution Unit (PDU)
- 360-415V input with NEMA L22-20P 3-phase input connection
- 208-240V output with 36 C13 & 9 C19 single phase output receptacles
- 0U / 1778mm vertical rackmount installation supported
- Outlets are arranged in 3 metered 15 outlet load banks
- Included cord retention brackets keep vital network equipment plugged in and continuously powered
- Toolless mounting supported in button-mount compatible racks, plus nut-and-bolt mounting brackets for other mounting applications (set of 2 9mm buttons pre-installed, 2 9mm and 4 6mm spare buttons included)
- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases

Highlights

- Metered 11.5kW 3-Phase 360-415V input / 208-240V output PDU
- Set of 3 digital meters report output load level per phase in amps
- 70in / 1778mm 0U vertical format, toolless button-mount installation
- NEMA L22-20P 3 phase input; 6ft 1.8m line cord
- 36 C13 & 9 C19 single phase outlets; Included cord retention brackets
- TAA Compliant

Package Includes

- Metered rackmount PDU with pre-installed mounting buttons
- Cord retention brackets
- Spare installation buttons (2 9mm / 4 6mm)
- Rack mounting brackets
- Owner's manual

Specifications

| OVERVIEW | |
|--------------------------------|----------------------------------|
| UPC Code | 037332171955 |
| PDU Type | Metered |
| INPUT | |
| PDU Input Voltage | 360-415V |
| Recommended Electrical Service | Three-phase 20A 360-415V service |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--|---|
| Maximum Input Amps | 16 |
| PDU Plug Type | NEMA L22-20P |
| Input Phase | 3-Phase |
| Input Cord Length (ft.) | 6 |
| Input Cord Length (m) | 1.83 |
| OUTPUT | |
| Output Capacity Details | 11.5kW (415/240V), 11kW (400/230V), 10.6kW (380/220V), 10kW (360/208V) total capacity; 16A max per output phase (L1-L2, L2-L3, L3-L1); 16A max per C19 outlet; 12A max per C13 outlet |
| Frequency Compatibility | 50 / 60 Hz |
| Output Receptacles | (36) C13; (9) C19 |
| Output Nominal Voltage | 208-240V |
| Overload Protection | n/a |
| USER INTERFACE, ALERTS & CONTROLS | |
| Reported Load Segments | Supports local monitoring of current for each output phase (16A balanced max per output load banks L1, L2 & L3); Outlets are color-coded and labeled for easy phase and load bank identification; L1-N feeds black outlets; L2-N feeds dark-gray outlets; L3-N feeds light-gray outlets |
| Front Panel LCD Display | Set of 3 digital meters report per-phase output current in amps (L1, L2, L3) |
| PHYSICAL | |
| Form Factors Supported | Vertical rackmount installation supported with included mounting brackets; supports toolless mounting in button-mount compatible racks |
| Material of Construction | Metal |
| PDU Form Factor | Vertical (0U) |
| Shipping Dimensions (hwd / cm) | 12.95 x 17.02 x 193.04 |
| Shipping Dimensions (hwd / in.) | 5.10 x 6.70 x 76.00 |
| Shipping Weight (kg) | 5.22 |
| Shipping Weight (lbs.) | 11.50 |
| Unit Dimensions (hwd / cm) | 177.8 x 5.6 x 4.9 |
| Unit Dimensions (hwd / in.) | 70 x 2.2 x 1.93 |
| Unit Weight (kg) | 3.63 |
| Unit Weight (lbs.) | 8.00 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 0C ~ 40C (32F ~ 104F) |
| Storage Temperature Range | -30°C to +50°C (-22°F to +122°F) |
| Relative Humidity | 5 to 95% non-condensing |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| STANDARDS & COMPLIANCE | |
|-------------------------------------|---|
| Certifications | Tested to UL (USA), CSA (Canada), NOM (Mexico), Class A (Emissions), RoHS (Hazardous Substances); TAA Compliant |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 2-year limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PDU3XMV6L2220](#)