

PowerAlert Console Launcher To address Java Runtime Environment (JRE) issues with respect to the SNMPWEBCARD web interface, Tripp Lite recommends using the [PowerAlert Console Launcher](#) . This application enables local access of the SNMPWEBCARD using a self-contained, compatible JRE version. The Console Launcher can be downloaded for free from the Technical Support page or from the Management Solutions / Utilities page.

1.9kW Single-Phase Switched PDU, 120V Outlets (8 5-15/20R), L5-20P/5-20P Adapter, 12ft Cord, 1U Rack-Mount, TAA

MODEL NUMBER: PDUMH20NET2



Description

Tripp Lite single phase Switched PDU / Power Distribution Unit offers advanced network control and monitoring with the ability to turn on, turn off, recycle or lock-out power to each individual receptacle, monitor site electrical conditions and remotely monitor output power consumption. PowerAlert interface supports remote control and custom notification of user-specified conditions via email, PowerAlert Console Launcher, SNMP, Telnet or SSH interface. Individually switched outlets can be controlled in real-time to remotely reboot unresponsive network hardware, or be custom programmed for user-defined power-up and power-down sequences to ensure proper startup of interdependent IT systems and prevent inrush-related overloads as network equipment is first energized. Unused PDU outlets can be electronically locked off to prevent the connection of unauthorized hardware. PDU output current consumption in amps is continuously displayed locally via visual meter and remotely via the network interface to warn of potential overloads before critical IT mains or branch breakers trip.

Features

- 20A 120V Switched Power Distribution Unit / PDU with built-in network interface (Agency derated to 16A continuous)
- Attached NEMA L5-20P input with NEMA 5-20P plug adapter, 12 ft. / 3.6m input cable
- 1U horizontal rackmount form factor
- 8 switched NEMA 5-15/20R outlets

Highlights

- Switched 20A 120V PDU, 1U horizontal rackmount format
- Reports voltage, frequency & load level via ethernet interface
- Visual current meter, Reversible housing
- NEMA L5-20P input with 5-20P plug adapter, 12 ft. / 3.6m line cord
- 8 NEMA 5-15/20R switched outlets with cord retention brackets
- Temperature, humidity and contact closure monitoring options
- Trade Agreements Act / TAA Compliant for GSA Schedule purchases

Package Includes

- PDU with attached L5-20P input power cord and 5-20P plug adapter
- Rackmount installation brackets and wire retention plates
- Configuration cable
- User manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Supports power-on, power-off or reboot of each outlet on a real-time or programmable basis
- Enables reboot of locked equipment, custom power-on/power-off sequences, load-shedding of optional loads and disabling unused outlets
- Network interface provides PDU control and data regarding input voltage and total output load level in amps
- Digital display continuously reports total output load level in amps
- Supports user-specified alarm notification thresholds
- In-rack environmental reporting with optional ENVIROSENSE temperature / humidity sensor and rack access notification with up to 4 optional SRSWITCH door sensors
- DHCP/Manual configuration support
- 10/100 Mbps auto-sensing
- Real-time clock backup maintains the time of day and date even if the PDU is unpowered
- Tiered access privileges allow an administrator and a guest to login simultaneously
- Alert notifications via email or SNMP traps offer immediate event notification
- Firmware upgrade ability supports future product enhancements
- Supports HTTP, HTTPS, PowerAlert Network Management System, SMTP, SNMPv1, SNMPv2, SNMPv3, Telnet, SSH, FTP, DHCP, BOOTP, NTP protocols
- Fully compatible with FREE PowerAlert Network Management System / NMS Software
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Mounting ears are reversible for front or rear facing rackmount installation
- Included cord retention brackets
- Trade Agreements Act / TAA Compliant for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332174703
PDU Type	Switched
INPUT	
Recommended Electrical Service	20A 120V
Maximum Input Amps	20
Maximum Input Amps Details	Agency de-rated to 16A continuous
PDU Plug Type	NEMA 5-20P; NEMA L5-20P
Input Phase	Single-Phase
Input Cord Length (ft.)	12



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Input Cord Length (m)	3.66
OUTPUT	
Output Capacity Details	2.03kW (127V), 1.92kW (120V), 1.6kW (100V) / 20A total capacity (Agency de-rated to 16A); 16A max per outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) 5-15/20R
Output Nominal Voltage	100; 120; 127
Overload Protection	n/a
Customized Load Management Receptacles	8 individually switched output receptacles
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Digital display reports total PDU output current in amps
Front Panel LEDs	8 LEDs display power on-off status for each output receptacle
Switches	n/a
PHYSICAL	
Form Factors Supported	1U rackmount
Material of Construction	Metal
Minimum Required Rack Depth (cm)	23.62
Minimum Required Rack Depth (inches)	9.3
PDU Form Factor	Horizontal (1U)
Shipping Dimensions (hwd / cm)	29.72 x 5.08 x 51.31
Shipping Dimensions (hwd / in.)	11.70 x 2.00 x 20.20
Shipping Weight (kg)	3.54
Shipping Weight (lbs.)	7.80
Unit Dimensions (hwd / cm)	4.44 x 44.4 x 10.8
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 4.25
Unit Weight (kg)	2.72
Unit Weight (lbs.)	5.99
ENVIRONMENTAL	
Storage Temperature Range	5 to 122F (-15 to 50C)
Relative Humidity	5 to 95% (non-condensing)
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

COMMUNICATIONS	
SNMP Compatibility	Yes, pre-installed SNMPWEBCARD provides remote monitoring via PowerAlert Console Launcher, Telnet, SSH, and SNMP management systems. Remote management gives user ability to turn connected loads on or off individually
SPECIAL FEATURES	
TVSS Grounding	Rear panel grounding lug
STANDARDS & COMPLIANCE	
Certifications	Tested to UL 60950-1 (USA), CSA/CSA-C22.2 NO. 60950-1 (Canada), Class A (Emissions), NOM (Mexico), RoHS compliant, TAA Compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PDUMH20NET2](#)