




**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

## 8-Outlet Vertical Power Strip, 6 ft. (1.83 m) Cord, 5-15P, 48 in.

MODEL NUMBER: **PS480806**



The PS480806 power strip provides horizontal or vertical power distribution for rackmount, raceway and workbench applications in a convenient 48-in. mountable housing.

### Features

#### Multi-Outlet Power Distribution

#### Vertical or Horizontal Moun

#### Premium Safety Features

#### Heavy-Duty Housing

### Highlights

- Ideal for applications needing multiple convenience outlets for powering a variety of electronic equipment
- 48-in. mountable housing with 8 standard NEMA 5-15R outlets and a 6-ft. power cord
- Lighted, covered On/Off switch and 15-amp circuit breaker
- Sturdy construction and heavy-duty, all-metal housing

### Package Includes

- PS480806
- Mounting hardware
- Instruction manual

## Specifications

OVERVIEW	
UPC Code	037332186645
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Input Cord Length (m)	1.83
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(8) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(8) Yes
Right-Angle Outlets	No
Outlet Spacing	5.67
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off
<b>PHYSICAL</b>	
Color	Silver
Antimicrobial Coating	No
Power Cord Color	Black
Form Factors Supported	Supports vertical or horizontal mounting in rack enclosures, raceways and a variety of other applications
Housing Color	Silver
Included Mounting Accessories	Includes mounting clips
Integrated Keyhole Mounting Slots	No
Material of Construction	Aluminum
Outlets Measurement (Center to Center)	5.67
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	6.10 x 8.89 x 131.83
Shipping Dimensions (hwd / in.)	2.40 x 3.50 x 51.90
Shipping Weight (kg)	1.50
Shipping Weight (lbs.)	3.30
Unit Dimensions (hwd / cm)	3.18 x 3.81 x 121.92
Unit Dimensions (hwd / in.)	1.25 x 1.5 x 48
Unit Weight (kg)	1.16
Unit Weight (lbs.)	2.56



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

STANDARDS & COMPLIANCE	
Canada	cUL
UL1363 (Power Tap)	UL1363
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PS480806](#)