

8A, 200V - 1000V Standard Surface Mount Rectifier

FEATURES

- Low power loss, high efficiency
- Ideal for automated placement
- Wettable flank
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

APPLICATIONS

- DC to DC converter
- Switching mode converters and inverters
- General purpose


MECHANICAL DATA

- Case: TO-277A (SMPC4.6U)
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 1 whisker test
- Polarity: Indicated by cathode band
- Weight: 0.104g (approximately)

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
I_F	8	A
V_{RRM}	200 - 1000	V
I_{FSM}	230	A
$T_{J\ MAX}$	150	°C
Package	TO-277A (SMPC4.6U)	
Configuration	Single die	



TO-277A (SMPC4.6U)



ABSOLUTE MAXIMUM RATINGS (T _A = 25°C unless otherwise noted)								
PARAMETER		SYMBOL	TUAS8D	TUAS8G	TUAS8J	TUAS8K	TUAS8M	UNIT
Marking code on the device			AS8D	AS8G	AS8J	AS8K	AS8M	
Repetitive peak reverse voltage		V _{RRM}	200	400	600	800	1000	V
Reverse voltage, total rms value		V _{R(RMS)}	140	280	420	560	700	V
Forward current		I _F	8					A
Surge peak forward current single half sine-wave superimposed on rated load	t = 8.3ms	I _{FSM}	230					A
	t = 1.0ms		580					A
Junction temperature		T _J	-55 to +150					°C
Storage temperature		T _{STG}	-55 to +150					°C

THERMAL PERFORMANCE

PARAMETER	SYMBOL	TYP	UNIT
Junction-to-lead thermal resistance	$R_{\theta JL}$	4	°C/W
Junction-to-ambient thermal resistance	$R_{\theta JA}$	38	°C/W
Junction-to-case thermal resistance	$R_{\theta JC}$	8	°C/W

Thermal Performance Note: Units mounted on PCB (16mm x 16mm Cu pad test board)

ELECTRICAL SPECIFICATIONS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER		CONDITIONS	SYMBOL	TYP	MAX	UNIT
Forward voltage ⁽¹⁾	TUAS8D TUAS8G TUAS8J	I _F = 4A, T _J = 25°C	V _F	0.90	-	V
		I _F = 8A, T _J = 25°C		0.96	1.10	V
		I _F = 4A, T _J = 125°C		0.78	-	V
		I _F = 8A, T _J = 125°C		0.87	1.01	V
	TUAS8K TUAS8M	I _F = 4A, T _J = 25°C		0.90	-	V
		I _F = 8A, T _J = 25°C		0.97	1.10	V
		I _F = 4A, T _J = 125°C		0.78	-	V
		I _F = 8A, T _J = 125°C		0.87	1.01	V
Reverse current @ rated V _R ⁽²⁾		T _J = 25°C	I _R	-	5	μA
		T _J = 125°C		-	60	μA
Junction capacitance	TUAS8D TUAS8G TUAS8J	1MHz, V _R = 4.0V	C _J	62	-	pF
	TUAS8K TUAS8M			54	-	pF

Notes:

- Pulse test with $PW = 0.3\text{ms}$
- Pulse test with $PW = 30\text{ms}$

ORDERING INFORMATION

ORDERING CODE ⁽¹⁾	PACKAGE	PACKING
TUAS8x	TO-277A (SMPC4.6U)	6,000 / Tape & Reel

Notes:

- "x" defines voltage from 200V(TUAS8D) to 1000V(TUAS8M)

CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.1 Forward Current Derating Curve




Fig.2 Typical Junction Capacitance




Fig.3 Typical Reverse Characteristics




Fig.4 Typical Forward Characteristics




Fig.5 Typical Reverse Characteristics






Fig.6 Typical Forward Characteristics



CHARACTERISTICS CURVES


($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.7 Typical Transient Thermal Impedance



PACKAGE OUTLINE DIMENSIONS


TO-277A (SMPC4.6U)



DIM.	Unit (mm)		Unit (inch)	
	Min.	Max.	Min.	Max.
A	1.00	1.20	0.039	0.047
b	1.05	1.35	0.041	0.053
b2	1.90	2.20	0.075	0.087
b4	0.75 (NOM.)		0.030 (NOM.)	
c	0.15	0.40	0.006	0.016
D	4.45	4.75	0.175	0.187
D1	4.25	4.35	0.167	0.171
D2	3.40	3.70	0.134	0.146
E	6.35	6.65	0.250	0.262
E1	6.05	6.15	0.238	0.242
E2	4.40	4.80	0.173	0.189
E3	3.94 (NOM.)		0.155 (NOM.)	
e	2.08 (NOM.)		0.082 (NOM.)	
L	0.94	1.24	0.037	0.049
L1	0.05	0.35	0.002	0.014
M	0.65	1.15	0.026	0.045
N	0.25	0.75	0.010	0.030

Package body size D1 and E1 do not include mold flash
 Mold flash shall not exceed 0.1mm per side

SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
A	4.95	0.195
B	4.95	0.195
C	1.60	0.063
D	1.42	0.056
E	6.95	0.274
F	1.04	0.041

MARKING DIAGRAM



P/N = Marking Code
 YW = Date Code
 F = Factory Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taiwan Semiconductor:

[TUAS8D M3G](#) [TUAS8G M3G](#) [TUAS8J M3G](#) [TUAS8K M3G](#) [TUAS8M M3G](#) [TUAS8D](#) [TUAS8G](#) [TUAS8J](#) [TUAS8K](#)
[TUAS8M](#)