



Features

- ✧ For surface mounted application
- ✧ Easy pick and place
- ✧ Metal to silicon rectifier, majority carrier conduction
- ✧ Low power loss, high efficiency
- ✧ High current capability, low VF
- ✧ High surge current capability
- ✧ Plastic material used carriers Underwriters Laboratory Classification 94V-0
- ✧ Epitaxial construction
- ✧ High temperature soldering: 260°C/10 seconds at terminals
- ✧ Green compound with suffix "G" on packing code & prefix "G" on datecode.

Mechanical Data

- ✧ Case: Molded plastic
- ✧ Terminals: Pure tin plated, lead free.
- ✧ Polarity: Indicated by cathode band
- ✧ Packaging: 12mm tape per EIA STD RS-481
- ✧ Weight: 0.093 grams

Maximum Ratings and Electrical Characteristics

Rating at 25 °C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.


For capacitive load, derate current by 20%

Type Number	Symbol	SS 22	SS 23	SS 24	SS 25	SS 26	SS 29	SS 210	SS 215	Units
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	20	30	40	50	60	90	100	150	V
Maximum RMS Voltage	V _{RMS}	14	21	28	35	42	63	70	105	V
Maximum DC Blocking Voltage	V _{DC}	20	30	40	50	60	90	100	150	V
Maximum Average Forward Rectified Current at T _L (See Fig. 1)	I _{F(AV)}	2								A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	I _{FSM}	50								A
Maximum Instantaneous Forward Voltage (Note 1) IF= 2 A @ 25 °C @ 100 °C	V _F	0.5 0.4			0.70 0.65		0.85 0.70		0.95 0.80	V
Maximum DC Reverse Current at Rated DC Blocking Voltage @ T _A =25 °C @ T _A =100 °C @ T _A =125 °C	I _R	0.4					0.1			mA
		10			5		-			mA
		-					5.0			mA
Typical Junction Capecitance (Note 2)	C _j	130								pF
Typical Thermal Resistance	R _{θJL} R _{θJA}	17 75								°C/W
Operating Temperature Range	T _J	- 65 to + 125			- 65 to + 150					°C
Storage Temperature Range	T _{STG}	- 65 to + 150								°C

Note 1: Pulse Test with PW=300u sec, 1% Duty Cycle


Note 2: Measure at 1MHz and Applied Reverse Voltage of 4.0V D.C.

SS22 - SS215 2.0 AMPS. Surface Mount Schottky Barrier Rectifiers SMB/DO-214AA



Dimensions in inches and (millimeters)

Marking Diagram



- SS2X = Specific Device Code
 G = Green Compound
 Y = Year
 M = Work Month

RATINGS AND CHARACTERISTIC CURVES (SS22 THRU SS215)

FIG. 1- MAXIMUM FORWARD CURRENT DERATING CURVE




FIG. 2- MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG. 3- TYPICAL FORWARD CHARACTERISTICS




FIG. 4- TYPICAL REVERSE CHARACTERISTICS




FIG. 5- TYPICAL JUNCTION CAPACITANCE





FIG. 6- TYPICAL TRANSIENT THERMAL CHARACTERISTICS



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Taiwan Semiconductor:](#)

[SS22](#) [SS24](#) [SS23](#) [SS25](#) [SS26](#) [SS215](#) [SS210](#)