

External SAS Cable, 4 Lane - mini-SAS (SFF-8088) to 4xInfiniband (SFF-8470), 2M (6.56 ft.), TAA

MODEL NUMBER: **S520-02M**



Highlights

- Hi-Performance 2 Meter SAS External Cable
- Mini-SAS SFF-8088 (iSAS) to SFF-8470
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- SAS Controllers, SAS Chassis, SAS/SATA Hard Drives

Package Includes

- 2 Meter SAS External SFF-8088 to SFF-8470 Cable

Features

- External SAS Cable, Mini-SAS SFF-8088 (iSAS) to SFF-8470 - 2 Meter
- Made with High-Performance Infiniband Cable
- Supports data transfer rates from 3.0 up to 6.0 gigabytes per second
- SFF-8470 thumbscrew type connector and SFF-8088 connector in die cast zinc housing for durability
- RoHS compliant
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332151957
Technology	SAS
PHYSICAL	
Color	Black
Cable Length (ft.)	6.6
Cable Length (m)	2
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 21.59
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 8.50



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (kg)	0.23
Shipping Weight (lbs.)	0.50
CONNECTIONS	
Side A - Connector 1	SFF-8088
Side B - Connector 1	SFF-8470
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[S520-02M](#)