

SmartOnline 230V 2kVA 1.4kW Double-Conversion UPS, Tower, Network Card Options, C20 inlet, DB9 Serial

MODEL NUMBER: **SUINT2000XL**



Description

Tripp Lite's SmartOnline SUINT2000XL on-line, double-conversion UPS protects critical server, networking and telecommunications equipment from blackouts, voltage fluctuations and transient surges. Space-saving upright tower format. Large capacity 2000VA/1400W UPS continuously converts incoming AC to DC, then back to perfect sine wave AC output at selectable 220/230/240V AC (+/-2%). Removes harmonic distortion, fast electrical impulses, frequency fluctuations and other hard-to-solve power problems not addressed by other UPS types. True sine wave output and zero transfer time offer guaranteed compatibility with all equipment types. Includes 8 C13 outlets. Battery support can be extended with external battery packs. Includes slot for internal network management card, plus DB9 enhanced serial monitoring port for unattended shutdown, remote control and monitoring of UPS system and power data.

Features

- True on-line, double conversion UPS provides pure sine wave AC output at all times
- Maintains continuous operation with zero transfer time through blackouts, voltage fluctuations and surges
- Removes harmonic distortion, electrical impulses, frequency variations and other hard-to-solve power problems
- Corrects brownout and overvoltages from 175-280V at full load. Input voltage range extends to 80-280V at 50% load or less
- 2000VA/1400W power capacity with 8 C13 outlets
- IEC320-C20 input connection accepts a variety of detachable cordsets to match country or site-specific wall receptacles
- Standard internal battery set provides 14 min. runtime at half load and 5 min. runtime at full load

Highlights

- 2000VA on-line, double-conversion, extended run tower UPS
- Maintains sine-wave 220/230/240V +/-2% output during overvoltages to 280V and brownouts as low as 80V (50/60Hz auto-sensing)
- Network communications supported via serial port and Network management card options
- C20 inlet, C13 outlets, 3 C13 to C14 power cables included
- Fault-tolerant auto-bypass and current monitoring

Package Includes

- SUINT2000XL UPS System
- DB9 serial cable
- 3 C13-to-C14 jumper cables
- Owner's manual with warranty information



- Intelligent battery management system extends battery life
- Expandable runtime with optional external battery packs
- DB9 serial port for network interface; SNMP compatible
- Compatible with Tripp Lite UPS management card options TLNETCARD, WEBCARDLX, SNMPWEBCARD, MODBUSCARD and RELAYIOCARD
- Serial port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from www.tripplite.com/poweralert
- Fault tolerant electronic bypass maintains utility output during a variety of UPS fault conditions
- Diagnostic LEDs
- Optional PDUBHV20 bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- 3 C13-to-C14 power cables included

Specifications

OVERVIEW	
UPC Code	037332128591
UPS Type	On-Line
INPUT	
Rated input current (Maximum Load)	7.4A (220V), 7.1A (230V), 6.8 (240V)
Nominal Input Voltage(s) Supported	220V AC; 230V AC; 240V AC
UPS Input Connection Type	C20 inlet
UPS Input Connection Description	IEC320-C20 input connection accepts a variety of detachable cordsets to match country or site-specific wall receptacles
Input Circuit Breakers	20A
Input Phase	Single-Phase
OUTPUT	
Output Volt Amp Capacity (VA)	2000
Output kVA Capacity (kVA)	2
Output Watt Capacity (Watts)	1400
Output kW Capacity (kW)	1.4
Power Factor	0.7
Crest Factor	3:1
Nominal Voltage Details	230V default
Frequency Compatibility	50 / 60 Hz

3 / 5



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

LED Indicators	14 LEDs indicate line power, online mode, economy/bypass mode, on-battery, overload, battery low, replace battery and fault status information - includes 4-LED meter display for load and battery charge level
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	570
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Cooling Method	Fan
Primary Form Factor	Tower
Primary UPS Depth (mm)	424
Primary UPS Height (mm)	373
Primary UPS Width (mm)	140
Shipping Dimensions (hwd / cm)	48.01 x 24.89 x 59.18
Shipping Dimensions (hwd / in.)	18.90 x 9.80 x 23.30
Shipping Weight (kg)	29.66
Shipping Weight (lbs.)	65.40
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	37.34 x 13.97 x 42.42
UPS Power Module Dimensions (hwd, in.)	14.7 x 5.5 x 16.7
UPS Power Module Weight (kg)	30.48
UPS Power Module Weight (lbs.)	67.2
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	523
Battery Mode BTU / Hr. (Full Load)	749
AC Mode Efficiency Rating (100% Load)	90%
AC Economy Mode Efficiency Rating (100% Load)	94%
Audible Noise	< 45 dB at front side 1m
COMMUNICATIONS	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Network Management Cards	SNMPWEBCARD ; TLNETCARD ; WEBCARDLX ; MODBUSCARD ; RELAYIOCARD
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions; DB9 port supports RS232 communications
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at http://www.tripplite.com/poweralert
Communications Cable	DB9 cabling included
Communications Interface	DB9 Serial; Slot for SNMP/Web interface
LINE / BATTERY TRANSFER	
Transfer Time	No transfer time (0 ms.) in online, double-conversion mode
Low Voltage Transfer to Battery Power (Setpoint)	175V (100% load), 80V (<50% load)
High Voltage Transfer to Battery Power (Setpoint)	280
SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Automatic inverter bypass
STANDARDS & COMPLIANCE	
UPS Certifications	CE
Certification Details	CE EN62040-1-1, EN62040-2 Class A
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SUINT2000XL](#)