


Protect It! 10-Outlet Surge Protector, 8 ft. (2.43 m) Cord, 3345 Joules, Tel/Modem/Coaxial Protection

MODEL NUMBER: **TLP1008TELT**



Highlights

- 10 outlets / 8-ft. (2.43 m) cord
- 1 in/2 out tel/modem surge protection
- 1 line 2.2GHz gold coaxial protection
- 3345 joule rating

Package Includes

- TLP1008TELT surge suppressor
- 6-ft. RJ11 cable
- 6-ft. (1.83 m) gold coax cable
- Instruction manual and warranty information

Description

Tripp Lite's TLP1008TELT offers economical AC surge suppression for protection of workstations, PCs, telecom systems, home electronics and other sensitive equipment. The TLP1008TELT features 10 outlets, an 8-ft. (2.43 m) cord with a space-saving right-angle plug, and diagnostic LEDs to warn of suppressor damage. The unit has a surge suppression rating of 3345 joules to shield equipment from line noise and the strongest surges. Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment. Built-in 2.2GHz goldcoax jacks prevent surges from damaging your cable/satellite equipment. \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

PLUG/OUTLETS: Input: NEMA5-15P/Output: 10 NEMA5-15R/8-ft. (2.43 m) AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip with 5 transformer-spaced outlet

SUPPRESSION: AC: 150V RMS Clamping/3345 joules/400V UL1449 3rd Edition

Features

- 10 outlets with child safety covers
- 8-ft. (2.43 m) cord with space-saving right-angle plug
- Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment; - built-in splitter protects two devices sharing a single line; 6-ft. (1.83 m) telephone cord included
- Built-in 2.2GHz gold coax jacks prevent surges from damaging your cable/satellite equipment; 6-ft gold coax cable included
- Surge suppression rating: 3345 joule protection
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker
- Diagnostic LEDs confirm suppressor "protection present" (green) and "grounded" (red) status



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- Can accommodate up to 4 transformers without blocking remaining outlets
- Keyhole supports for wall mounting
- \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required
- Lighted power switch

Specifications

| OVERVIEW | |
|------------------------------------|---|
| UPC Code | 037332119070 |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 120V (110-125V) |
| Input Cord Gauge Type | 14 gauge; SJT |
| Voltage Compatibility (VAC) | 120 |
| Maximum Surge Amps | 135000 |
| Input Plug Type | NEMA 5-15P |
| Input Cord Length (ft.) | 8 |
| Right-Angle Plug | Yes |
| Input Cord Length (m) | 2.44 |
| Integrated Cord Clip | No |
| OUTPUT | |
| Frequency Compatibility | 50 / 60 Hz |
| Output (Watts) | 1800 |
| Output Receptacles | (10) 5-15R |
| Circuit Breaker (amps) | 15 |
| Overload Protection | 15A resettable circuit breaker |
| Transformer Accommodation | (8) Yes |
| Outlet Orientation | Two rows of outlets, including 4 widely spaced for transformers |
| Right-Angle Outlets | No |
| USER INTERFACE, ALERTS & CONTROLS | |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--|---|
| Diagnostic LED(s) | Yes |
| Switches | Two-position on/off power switch |
| Diagnostic LED Details | Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status |
| SURGE / NOISE SUPPRESSION | |
| AC Suppression Joule Rating | 3345 |
| AC Suppression Response Time | < 1 ns |
| Protection Modes | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression |
| Clamping Voltage (RMS) | 150 |
| UL1449 Let Through Rating | 400V - UL Verified |
| EMI / RFI Filtering | Up to 40 dB |
| Automatic Shut-Off | Yes |
| DATALINE SURGE SUPPRESSION | |
| Telephone/DSL Protection | Yes |
| Telephone/DSL Protection Details | 1 line |
| Cable (Coax) Protection | Yes |
| Cable (Coax) Protection Details | 1 line |
| Network (Ethernet) Protection | No |
| PHYSICAL | |
| Antimicrobial Coating | No |
| Power Cord Color | Black |
| Housing Color | Black |
| Integrated Keyhole Mounting Slots | Yes |
| Keyhole Slot Mounting Measurement (Center to Center) | 108mm |
| Material of Construction | Plastic |
| Outlets Measurement (Center to Center) | Between Standard Outlets = 28.4mm; Between Standard and Transformer Outlets = 56.8mm |
| Receptacle Color | Black |
| Shipping Dimensions (hwd / cm) | 36.58 x 6.35 x 20.83 |
| Shipping Dimensions (hwd / in.) | 14.40 x 2.50 x 8.20 |
| Shipping Weight (kg) | 1.22 |
| Shipping Weight (lbs.) | 2.70 |
| Unit Dimensions (hwd / cm) | 29.5 x 12.7 x 6.5 |
| Unit Dimensions (hwd / in.) | 11.6 x 5 x 2.25 |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--|--|
| Unit Weight (kg) | 1.00 |
| Unit Weight (lbs.) | 2.2 |
| SPECIAL FEATURES | |
| Rotatable Outlets | No |
| STANDARDS & COMPLIANCE | |
| Canada | cUL |
| Approvals | Exceeds IEEE 587 category A&B specifications |
| UL1449 3rd Edition (AC Suppression) | UL1449 3rd Edition |
| UL1363 (Power Tap) | UL1363 |
| UL497A (Communications) | UL497A |
| FCC Part 68 (Communications) | FCC Part 68 |
| Industry Canada (Communications) | Industry Canada |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$150,000 Ultimate Lifetime Insurance |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLP1008TELTV](#)