


**TO-220**

**ITO-220**
**Pin Definition:**

1. Ground
2. Input (tab)
3. Output

### General Description

The TS7900 series of fixed output negative voltage regulators are intended as complements to the popular TS7800 series device. These negative regulators are available in the same seven-voltage options as the TS7900 devices. In addition, one extra voltage option commonly employed in MECL systems is also available in the negative TS7900 Series. Available in fixed output voltage options from -5.0 to -24 volts, these regulators employ current limiting, thermal shutdown, and safe-area compensation--making them remarkably rugged under most operating conditions. With adequate heat sinking they can deliver output currents in excess of 1 ampere.

### Features

- Output Voltage: -5 & -12V
- Output current up to 1A
- No external components required
- Internal thermal overload protection
- Internal short-circuit current limiting
- Output transistor safe-area compensation
- Output voltage offered in 4% tolerance


### Ordering Information

Part No.	Package	Packing
TS79xxCZ C0	TO-220	50pcs / Tube
TS79xxCZ C0G	TO-220	50pcs / Tube
TS79xxCI C0	ITO-220	50pcs / Tube
TS79xxCI C0G	ITO-220	50pcs / Tube

**Note:** Where xx denote voltage option

"G" denote for Green Product Halogen Free

### Standard Application Circuit



A common ground is required between the input and the output voltages. The input voltage must remain typically 2.0V above the output voltage even during the low point on the Input ripple voltage.

XX = these two digits of the type number indicate voltage.

\* = Cin is required if regulator is located an appreciable distance from power supply filter.

\*\* = Co is not needed for stability; however, it does improve transient response.

### Absolute Maximum Rating (Ta = 25°C unless otherwise noted)

Parameter	Symbol	Limit	Unit
Input Voltage	V <sub>IN</sub>	-35	V
Power Dissipation	P <sub>D</sub>	Internal Limited	W
Junction Temperature	T <sub>J</sub>	+150	°C
Storage Temperature Range	T <sub>STG</sub>	-65~+150	°C
Thermal Resistance - Junction to Case	R <sub>θ<sub>JC</sub></sub>	3	°C/W
		5	
Thermal Resistance - Junction to Ambient	R <sub>θ<sub>JA</sub></sub>	50	°C/W
		60	

**Note:** \* Follow the derating curve

**TS7905 Electrical Characteristics**

(Vin= -10V, Iout=500mA, 0°C≤Tj≤125°C, Cin=0.33uF, Cout=0.1uF; unless otherwise specified.)

Parameter	Symbol	Test Condition		Min	Typ	Max	Unit
Output voltage	Vout	Tj=25°C		-4.80	-5	-5.20	V
		-7.5V≤Vin≤-20V, 10mA≤Iout≤1A, PD≤15W		-4.75	-5	-5.25	
Line Regulation	REGline	Tj=25°C	-7.5V≤Vin≤-25V	--	3	100	mV
			-8V≤Vin≤-12V	--	1	50	
Load Regulation	REGload	Tj=25°C	10mA≤Iout≤1A	--	15	100	mV
			250mA≤Iout≤750mA	--	5	50	
Quiescent Current	Iq	Iout=0, Tj=25°C		--	4	8	mA
Quiescent Current Change	ΔIq	-7.5V≤Vin≤-25V		--	--	1.3	
		10mA≤Iout≤1A		--	--	0.5	
Output Noise Voltage	Vn	10Hz≤f≤100KHz, Tj=25°C		--	40	--	μV
Ripple Rejection Ratio	RR	f=120Hz, -8V≤Vin≤-18V		62	74	--	dB
Voltage Drop	Vdrop	Iout=1A, Tj=25°C		--	2	--	V
Output Short Circuit Current	Ios	Tj=25°C		--	750	--	mA
Peak Output Current	Io peak	Tj=25°C		--	2.1	--	A
Temperature Coefficient of Output Voltage	ΔVout/ ΔTj	Iout=10mA, 0°C≤Tj≤125°C		--	-0.1	--	mV/ °C

**TS7912 Electrical Characteristics**

(Vin= -19V, Iout=500mA, 0°C≤Tj≤125°C, Cin=0.33uF, Cout=0.1uF; unless otherwise specified.)

Parameter	Symbol	Test Condition		Min	Typ	Max	Unit
Output Voltage	Vout	Tj=25°C		-11.53	-12	-12.48	V
		-14.5V≤Vin≤-27V, 10mA≤Iout≤1A, PD ≤15W		-11.42	-12	-12.60	
Line Regulation	REGline	Tj=25°C	-14.5V≤Vin≤-30V	--	10	240	mV
			-15V≤Vin≤-19V	--	3	120	
Load Regulation	REGload	Tj=25°C	10mA≤Iout≤1A	--	12	240	mV
			250mA≤Iout≤750mA	--	4	120	
Quiescent Current	Iq	Tj=25°C, Iout=0		--	4.3	8	mA
Quiescent Current Change	ΔIq	-14.5V≤Vin≤-30V		--	--	1	
		10mA≤Iout≤1A		--	--	0.5	
Output Noise Voltage	Vn	10Hz≤f≤100KHz, Tj=25°C		--	75	--	uV
Ripple Rejection Ratio	RR	f=120Hz, -15V≤Vin≤-25V		55	70	--	dB
Voltage Drop	Vdrop	Iout=1A, Tj=25°C		--	2	--	V
Output Short Circuit Current	Ios	Tj=25°C		--	350	--	mA
Peak Output Current	Io peak	Tj=25°C		--	2.1	--	A
Temperature Coefficient of Output Voltage	ΔVout/ ΔTj	Iout=10mA, 0°C≤Tj≤125°C		--	-1	--	mV/ °C

- Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible, and thermal effects must be taken into account separately.
- This specification applies only for DC power dissipation permitted by absolute maximum ratings.

### Electrical Characteristics Curve




Figure 1. Worse Case Power Dissipation as a Function of Ambient Temperature




Figure 2. Peak Output Current as a Function of Input-Output Differential Voltage




Figure 3. Ripple Rejection as a Function of Frequency




Figure 4. Ripple Rejection as a Function of Output Voltage




Figure 5. Output Voltage as a Function of Junction Temperature






Figure 5. Output Voltage as a Function of Junction Temperature

### TO-220 Mechanical Drawing




TO-220 DIMENSION				
DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	10.00	10.50	0.394	0.413
B	3.74	3.91	0.147	0.154
C	2.44	2.94	0.096	0.116
D	--	6.35	--	0.250
E	0.38	1.10	0.015	0.043
F	2.34	2.71	0.092	0.107
G	4.69	5.43	0.185	0.214
H	12.70	14.73	0.500	0.580
I	8.38	9.38	0.330	0.369
J	14.22	16.51	0.560	0.650
K	3.55	4.82	0.140	0.190
L	1.16	1.40	0.046	0.055
M	27.70	29.62	1.091	1.166
N	2.03	2.92	0.080	0.115
O	0.25	0.61	0.010	0.024
P	5.84	6.85	0.230	0.270

### Marking Diagram




- XX** = Output Voltage  
(05=-5V, 12=-12V)
- Y** = Year Code
- M** = Month Code  
(A=Jan, B=Feb, C=Mar, D=Apl, E=May, F=Jun, G=Jul, H=Aug, I=Sep, J=Oct, K=Nov, L=Dec)
- = Month Code for Halogen Free Product  
(O=Jan, P=Feb, Q=Mar, R=Apl, S=May, T=Jun, U=Jul, V=Aug, W=Sep, X=Oct, Y=Nov, Z=Dec)
- L** = Lot Code
- CZ** = Package Code for TO-220

## ITO-220 Mechanical Drawing



ITO-220 DIMENSION				
DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	9.96	10.36	0.392	0.407
B	6.20 (typ.)		0.244 (typ.)	
C	2.20 (typ.)		0.087 (typ.)	
D	§ 1.40 (typ.)		§ 0.055 (typ.)	
E	15.07	16.07	0.593	0.632
F	0.80 (typ.)		0.031 (typ.)	
G	2.44	2.64	0.096	0.104
H	13.08	13.48	0.514	0.530
I	1.47 (max.)		0.057 (max.)	
J	3.20	3.40	0.125	0.133
K	4.60	4.80	0.181	0.188
L	1.15 (typ.)		0.045 (typ.)	
M	2.44	2.64	0.096	0.104
N	2.60	2.80	0.102	0.110
O	6.55	6.65	0.258	0.262

## Marking Diagram



### Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Taiwan Semiconductor:

[TS7924CZ](#) [TS7924CI](#) [TS7915CZ](#) [TS7915CI](#) [TS7908CI](#) [TS7908CZ](#) [TS7912CI](#) [TS7906CI](#) [TS7906CZ](#) [TS7912CZ](#)  
[TS7909CZ](#) [TS7909CI](#) [TS7905CI](#) [TS7918CZ](#) [TS7918CI](#) [TS7912CZ C0](#) [TS7905CZ C0](#) [TS7905CI C0G](#) [TS7905CZ](#)  
[C0G](#) [TS7912CI C0G](#) [TS7912CZ C0G](#)