

Protect It! 8-Outlet Computer Surge Protector, 8 ft. (2.43 m) Cord, 2160 Joules, Tel/Modem/Fax Protection

MODEL NUMBER: TLP808TEL



Highlights

- 8 outlets / 8-ft. (2.43 m) cord
- 2160 joule rating
- Modem/fax surge protection

Package Includes

- TLP808TEL
- 6-ft. (1.83 m) telephone cord
- Instruction manual with warranty information

Description

Tripp Lite's TLP808TEL surge suppressor has 8 outlets, an 8-ft. (2.43 m) cord with a space-saving right-angle plug, and diagnostic LEDs. The unit has a surge suppression rating of 2160 joules to handle the strongest surges. Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment. \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Features

- 2160 joules AC surge suppression shields equipment from the strongest surges and line noise
- 8 AC outlets with room for 3 transformer plugs without blocking outlets covers computers and all peripherals
- Long 8-ft. (2.43 m) AC line cable with space-saving angle input plug conveniently reaches distant outlets
- built-in RJ11 jacks (1in/2 out) prevent surges from damaging your modem/fax/phone equipment
- Lighted power switch with integrated 15 amp circuit breaker offers power control and overload protection
- Integrated child-safety sliding outlet covers safely seal off all unused outlets
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- Attractive white suppressor housing with keyhole mounting tabs allow versatile placement options
- \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332095367
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	144000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	8
Right-Angle Plug	Yes
Input Cord Length (m)	2.44
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(8) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(6) Yes
Outlet Orientation	Single row of 5, plus a second row of 3 for transformer accommodation
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2-position red illuminated on/off power switch
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2160
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	330/400/400
EMI / RFI Filtering	Up to 40 dB



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Antimicrobial Coating	No
Power Cord Color	Light Gray
Housing Color	White
Integrated Keyhole Mounting Slots	Yes
Keyhole Slot Mounting Measurement (Center to Center)	Distance between horizontal slots = 75mm; Distance between vertical slots = 41.6mm
Material of Construction	Plastic
Receptacle Color	Light gray
Shipping Dimensions (hwd / cm)	27.94 x 18.80 x 5.08
Shipping Dimensions (hwd / in.)	11.00 x 7.40 x 2.00
Shipping Weight (kg)	0.86
Shipping Weight (lbs.)	1.90
Unit Dimensions (hwd / cm)	12.34 x 24.26 x 3.84
Unit Dimensions (hwd / in.)	4.86 x 9.55 x 1.51
Unit Weight (kg)	0.86
Unit Weight (lbs.)	1.89
SPECIAL FEATURES	
Additional Information	Pair of phone line output jacks serve as a line splitter to enable the protection of two devices sharing a single dialup phone line
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Canada	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

FCC Part 68 (Communications)	FCC Part 68
Industry Canada (Communications)	Industry Canada
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 Ultimate Lifetime Insurance

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLP808TEL](#)