Please read this notice before using the TAIYO YUDEN products.

### **I** REMINDERS

Product information in this catalog is as of October 2017. All of the contents specified herein are subject to change without notice due to technical improvements, etc. Therefore, please check for the latest information carefully before practical application or use of our products.

Please note that TAIYO YUDEN shall not be in any way responsible for any damages and defects in products or equipment incorporating our products, which are caused under the conditions other than those specified in this catalog or individual product specification sheets.

- Please contact TAIYO YUDEN for further details of product specifications as the individual product specification sheets are available.
- Please conduct validation and verification of our products in actual condition of mounting and operating environment before using our products.
- The products listed in this catalog are intended for use in general electronic equipment (e.g., AV equipment, OA equipment, home electric appliances, office equipment, information and communication equipment including, without limitation, mobile phone, and PC) and medical equipment classified as Class I or II by IMDRF. Please be sure to contact TAIYO YUDEN for further information before using the products for any equipment which may directly cause loss of human life or bodily injury (e.g., transportation equipment including, without limitation, automotive powertrain control system, train control system, and ship control system, traffic signal equipment, disaster prevention equipment, medical equipment classified as Class III by IMDRF, highly public information network equipment including, without limitation, telephone exchange, and base station).

Please do not incorporate our products into any equipment requiring high levels of safety and/or reliability (e.g., aerospace equipment, aviation equipment\*, medical equipment classified as Class IV by IMDRF, nuclear control equipment, undersea equipment, military equipment).

\*Note: There is a possibility that our products can be used only for aviation equipment that does not directly affect the safe operation of aircraft (e.g., in-flight entertainment, cabin light, electric seat, cooking equipment) if such use meets requirements specified separately by TAIYO YUDEN. Please be sure to contact TAIYO YUDEN for further information before using our products for such aviation equipment.

When our products are used even for high safety and/or reliability-required devices or circuits of general electronic equipment, it is strongly recommended to perform a thorough safety evaluation prior to use of our products and to install a protection circuit as necessary.

Please note that unless you obtain prior written consent of TAIYO YUDEN, TAIYO YUDEN shall not be in any way responsible for any damages incurred by you or third parties arising from use of the products listed in this catalog for any equipment requiring inquiry to TAIYO YUDEN or prohibited for use by TAIYO YUDEN as described above.

Information contained in this catalog is intended to convey examples of typical performances and/or applications of our products and is not intended to make any warranty with respect to the intellectual property rights or any other related rights of TAIYO YUDEN or any third parties nor grant any license under such rights.

Please note that the scope of warranty for our products is limited to the delivered our products themselves and TAIYO YUDEN shall not be in any way responsible for any damages resulting from a fault or defect in our products. Notwithstanding the foregoing, if there is a written agreement (e.g., supply and purchase agreement, quality assurance agreement) signed by TAIYO YUDEN and your company, TAIYO YUDEN will warrant our products in accordance with such agreement.

The contents of this catalog are applicable to our products which are purchased from our sales offices or authorized distributors (hereinafter "TAIYO YUDEN's official sales channel"). Please note that the contents of this catalog are not applicable to our products purchased from any seller other than TAIYO YUDEN's official sales channel.


#### Caution for Export

Some of our products listed in this catalog may require specific procedures for export according to "U.S. Export Administration Regulations", "Foreign Exchange and Foreign Trade Control Law" of Japan, and other applicable regulations. Should you have any questions on this matter, please contact our sales staff.

## CYLINDER TYPE POLYACENE CAPACITORS



#### PARTS NUMBER



Jeenee name							
Code	Series name						
PAS	Polyacene capacitor						

②Dimensions( $\phi$ D)

<u>0</u>						
Dimensions ( $\phi$ D) [mm]						
8						
10						
12.5						

#### ③Dimensions(L)

Code	Dimensions(L)[mm]				
15	15				
16	16				
20	20				
30	30				
35	35				

#### (4) Characteristics spec

Code	Characteristics spec				
LS	Low ESR type				
LN	High Reliability type				
LA	High Voltage type				

#### 5Maximum usable voltage

0	0						
Code	Maximum usable voltage[V]						
2R5	2.5						
2R7	2.7						
3R0	3.0						

%R=Decimal point

### 6Nominal capacitance

Code (example)	Nominal capacitance[F]				
105	$10 \times 10^5 \mu\text{F} = 1\text{F}$				
S	S				
206	$20 \times 10^{6}  \mu  \text{F} = 20 \text{F}$				

#### EXTERNAL DIMENSIONS



Characteristics spec	Part number	φD	L	$\phi$ d	Р
Low ESR type	PAS0815LS2R5105	8	15	0.6	3.5
(LS series)	PAS1016LS2R5205	10	16	0.6	5.0
	PAS0815LN2R7205	8	15	0.6	3.5
	PAS1030LN2R7705	10	30	0.6	5.0
High Reliability type (LN Series)	PAS1030LN2R7905	10	30	0.6	5.0
(LIN Series)	PAS1220LN2R7905	12.5	20	0.6	5.0
	PAS1230LN2R7166	12.5	30	0.6	5.0
	PAS1020LA3R0405	10	20	0.6	5.0
High Voltage Type (LA Series)	PAS1220LA3R0905	12.5	20	0.6	5.0
(LA Series)	PAS1235LA3R0206	12.5	35	0.6	5.0
	•			L los lator and	

Unit:mm

#### PARTS NUMBER

Characteristics spec	Part number	Maximum usable voltage[V]	Nominal capacitance[F]	ESR@1KHz[m $\Omega$ ]
Low ESR type	PAS0815LS2R5105	0.5	1	70
(LS series)	PAS1016LS2R5205	2.5	2	50
	PAS0815LN2R7205		2	180
Link Delinkiliter terre	PAS1030LN2R7705		7	80
High Reliability type (LN Series)	PAS1030LN2R7905	2.7	9	80
	PAS1220LN2R7905		9	60
	PAS1230LN2R7166		16	50
High Voltage Type (LA Series)	PAS1020LA3R0405		4	300
	PAS1220LA3R0905	3.0	9	200
	PAS1235LA3R0206		20	100

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/). [LS series]

Part number	Operating temp. range [°C]	Maximum usable voltage [V]	Initial capacitance [F]	Initial ESR@1KHz [mΩ]	Temperature characteristics
PAS0815LS2R5105	-25~+70	2.5	1.0±20%	Under 70	Lowest temperature(-25°C) Capacitance:Over 70% of initial spec. Internal resistance:Within 4 times of initial spec.
PAS1016LS2R5205		2.0	2.0±20%	Under 50	Highest temperature(70°C) Capacitance : Within initial spec. Internal resistance : Within initial spec.

[LN series]

Part number	Operating temp. range [°C]	Maximum usable voltage [V]	Initial capacitance [F]	Initial ESR@1KHz [mΩ]	Temperature characteristics
PAS0815LN2R7205			2.0±20%	Under 180	Lowest temperature(-40°C) Capacitance:Over 85% of initial spec.
PAS1030LN2R7705	-40~+70 Over +70~+85		7.0±20%	Under 80	Internal resistance Within 6 times of initial spec.
PAS1030LN2R7905		2.7 2.3	9.0±20%	Under 80	High temperature(70°C) Capacitance:Within initial spec.
PAS1220LN2R7905			9.0±20%	Under 60	Internal resistance:Within initial spec. Highest temperature(85°C)
PAS1230LN2R7166			16±20%	Under 50	Capacitance:Over 90% of initial spec. Internal resistance:Within initial spec.

[LA series]

Part number	Operating temp. range [°C]	Maximum usable voltage [V]	Initial capacitance [F]	Initial ESR@1KHz [mΩ]	Temperature characteristics
PAS1020LA3R0405			4.0±20%	Under 300	Lowest temperature(-25°C) Capacitance:Over 70% of initial spec. Internal resistance:Within 4 times of initial spec.
PAS1220LA3R0905	$-25 \sim +60$ Over $+60 \sim +70$ Over $+70 \sim +85$	3.0 2.7 2.3	9.0±20%	Under 200	High temperature(60°C/70°C) Capacitance:Within initial spec. Internal resistance:Within initial spec.
PAS1235LA3R0206			20±20%	Under 100	Highest temperature(85°C) Capacitance:Over 90% of initial spec. Internal resistance:Within initial spec

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

Items		Specified valu	Test methods and remark		
itoms	LS series	LN series	LA series	rest methods and rendrk	
1. Operating temperature range	-25~+70°C	-40~+70 / +85°C	-25~+60 / +70 / +85°C		
2. Maximum usable voltage	2.5V	2.7V / 2.3V	3.0V / 2.7V / 2.3V		
3. Soldering		hin initial spec. ce:Within initial spec. noticeable abnormality	Material:Sn-3Ag-0.5Cu Solder temperature:260±5°C Dipping time:10±1 sec. Dipping depth:1.5~2mm from cell body		
4. Floating charge characteristics	Capacitance:Over 70% of initial spec. Internal resistance:Within 4 times of initial spec.			Apply a max. usable voltage to capacitor for 1000 hours at max. operating temperature and measure the floating charge characteristics after returning to normal temperature and humidity.	
5. Charge/Discharge cycle characteristics		noticeable abnormality	Measure the charge/discharge cycle characteristics after 10000 charge/discharge cycle at $25\pm5^{\circ}$ C with under mentioned charge/discharge cycle test condition for each parts.		
6. Thermal durability	Capacitance : Within initial spec. Internal resistance : Within initial spec. Appearance : No noticeable abnormality			Leave the capacitor in environment of the max. usable temperature $\pm 2^{\circ}C$ and $-25\pm 2^{\circ}C$ consecutively for 96 hours each, and return to normal temperature and humidity.	
7. Humidity durability	Capacitance:Within initial spec. Internal resistance:Within 4 times of initial spec. Appearance:No noticeable abnormality			Temperature: $40\pm 2^{\circ}$ C, humidity: $90 \sim 95\%$ RH leave the capacitor for 500 hours, and return to normal temperature and humidity.	
8. Shock resistance	<b>.</b>			According to JIS C 60068-2-27 Half-sine wave A=294	
9. Vibration resistance	No exterior abnormality observed: initial spec. values retained			Apply a sine wave vibration of 1.5mm amplitude and frequency 10~55Hz, for 2 hours per each direction (X,Y and Z), total 6 hours.	

Charge/Discharge cycle test condition

Part number	Charging voltage [V]	Charging time [sec]	Max. Charging current [A]	Discharge current [A]	Terminal voltage [V]
PAS0815LS2R5105	2.5	10	1	1	
PAS1016LS2R5205					
PAS0815LN2R7205	2.7	30	0.2	0.2	
PAS1030LN2R7705			0.9	0.9	1.5
PAS1030LN2R7905			1	1	
PAS1220LN2R7905			1	1	
PAS1230LN2R7166			1	1	
PAS1020LA3R0405	3.0		2	0.5	
PAS1220LA3R0905			3	1	
PAS1235LA3R0206			5	1	

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

#### PRECAUTIONS

#### 1. Use within the usable voltage range

Applying voltage exceeding the maximum working voltage may cause leakage or damage.

#### 2. Use within the operating temperature range

#### 3. Lifetime of POLYACENE capacitor is finite

The life of the product is affected by operating temperature and operating voltage. In addition, the internal resistance rises gradually with usage and the capacity drops.

#### 4. There are temperature dependence and voltage dependence in the electrical characteristics

The electrical characteristics of the product vary depending on operating temperature and voltage. Please check the temperature characteristics before using the product.

#### 5. Polyacene capacitor has polarity

Check the polarity before use. It will be damage if it is reversely charged. Avoid using products with reverse voltage applied.

#### 6. Be aware of the ripple current and use in circuits that repeat sudden charge and discharge

POLYACENE capacitor may be used in a circuit that repeats sudden charge / discharge or application of high ripple current may cause the life to be shortened due to heat generation. Please inquire when using it for such a circuit.

#### 7. Mind the voltage drop during discharge (backup)

If the discharge current is large, a voltage drop occurs at the start of discharge. Be careful about discharge current.

#### 8. Series connection

When POLYACENE capacitors are connected in series, the balance of the applied voltage may be lost, and some capacitors may be overcharged or may lead to shortening lifetime and breakdown. Take a margin against the maximum usable voltage or add a balancing resister.

#### 9. POLYACENE capacitor has the pressure release vent

In case of inside pressure of capacitor excessively rising, the pressure release vent will be opened in order to release inner gas. Following clearance (Diameter  $\langle \phi 18 : \text{over } 2\text{mm}$ , Diameter  $\geq \phi 18 : \text{over } 3\text{mm}$ ) should be made above the pressure release vent.

Don't set up wiring or a pattern in the upper part of the pressure release vent, so that the high temperature gas is gushed when the pressure release vent open.

The product which open the pressure release vent cannot use.

#### 10. Iinsulation of the aluminum case and sleeve of lithium ion capacitor is not guaranteed

There is a possibility of short-circuiting when the circuit pattern is arranged under the POLYACENE capacitor or when it comes in contact with other parts.

#### 11. Environmental of usage

In case POLYACENE capacitor is used in high humidity, alkaline or acid air, it may cause deteriorating of its performance and short circuit by corrosion of outer can or lead terminal. In addition, used in sudden temperature change or high humidity, it may cause deteriorating of its performance and electrolyte leak by dew condensation.

#### 12. Don't apply shock and vibration or pressure

POLYACENE capacitors are weak parts for mechanical shock. Be careful not to drop the product or apply strong force to the main body and lead terminal. Also, if you apply excessive vibration or shock after mounting, stress such as grasping, tilting, pushing, twisting, etc., the soldered part may come off or the lead terminal part may be damaged.

#### 13. Be careful not to apply excessive heat when mounting

If excessive heat stress is added to the product, electric characteristics deterioration and electrolyte leakage may occur. Soldering conditions should be within the range specified in the delivery specifications.

#### 14. Please consult about substrate cleaning after soldering

There are cases where the product may be adversely affected depending on the type of solvent and washing conditions, so please consult in advance.

#### 15. Storage

Keep following cautions for storage of POLYACENE capacitor.

•Don't store in the high temperature and the high humidity condition and a place where receiving direct sunlight. Storing POLYACENE capacitor in the room condition of 10 °C - 35 °C and less than 65% relative humidity is recommended. Sudden temperature change or high humidity may cause deteriorating of its characteristics and solderability.

•Don't store POLYACENE capacitor near water, salt water or oil, and in the dew condensation, gasified oil or salinity filled place.

•Don't store POLYACENE capacitor in the hazardous gas (hydrogen sulfide, sulfurous, chlorine, ammonia, bromine, methyl bromine, ozone and etc.).

·Don't fumigate by halogen fumigant.

•Don't store POLYACENE capacitor near acid or alkaline solvent.

•Don't store POLYACENE capacitor in a place where exposed to ultraviolet or radioactive rays.

•Don't store POLYACENE capacitor in a place where vibration and shock might occur.

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

#### 16. Disposal

Dispose POLYACENE capacitor properly with a decree or the regulation a local public organization designates.

#### 17. Usage

POLYACENE capacitor is developed on the assumption that this product will be used in the memory-backup & RTC for usage of information & communication equipment, home electronics, audio & visual equipment, office equipment, etc. Consult us about using high reliability and safety required products such as medical equipment, transportation equipment, industrial equipment, flight / space equipment and emergency equipment, etc.

#### 18. Other Notice

•Don't heat or throw POLYACENE capacitor into fire.

- •Don't short-circuit.
- •Don't solder directly to a cell body.
- •Don't open a body.
- •Don't deform.
- •Don't apply pressure.

%All of the contents specified herein are subject to change without notice due to technical improvements, etc.

\*Please see JEITA RCR-2370C for details.

JEITA RCR-2370C

Safety application guide of electric double layer capacitor (EDLC) (Directions guideline of electric double layer capacitor) J

[Corporation Electronic Industries Association of Japan. Enactment in March 1995 and revision in July 2008]

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taiyo Yuden:

 PAS0815LA2R3185
 PAS1020LA2R3475
 PAS1020LA3R0405
 PAS1220LA2R3106
 PAS1220LA3R0905

 PAS1235LA2R3226
 PAS1235LA3R0206
 PAS1840LA2R3566
 PAS1840LA3R0506
 PAS0815LS2R5105

 PAS1016LS2R5205
 PAS1030LN2R7905
 PAS1235LN2R7206
 PAS0815LN2R7205
 PAS1020LN2R7405

 PAS1220LN2R7905
 PAS1030LN2R7705
 PAS1230LN2R7166
 PAS1230LN2R7166