

3 Port HDMI over Cat5/6 Switch/Extender Kit, 1080p 60 Hz, Serial and IR Control, 656 ft. (200 m), TAA

MODEL NUMBER: **B160-103-HDSI**



Converts HDMI A/V to an IP-based signal that is transmitted through a managed switch to an HDMI display 656 ft. away via Cat5e/6 cable.

Features

DVI/HDMI Switch Kit for Digital Signage or Extending Video in Schools or Trade Show Booths

This switch/extender kit comes with three Tripp Lite B160-001-HDSI transmitters and one B160-100-HDSI receiver. It extends and distributes DVI or HDMI audio/video, RS-232 serial and IR (infrared) remote signals from three source devices, such as Blu-ray players and media servers, to an HDMI display via Cat5e/6 cabling. The maximum distance between a transmitter and receiver is 328.08-ft. (100 m). However, by connecting a dedicated network switch (sold separately) in between, you can extend the audio/video as far as 656-ft. (200 m).

Scale Up to a Multi-In, Multi-Out Installation to Take You Beyond 656 Feet

You can create an installation featuring multiple sources and displays by connecting a dedicated managed Ethernet network switch with Internet Group Management Protocol (IGMP), such as Tripp Lite's NSS-G16D2. By adding multiple managed switches, you can create a multi-in, multi-out installation with as many as 64 transmitters and 255 receivers. The IGMP-enabled switch will let you manage all connections for centralized control over which sources show on which displays. Note: Unmanaged switch installations are limited to two transmitter units. The number of receivers is limited to the number of ports remaining on the unmanaged switch. This transmitter/receiver extender kit is designed for use with a dedicated network switch. Connecting a switch used with other networking equipment will result in degraded or non-functional performance.

Transmits Crystal-Clear 1080p Video with Stereo Audio

The B160-103-HDSI supports video resolutions up to 1920 x 1080 (1080p) at 60 Hz with 24-bit True Color in a managed switch installation. It extends IR signals that control a DVI or HDMI source to the remote display, as well as RS-232 signals at serial baud rates up to 57600 bps. This allows you to operate the source devices' remote controls (play, rewind, pause, etc.), while standing near the receiver located up to 656-ft. (200 m) away. Adapter cables are included for converting DVI signals to HDMI and vice versa.

Plug-and-Play Operation for Quick Setup and Immediate Use

The included transmitter and receiver units work right out of the box with no software required. Mounting hardware is included for installing the units on walls, poles or 19-inch racks. Cat6 patch cable (such as Tripp Lite's N202-Series) can be used to connect the transmitters to a receiver or network switch. Connect an additional display to a transmitter's local output with HDMI cable (such as Tripp Lite's P568- or P569-Series) to monitor the image being transmitted to a remote display.

Highlights

- Switch kit includes 3 B160-001-HDSI transmitters and one B160-100-HDSI receiver
- Delivers HD picture quality at resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Transmitters' local HDMI ports let you monitor images being shown on remote display
- Plug-and-play operation with no software required for easy, immediate installation
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

- Keep your video sources in a secure location, with displays located elsewhere for viewing by the intended audience
- Create an easily updatable video board communicating dynamic information, such as a restaurant menu or a theater schedule
- Display arrivals, departures and up-to-the-minute information in an airport or train station
- Duplicate audio/video content across multiple displays, show different content on multiple screens or create an impressive video wall made up of many monitors (multiple transmitters and receivers required)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

TAA-Compliant for GSA Schedule Purchases

The B160-103-HDSI is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

System Requirements

- Source devices with DVI or HDMI output (media server, Blu-ray player)
- Display device with DVI or HDMI input (HDTV, projector, monitor)

Package Includes

- (3) B160-001-HDSI transmitter units
- B160-100-HDSI receiver unit
- (3) IR-Out cables
- IR-In cable
- (4) HDMI to DVI adapter cables
- (4) 3.5 mm to DB9 adapter cables (M/F)
- (4) External power supplies with 4.5-ft. (1.37 m) cord (Input: 100-240V, 50/60 Hz, 1A; Output: 5V 2A)
- (16) International plug adapters (North America, Europe, U.K., Australia)
- (4) Sets of mounting hardware
- (4) Owner's manuals

Specifications

OVERVIEW	
UPC Code	037332236012
Product Type	Extender Kit
Technology	DVI; HDMI; IR; Serial (RS232); A/V over IP; Cat5/5e; Cat6
VIDEO	
Max Supported Video Resolution	1920x1080 (1080p @ 60Hz)
Max 1280 x 720 (720p) Range (ft)	328
Max 1920 x 1080 (1080p) Range (ft)	328



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Transmitter Video Input	HDMI
Transmitter - Number of Video Outputs	3
Transmitter - Local Display Output	HDMI
Receiver/Transceiver Video Output	HDMI
Receiver - Number of Video Outputs	1
Range Extension using other Tripp Lite product	328ft
Recommended Cabling	N202-Series Cat6 Patch Cable
Other Tripp Lite product used to extend range	network switch
Max Supported Color Depth	24-bit True Color
HDR Support	No
3D Video Supported	Yes
Maximum Signal Range (ft)	328
Maximum Signal Range (m)	100
Maximum Signal Range Details	328 ft via Cat6275 ft via Cat5e
AUDIO	
Audio Input	HDMI
Audio Output	HDMI
Audio Specification	Stereo Audio
POWER	
Power Source	Transmitter and Receiver (Included)
Power Source Type	AC Adapter
AC Plug Type	NEMA 1-15P; BS1363; CEE 7/16 Schuko; AS/NZS 3112
External Power Supply Input Specs (V / Hz / A)	100-240V / 50-60Hz / 1.0A
External Power Supply Output Specs (V / A)	5V/2A
External Power Supply Cord Length (ft.)	4.5
External Power Supply Cord Length (m.)	1.4
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	BSMI; CB; CCC; CE; FCC; GS; PSE; RCM; TUV; UL; cUL
Power Over Cable (PoC) Support	No
USER INTERFACE, ALERTS & CONTROLS	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

LED Indicators	TX & RX: RJ45 (Green / Power, Orange / Signal), Channel Signal (Red), Power (Green)
PHYSICAL	
Color	Black
Included Mounting Accessories	Wallmount
Material of Construction	Metal
Number of Displays	3
Optional Mounting Accessory Notes	Can DIN Mount using Tripp Lite Bracket B110-DIN-02
Form Factor/Mounting Options	Box; Wall-mount
Receiver Unit Dimensions (hwd / cm.)	2.97 x 10 x 12.8
Receiver Unit Dimensions (hwd / in.)	1.17 x 3.94 x 5.04
Receiver Unit Weight (kg)	1.4993
Receiver Unit Weight (lbs.)	0.2
Shipping Dimensions (hwd / cm)	27.43 x 11.94 x 34.04
Shipping Dimensions (hwd / in.)	10.80 x 4.70 x 13.40
Shipping Weight (kg)	3.54
Shipping Weight (lbs.)	7.80
Transmitter Unit Dimensions (hwd / cm.)	2.97 x 10 x 12.8
Transmitter Unit Dimensions (hwd / in.)	1.17 x 3.94 x 5.04
Transmitter Unit Weight (kg)	1.4993
Transmitter Unit Weight (lbs.)	0.2
Unit Packaging Type	Box
Housing	Metal
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 °F (0 to 40 °C)
Storage Temperature Range	5 to 122 °F (-15 to 50 °C)
Relative Humidity	0% to 85%, Non-Condensing
COMMUNICATIONS	
Signal Range (ft.)	656
Signal Range (m)	200
EDID Compatible	Yes
IR Remote Extension Support	Yes



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

RS-232 Serial Extension Support	Yes
Consumer Electronics Control (CEC) Supported	Yes
Latency	2-3 seconds
USB Extension Support	No
CONNECTIONS	
Side A - Connector 1	(6) HDMI (FEMALE)
Side A - Connector 2	(3) RJ45 (FEMALE)
Side A - Connector 3	(6) 3.5MM (FEMALE)
Side B - Connector 1	(1) HDMI (FEMALE)
Side B - Connector 2	(1) RJ45 (FEMALE)
FEATURES & SPECIFICATIONS	
HDCP Specification	1.4
Driver Required	No
Recommended Category Cable	CAT6
Built-In Equalizer	No
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[B160-103-HDSI](#)