

IR over Wireless Signal Extender Kit - Up to 656 ft. (199.94 m)

MODEL NUMBER: **B164-101-WIR**



Allows you to control your IR-enabled device from 656 ft. away without it being in direct line of sight.

Features

Wireless IR Extender Recommended for Displaying Video in Conference Rooms and Bars This complete wireless IR transmitter and receiver system is ideal for audio/video presentations in conference rooms, lecture halls, home theaters, restaurants, bars and other locations where the source and display devices need to be separated or hidden from view. The B164-101-WIR allows you to control the IR-enabled source device, such as a DVD player or cable box, while holding its remote up to 656 feet (200 meters) away from it.

IR Pass Through Allows Total Access and Control with No Latency The included transmitter and receiver units accept all IR signal frequencies from 20 kHz to 60 kHz to ensure compatibility with your IR devices. Because the source and display do not have to be within each other's line of sight, you are free to store them in separate rooms or inside IDF closets and entertainment centers. Make sure the receiver's IR bulb is within sight of the source and the transmitter's IR bulb is in range of the source's remote. The extender uses a 915 MHz RF (radio frequency) band for wireless communication.

Plug-and-Play Operation for Quick Setup and Immediate Use The wireless IR extender kit works right out of the box with no software or drivers required. Connect the included IR cables for remote control, and connect the included USB cables to power the transmitter and receiver units. "Lock ID" buttons on each unit exclusively pair the transmitter and receiver, preventing interference from other components. Blue LEDs indicate power, data transmission and connection status.

Specifications

Highlights

- Control your IR device up to 656 ft. (200 m) away through ceilings and walls
- IR pass through allows use of the source's remote while near the display with no latency
- Accepts IR signal frequencies from 20–60 kHz, so it's compatible with all your IR devices
- Durable aluminum housings dissipate heat to keep units functioning at their peak
- Easy plug-and-play operation—just connect and pair the transmitter and receiver

Applications

- Watch television in one room, while changing channels on the cable box or DVR located in a different room or secured inside a cabinet
- Extend audio/video signals in an environment where drilling through walls for cabling is impossible or not practical
- Gain flexibility in where the source and display are placed, with the freedom to move and relocate them where needed
- Create a cleaner, streamlined installation for a restaurant, bar, trade show booth, lecture hall or home theater

System Requirements

- Source and display devices with IR capability

Package Includes

- Transmitter unit
- Receiver unit
- IR-Out cable
- IR-In cable
- (2) USB-to-DC power cables
- (2) Wireless signal antennas
- Owner's manual

OVERVIEW	
UPC Code	037332225832
Product Type	Extender Kit
Technology	IR; Wireless
VIDEO	
HDR Support	No
Maximum Signal Range (ft)	656
Maximum Signal Range (m)	200
INPUT	
Bus Powered	Yes
POWER	
Power Over Cable (PoC) Support	No
Power Consumption Detail	TX: <300MV, RX: <300MV
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	TX: 1x BLUE LED (SIGNAL); RX: 1x BLUE LED (SIGNAL)
PHYSICAL	
Color	Black
Material of Construction	Aluminum
Rackmountable	No
Receiver Unit Dimensions (hwd / in.)	2.95 x 4.92 x 3.3
Receiver Unit Weight (lbs.)	0.62
Shipping Dimensions (hwd / in.)	2.95 x 4.92 x 3.30
Shipping Dimensions (hwd / cm)	7.49 x 12.50 x 8.38
Shipping Weight (lbs.)	0.62
Shipping Weight (kg)	0.28
Transmitter Unit Dimensions (hwd / in.)	2.95 x 4.92 x 3.3
Transmitter Unit Weight (lbs.)	0.62
Unit Packaging Type	Box
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)

Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	10% to 90% RH, Non-Condensing
COMMUNICATIONS	
Signal Range (ft.)	656
Signal Range (m)	200
Transmission Distance	200m
IR Remote Extension Support	Yes
RS-232 Serial Extension Support	No
USB Extension Support	No
CONNECTIONS	
Side A - Connector 1	3.5MM (FEMALE)
Side B - Connector 1	3.5MM (FEMALE)
Daisy-chainable / Cascadable	No
FEATURES & SPECIFICATIONS	
Driver Required	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA); Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[B164-101-WIR](#)