





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-	9507	RELEASED	4/29/09	
A		UPDATE DRAWING	10/13/14	HR/NP



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material: Insulator: Nylon 66, rated UL 94V-0
Insulator color: Beige
Contacts: Brass
Plating: Tin over Copper underplate overall
Electrical: Operating voltage: 250 VDC max
Current rating: AC/DC 1 Amp max
Contact resistance: 30 mohms max
Insulation resistance: 1,000 Mohms min @ 500 VDC
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating: Operating temperature: -25°C to +85°C
Environmental: Lead free, RoHS compliant

Positions: 2 thru 15, 20, 25, 30
A = .049 [1.25] x No. of Spaces
B = .049 [1.25] x No. of Positions + .026 [0.65]
C = .049 [1.25] x No. of Positions + .049 [1.25]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES Holes .X ± .10 ØX ± .10 .XX ± .020 ØXX ± .015 .XXX ± .015 ØXXX ± .010				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
APPROVALS				TITLE .049 [1.25] SHROUNDED HEADER STRAIGHT, PCB			
DRAWN	DY	4/29/09		SIZE	PART NO.	125SH-C-XX-TS	REV.
CHECKED				X			A
APPROVED				REF: S00099T	SCALE: NTS	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[125SH-C-05-TS](#) [125SH-C-13-TS](#) [125SH-C-10-TS](#) [125SH-C-15-TS](#) [125SH-C-06-TS](#) [125SH-C-09-TS](#) [125SH-C-04-TS](#) [125SH-C-08-TS](#) [125SH-C-11-TS](#) [125SH-C-02-TS](#) [125SH-C-03-TS](#) [125SH-C-14-TS](#) [125SH-C-12-TS](#) [125SH-C-07-TS](#)