

6

5

4

3




2

1

APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	01/17/07	
A		REVISED SPEC	9/8/11	



RECOMMENDED PC BOARD LAYOUT

SPECIFICATIONS:

Material:

Insulator: Hi-Temp. Thermoplastic, rated UL 94V-0

Insulator color: Natural

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 50 VAC max

Current rating: 1 Amp max

Contact resistance: 20 mohms max.

Insulation resistance: 100 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant

ROHS  
COMPLIANT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH			
INCHES				909 Railway Avenue, Union, NJ 07083			
HOLES				Phone: 908-687-5000 Fax: 908-687-5710			
.X	± .10	ØX	± .10	TITLE 1.0mm WIRE TO BOARD WAFER SMT SIDE ENTRY			
.XX	± .020	ØXX	± .015				
.XXX	± .015	ØXXX	± .010				
APPROVALS				DATE			
DRAWN	BW			01/17/07			
CHECKED							
APPROVED							
SIZE				PART NO.			
X				1SH-A-XX-TR-SMT			
REF: S00016T				SCALE: NTS			
				SHEET 1 OF 1			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[1SH-A-02-TR-SMT](#) [1SH-A-08-TR-SMT](#) [1SH-A-12-TR-SMT](#) [1SH-A-20-TR-SMT](#) [1SH-A-03-TR-SMT](#) [1SH-A-10-TR-SMT](#) [1SH-A-15-TR-SMT](#) [1SH-A-04-TR-SMT](#) [1SH-A-11-TR-SMT](#) [1SH-A-09-TR-SMT](#) [1SH-A-05-TR-SMT](#) [1SH-A-06-TR-SMT](#) [1SH-A-07-TR-SMT](#) [1SH-A-13-TR-SMT](#) [1SH-A-14-TR-SMT](#)