





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/7/05	
A		UPDATED SPECS	7/12/17	



PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 3 Amps max

Contact resistance: 10 mohms max

Insulation resistance: 1,000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 15
A = .079 [2.00] x No. of Positions + .075 [1.90]
B = .079 [2.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				ADAM TECH 909 Railway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
HOLES				TITLE .079 [2.00] SHROUDED HEADER RIGHT ANGLE, PCB			
.X	± .10	Ø.X	± .10				
.XX	± .020	Ø.XX	± .015				
.XXX	± .015	Ø.XXX	± .010				
APPROVALS				DATE			
DRAWN	SS	4/7/05					
CHECKED				SIZE PART NO. REV.			
APPROVED				X 2SH-C-XX-TR A			
REF:				SCALE: NTS SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[2SH-C-02-TR](#) [2SH-C-03-TR](#) [2SH-C-04-TR](#) [2SH-C-06-TR](#) [2SH-C-05-TR](#) [2SH-C-08-TR](#) [2SH-C-09-TR](#) [2SH-C-10-TR](#) [2SH-C-07-TR](#) [2SH-C-16-TR](#) [2SH-C-14-TR](#) [2SH-C-12-TR](#) [2SH-C-11-TR](#) [2SH-C-15-TR](#) [2SH-C-13-TR](#)