

8.6kW 3-Phase Monitored PDU, 208/120V Outlets (36 C13, 6 C19 & 3 5-15/20R), NEMA L21-30P, 10 ft. Cord, 0U Vertical, TAA

MODEL NUMBER: PDU3VN10L2130



High-capacity 8.6kW PDU powers high-density data center equipment racks. LED display and Ethernet interface help you monitor load levels with billing-grade accuracy to prevent PDU and circuit overloads that cause downtime.

Description

The PDU3VN10L2130 8.6kW 3-Phase Monitored PDU features 45 outlets for distributing network-grade 208/120V AC power to rack-mounted network devices, including computers, servers, routers and switches. Outlets are arranged in six load banks: 36 C13 208V and six C19 208V outlets divided evenly into three banks and three NEMA 5-15/20R 120V outlets, each in its own bank.

A built-in SNMPWEBCARD enables full remote access for power monitoring, configuration, control and notifications 24 hours a day via secure web browser, telnet or SSH, as well as real-time load/current data with billing-grade accuracy (+/- 1 percent). Tiered access privileges allow both an administrator and a guest to log in. Automated alerts help prevent accidental overloads, power loss and downtime. Digital LED display indicates amps, kilowatts, volts and power unbalance percentage, as well as temperature and humidity conditions when using the optional ENVIROSENSE module (sold separately).

Protocols supported include HTTP, HTTPS, PowerAlert®, SMTP, SNMPv1, SNMPv2, SNMPv3, telnet, SSH, FTP, DHCP, BOOTP and NTP. Network settings can be assigned automatically or manually.

Ideal for three-phase network configurations in high-density data centers and heavily configured equipment racks, the PDU3VN10L2130 mounts vertically in 0U of rack space using the pre-installed buttons or included hardware. The NEMA L21-30P input plug with 10-foot cord connects to a compatible AC power source, generator or protected UPS.

Features

Highlights

- Ideal for 3-phase configurations in high-density data centers
- 3-phase input and single-phase 208/120V output
- 45 outlets (36 C13, 6 C19 & 3 5-15/20R) in 6 load banks
- Ethernet network interface for full remote access 24/7
- Digital LED display for local load monitoring

Package Includes

- PDU3VN10L2130 8.6kW 208/120V 3-Phase Monitored PDU, 10 ft. cord
- (36) C13/C14 plug-lock inserts
- (6) C19/C20 plug-lock inserts
- Spare mounting buttons
- (2) Conventional mounting brackets
- Configuration cable for network interface
- Button/bracket-mounting hardware
- Owner's manual



Distributes Network-Grade Power

- 36 C13 and 6 C19 208V outlets and 3 NEMA 5-15/20R 120V outlets distribute network-grade power to connected equipment
- 6 load banks
- Outlets numbered and color-coded for easy identification of phase and load bank

Multi-Function Digital LED Display

- Indicates amps, watts, volts, power unbalance percentage, as well as selected input phase, load bank, output power and sensor option
- Rotates 180° for overhead or raised-floor power feeds

Advanced Network Monitoring

- Built-in SNMPWEBCARD enables full remote access for power monitoring, configuration and control via secure web browser, telnet or SSH
- Real-time load/current data with billing-grade accuracy (+/- 1%)
- Tiered access allows administrator and guest to log in
- Automated alerts help prevent accidental overloads, power loss and downtime
- Optional ENVIROSENSE module (sold separately) monitors temperature and humidity conditions

Broad Communications Compatibility

- Supports HTTP, HTTPS, PowerAlert, SMTP, SNMPv1, SNMPv2, SNMPv3, telnet, SSH, FTP, DHCP, BOOTP and NTP
- Network settings can be automatically or manually assigned via permanent IP addresses

Connects to AC Power Source

- NEMA L21-30P input plug with 10 ft. cord for connection to mains power source, generator or protected UPS
- Plug-lock inserts keep equipment power cords connected to outlets

Ready for Immediate 0U Toolless Rack-Mounting

- Pre-installed buttons for toolless mounting in compatible EIA-standard 2-post and 4-post racks
- Conventional 0U installation possible with included mounting hardware

TAA-Compliant

- Complies with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332196071



Tripp Lite
 1111 W. 35th Street
 Chicago, IL 60609 USA
 Telephone: 773.869.1234
 www.tripplite.com

PDU Type	Monitored
OUTPUT	
Output Capacity Details	8.6kW (208V) total capacity; 13.9A max per breakered outlet bank; 12A max per C13 outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(3) 5-15/20R; (36) C13; (6) C19
Output Receptacle Details	5-15/20R outlets provide 120V output; C13 and C19 outlets provide 208V output
Output Nominal Voltage	120; 208
Overload Protection	3 20A double-pole circuit breakers (1 per output phase)
INPUT	
PDU Input Voltage	208
Recommended Electrical Service	30A 208V with L21-30R outlet
Maximum Input Amps	24
PDU Plug Type	NEMA L21-30P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
Input Phase	3-Phase
USER INTERFACE, ALERTS & CONTROLS	
Reported Load Segments	Supports monitoring of input current per phase (L1, L2, L3) and output current for each output load bank (B1-B6); Outlets are color-coded and labeled for phase and load bank identification; L1-L2 feeds black C13/C19 outlets (B1); L2-L3 feeds dark-gray C13/C19 outlets (B2); L3-L1 feeds light-gray C13/C19 outlets (B3); L1-N feeds black 5-20R outlet (B4); L2-N feeds dark-gray 5-20R outlet (B5); L3-N feeds light-gray 5-20R outlet (B6)
Front Panel LCD Display	Large digital display reports Amperage, Kilowatts, Voltage, Unbalance percentage, Temperature* and Humidity* information (*requires ENVIROSENSE option); Small digital display provides detail on the measurement the large display is reporting: Input-phase (L#), Load bank (B#), Sensor (S#), Load unbalance (UB), Output power (OP)
Front Panel LEDs	Set of 6 LEDs identify the value displayed on the large digital display: Amperage (A), Kilowatts (kW), Voltage (V), Unbalance percentage (%UB), Temperature (T), Humidity (%RH); 3 additional multi-color LEDs offer power availability information for each pair of output load banks (Bank 1&4 / Bank 2&5 / Bank 3&6): GREEN (<80% load), YELLOW (>80% load), RED (Power OFF), RED FLASHING (Power OFF/breaker trip)
Switches	Set of UP/DOWN arrow buttons scroll through available Input, Bank, Power, Load balance and Sensor options; Additional MODE button advances the LEDs to view the next measurement
PHYSICAL	
Shipping Dimensions (hwd / in.)	6.30 x 9.70 x 75.80
Shipping Dimensions (hwd / cm)	16.00 x 24.64 x 192.53
Shipping Weight (lbs.)	23.80
Shipping Weight (kg)	10.80
Unit Dimensions (hwd / in.)	70 x 2.17 x 2.52
Unit Dimensions (hwd / cm)	177.8 x 5.512 x 6.401
Unit Weight (lbs.)	13.5



Unit Weight (kg)	6.12
Material of Construction	Metal
Form Factors Supported	Vertical rackmount installation supported with included mounting brackets; supports toolless mounting in button-mount compatible racks
PDU Form Factor	Vertical (0U)
ENVIRONMENTAL	
Storage Temperature Range	5 to 122F (-15 to 50C)
Relative Humidity	5 to 95% non-condensing
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
CERTIFICATIONS	
Certifications	Tested to UL60950-1 (USA, Canada), NOM (Mexico), Class A (Emissions), ROHS, TAA Compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PDU3VN10L2130](#)