








APPROVED: _____

DATE: _____ TITLE: _____

| Rev | AWO # | Description | Date | Appr |
|-----|-------|----------------------------|----------|-------|
| - | | RELEASED | 4/7/05 | |
| A | | REVISED INSULATOR MATERIAL | 10/25/11 | |
| B | | REVISED SPEC. | 11/20/12 | |
| C | | UPDATE DRAWING | 3/24/21 | LH/LW |



SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 250 V AC/DC

Current rating: 2.5 A AC/DC

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 600 VAC for 1 minute

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 18

A = .100 [2.54] x No. of Spaces

B = .100 [2.54] x No. of Positions + .100 [2.54]

C = .100 [2.54] x No. of Positions + .025 [0.64]

D = (4P-18P) .100 [2.54] x No. of Positions - .200 [5.08]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

| | | | |
|------|--------|-------|--------|
| .X | ± .10 | Ø.X | ± .10 |
| .XX | ± .020 | Ø.XX | ± .015 |
| .XXX | ± .015 | Ø.XXX | ± .010 |

APPROVALS

DATE

DRAWN

SS

4/7/05

CHECKED

APPROVED

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

.100 [2.54] LATCHING HEADER
RIGHT ANGLE, PCB

SIZE

X

PART NO.

CDR-XX-TR

REV.

C

REF: S00016T

SCALE: NTS

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[CDR-10-TR](#) [CDR-05-TR](#) [CDR-02-TR](#) [CDR-11-TR](#) [CDR-04-TR](#) [CDR-09-TR](#) [CDR-08-TR](#) [CDR-12-TR](#) [CDR-07-TR](#)
[CDR-06-TR](#) [CDR-03-TR](#)