











6	5	4	3	2	1																																																								
APPROVED: _____ DATE: _____ TITLE: _____			Rev -	AWO # 	Description RELEASED	Date 2/21/20	Appr 																																																						
 .550 [13.97]  .250 [6.35] 2 POSITION  .800 [20.32]  .500 [12.70] 3 POSITION  1.050 [26.67]  .750 [19.05] 4 POSITION  ALL MALE PIN B  A .100 [2.54] 5~10 POSITION  .300 [7.62] .581 [14.77] .157 [4.00]  A .250 [6.35] Ø.071 [1.80] .175 [4.45] RECOMMENDED PCB LAYOUT SINGLE ROW																																																													
<table><tr><th rowspan="2">Poles</th><th colspan="4">Dimensions</th></tr><tr><th colspan="2">A</th><th colspan="2">B</th></tr><tr><td>02</td><td>.250</td><td>[6.35]</td><td>.550</td><td>[13.97]</td></tr><tr><td>03</td><td>.500</td><td>[12.70]</td><td>.800</td><td>[20.32]</td></tr><tr><td>04</td><td>.750</td><td>[19.05]</td><td>1.050</td><td>[26.67]</td></tr><tr><td>05</td><td>1.000</td><td>[25.40]</td><td>1.307</td><td>[33.20]</td></tr><tr><td>06</td><td>1.250</td><td>[31.75]</td><td>1.550</td><td>[39.37]</td></tr><tr><td>07</td><td>1.562</td><td>[38.10]</td><td>1.800</td><td>[45.72]</td></tr><tr><td>08</td><td>1.750</td><td>[44.45]</td><td>2.050</td><td>[52.07]</td></tr><tr><td>09</td><td>2.000</td><td>[50.80]</td><td>2.300</td><td>[58.42]</td></tr><tr><td>10</td><td>2.250</td><td>[57.15]</td><td>2.550</td><td>[64.77]</td></tr></table>								Poles	Dimensions				A		B		02	.250	[6.35]	.550	[13.97]	03	.500	[12.70]	.800	[20.32]	04	.750	[19.05]	1.050	[26.67]	05	1.000	[25.40]	1.307	[33.20]	06	1.250	[31.75]	1.550	[39.37]	07	1.562	[38.10]	1.800	[45.72]	08	1.750	[44.45]	2.050	[52.07]	09	2.000	[50.80]	2.300	[58.42]	10	2.250	[57.15]	2.550	[64.77]
Poles	Dimensions																																																												
	A		B																																																										
02	.250	[6.35]	.550	[13.97]																																																									
03	.500	[12.70]	.800	[20.32]																																																									
04	.750	[19.05]	1.050	[26.67]																																																									
05	1.000	[25.40]	1.307	[33.20]																																																									
06	1.250	[31.75]	1.550	[39.37]																																																									
07	1.562	[38.10]	1.800	[45.72]																																																									
08	1.750	[44.45]	2.050	[52.07]																																																									
09	2.000	[50.80]	2.300	[58.42]																																																									
10	2.250	[57.15]	2.550	[64.77]																																																									
SPECIFICATIONS: Material: Insulator: Nylon 66, rated UL 94V-2 Insulator color: Natural Contacts: Phosphor Bronze, Tin plated Electrical: Current rating: 02~10P: 12 Amp Max (With UL1015, 12AWG) Contact resistance: 20 mohms max Insulation resistance: 1,000M ohms min Dielectric withstanding voltage: 2,900 VAC for 1 minute Temperature Rating: -40°C to +105°C Environmental: Lead free, RoHS compliant. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED INCHES HOLES <table><tr><td>.X</td><td>± .10</td><td>Ø.X</td><td>± .10</td></tr><tr><td>.XX</td><td>± .020</td><td>Ø.XX</td><td>± .015</td></tr><tr><td>.XXX</td><td>± .015</td><td>Ø.XXX</td><td>± .010</td></tr></table><table><tr><th colspan="2">APPROVALS</th><th>DATE</th></tr><tr><td>DRAWN</td><td>LH</td><td>2/21/20</td></tr><tr><td>CHECKED</td><td>AY1</td><td>2/21/20</td></tr><tr><td>APPROVED</td><td></td><td></td></tr></table> ADAM TECH INTERCONNECTS 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710 <table><tr><td colspan="3">TITLE WIRE TO BOARD, FEMALE, 6.35mm PITCH, WITH POLARIZING PEG, MALE PIN</td></tr><tr><td>SIZE X</td><td>PART NO. DME-XX-S2-P-S</td><td>REV. -</td></tr><tr><td>REF: S00124T</td><td>SCALE: NTS</td><td>SHEET 1 OF 1</td></tr></table>								.X	± .10	Ø.X	± .10	.XX	± .020	Ø.XX	± .015	.XXX	± .015	Ø.XXX	± .010	APPROVALS		DATE	DRAWN	LH	2/21/20	CHECKED	AY1	2/21/20	APPROVED			TITLE WIRE TO BOARD, FEMALE, 6.35mm PITCH, WITH POLARIZING PEG, MALE PIN			SIZE X	PART NO. DME-XX-S2-P-S	REV. -	REF: S00124T	SCALE: NTS	SHEET 1 OF 1																					
.X	± .10	Ø.X	± .10																																																										
.XX	± .020	Ø.XX	± .015																																																										
.XXX	± .015	Ø.XXX	± .010																																																										
APPROVALS		DATE																																																											
DRAWN	LH	2/21/20																																																											
CHECKED	AY1	2/21/20																																																											
APPROVED																																																													
TITLE WIRE TO BOARD, FEMALE, 6.35mm PITCH, WITH POLARIZING PEG, MALE PIN																																																													
SIZE X	PART NO. DME-XX-S2-P-S	REV. -																																																											
REF: S00124T	SCALE: NTS	SHEET 1 OF 1																																																											
6	5	4	3	2	1																																																								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DME-03-S2-P-S](#) [DME-02-S2-P-S](#) [DME-04-S2-P-S](#)