




APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Insulator: Hi-Temp Thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Operating voltage: 250 V

Current rating: 20 & 22 Awg: 5 Amps max

24 Awg: 4 Amps max

26 Awg: 3 Amps max

28 Awg: 2 Amps max

30 Awg: 1 Amp max

Contact resistance: 10 mohms max

Dielectric strength: 1,500 VAC for 1 minute

Temperature Rating:


-45°C to +125°C

Environmental:

Lead free, RoHS compliant.



Rev	AWO #	Description	Date	Appr
-	9648	RELEASED	2/15/07	
A		UPDATED	11/23/07	
B		UPDATED	1/07/08	
C		REDRAWN	7/16/09	
D		REVISED SOLDERIND TEMP	2/16/12	
E		REVISED DIMENSION C	3/12/12	
F		REVISED TOP VIEW	10/6/14	
G		UPDATED	5/19/16	AY/LL



PCB LAYOUT: COMPONENT SIDE
RECOMMENDED PCB THICKNESS: .062" [1.57]

POSITIONS	Dimension	
	A	B
2	NA	.262 [6.65]
4	.118 [3.00]	.380 [9.65]
6	.236 [6.00]	.498 [12.65]
8	.354 [9.00]	.616 [15.65]
10	.472 [12.00]	.734 [18.65]
12	.591 [15.00]	.852 [21.65]
14	.709 [18.00]	.970 [24.65]
16	.827 [21.00]	1.088 [27.65]
18	.945 [24.00]	1.206 [30.65]
20	1.063 [27.00]	1.325 [33.65]
22	1.181 [30.00]	1.443 [36.65]
24	1.299 [33.00]	1.561 [39.65]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	BW	2/15/07
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
.118 [3.00] DUAL ROW THRU HOLE HEADER
VERTICAL TYPE

SIZE X	PART NO. DML-XX-A-V-T-A	REV. G
REF: S00123T	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DML-16-A-V-T-A](#) [DML-06-A-V-T-A](#) [DML-12-A-V-T-A](#) [DML-10-A-V-T-A](#) [DML-24-A-V-T-A](#) [DML-04-A-V-T-A](#) [DML-14-A-V-T-A](#) [DML-08-A-V-T-A](#)